

























## Hazlux® 3 Standard housing

Individual components (to be used with ballast housing)




### Mounting options

			Part no.	Description	Conduit hub size (in)
 Rigid pendant	 Ceiling mount	 Wall mount	VP2	Rigid pendant	¾
			VP3	Rigid pendant	1
 Cone-top pendant	 25° angle stanchion	 Wall mount	VA2	Cone-top pendant	¾
			VA3	Cone-top pendant	1
 Flexible pendant	 HazVertor™ adapter ring	 25° angle stanchion	VF2	Flexible pendant	¾
			VF3	Flexible pendant	1
 Ceiling mount	 25° angle stanchion	 Wall mount	VC2	Ceiling mount	¾
			VC3	Ceiling mount	1
 Wall mount	 25° angle stanchion	 Wall mount	VB2-VIB	Wall mount	¾
			VB3-VIB	Wall mount	1
 25° angle stanchion	 25° angle stanchion	 25° angle stanchion	VS4-VIB	25° angle stanchion	1¼
			VS5-VIB	25° angle stanchion	1½
 Straight stanchion	 Straight stanchion	 Straight stanchion	VL4-VIB	Straight stanchion	1¼
			VL5-VIB	Straight stanchion	1½
			HV1	HazVertor™ adapter ring	N/A
			HV2	HazVertor™ adapter ring	N/A

### Globes or refractors




			Part no.	Description
 Heat-resistant globe	 Reflector glass	 Low-bay refractor	VGT22	5½"-dia. heat-resistant globe (250W max.)
			VGT22TS	5½"-dia. heat-resistant globe (250W max.) Coated with Tuff-Skin®
			VRF22C2	12"-dia. IES Type II refractor, 5½" thread
			VRF22C5	12"-dia. IES Type V refractor, 5½" thread
			VR22CBDL	Low-bay refractor with plastic lens

### Guards

			Part no.	Description
 Polymeric guard	 Cast guard	 Wire guard	VGU22P	Polymeric guard for VGT22 series globe
			VGU22	Polymeric guard for VGT22 series globe
			VGR48	Steel wire guard for All VRF series 12" refractors

## Individual components

### Reflectors or exit sign

			Part no.	Description
 Standard dome	 30° angle reflector	 Three sided exit Sign	VR22P	Standard dome, fiberglass-reinforced polyester
			VRA22P	30° angle reflector, fiberglass-reinforced polyester
			VRE22	Three-sided exit sign

Note: Reflectors are shipped bulk unless specified