

Tmax XT ranges

XT2 Accessories

3



SOR uncabled



SOR cabled



SOR for withdrawable



UVR uncabled



UVR cabled



UVR for withdrawable



Time delay device for undervoltage release

Service releases

Shunt opening release - SOR

Type	Fixed/Plug-in Part number	Withdrawable Part number
Uncabled version		
SOR 12V DC	KXTASORA	-
SOR 24-30V AC/DC	KXTASORB	-
SOR 48-60V AC/DC	KXTASORC	-
SOR 110...127V AC / 110...125V DC	KXTASORD	-
SOR 220...240V AC / 220...250V DC	KXTASORE	-
SOR 380-440V AC	KXTASORF	-
SOR 480-525V AC	KXTASORG	-
Cabled version		
SOR-C 12V DC	KXTASORCFPA	KXTCSORCWA
SOR-C 24-30V AC/DC	KXTASORCFPB	KXTCSORCWB
SOR-C 48-60V AC/DC	KXTASORCFPC	KXTCSORCWC
SOR-C 110...127V AC / 110...125V DC	KXTASORCFPD	KXTCSORCWD
SOR-C 220...240V AC / 220...250V DC	KXTASORCFPE	KXTCSORCWE
SOR-C 380-440V AC	KXTASORCFPF	KXTCSORCWF
SOR-C 480-525V AC	KXTASORCFPG	KXTCSORCWG

Undervoltage release - UVR

Type	Fixed/Plug-in Part number	Withdrawable Part number
Uncabled version		
UVR 24-30V AC/DC	KXTAUVR1	-
UVR 48V AC/DC	KXTAUVR2	-
UVR 60V AC/DC	KXTAUVR3	-
UVR 110...127V AC / 110...125V DC	KXTAUVR4	-
UVR 220...240V AC / 220...250V DC	KXTAUVR5	-
UVR 380-440V AC	KXTAUVR6	-
UVR 480-525V AC	KXTAUVR7	-
Cabled version		
UVR-C 24-30V AC/DC	KXTAUVRCFP1	KXTCUVRWC1
UVR-C 48V AC/DC	KXTAUVRCFP2	KXTCUVRWC2
UVR-C 60V AC/DC	KXTAUVRCFP3	KXTCUVRWC3
UVR-C 110...127V AC / 110...125V DC	KXTAUVRCFP4	KXTCUVRWC4
UVR-C 220...240V AC / 220...250V DC	KXTAUVRCFP5	KXTCUVRWC5
UVR-C 380-440V AC	KXTAUVRCFP6	KXTCUVRWC6
UVR-C 480-525V AC	KXTAUVRCFP7	KXTCUVRWC7

Delay device for undervoltage release - UVD⁽¹⁾

Type	Part number
UVD 24...30V AC/DC	KT3UVD8
UVD 48...60V AC/DC	KT3UVD7
UVD 110...125V AC/DC	KT3UVD4
UVD 220...250V AC/DC	KT3UVD2

⁽¹⁾IEC rated only.

Tmax XT ranges

XT2 Accessories



Socket-plug panel connector



Fixed part socket-plug connector



AUX uncabled



AUX cabled



Connectors

Fourth pole connectors for withdrawable⁽¹⁾

Type	Part number
Connector 4th Pole SOR / PS-SOR	KXTCE3PINCONSOR
Connector 4th Pole UVR	KXTCE3PINCONUVR

⁽¹⁾IEC rated only.

Socket plug connector on the panel⁽¹⁾

Type	Part number
Socket -plug connector with 3 PINS	KXTAE3PINCON
Socket -plug connector with 6 PINS	KXTAE6PINCON
Socket -plug connector with 9 PINS	KXTAE9PINCON
Socket -plug connector with 15 PINS	KXTAE15PINCON

⁽¹⁾IEC rated only.

Fixed part socket-plug connector⁽¹⁾

Type	Part number
Socket-plug connector of moving part - 12 PINS	KXTCE12PINMPCON
Socket-plug connector of fixed part - 12 PINS	KXTCE12PINFPCON

⁽¹⁾IEC rated only.

Electrical signals

Auxiliary contacts - AUX

Type	Fixed/Plug-in Part number	Withdrawable Part number
Uncabled version		
AUX 250V	KXTAAUX	-
AUX 24V DC	KXTAAUXD	-
AUX-S51 250V	KXTCAXS51	-
AUX-S51 24V DC	KXTCAXDS51	-
Cabled version		
AUX-C 3 Q 250V Left	KXTCAXC3QL	-
AUX-C 1 Q + 1 SY 250V	KXTAAXCQSYFP	KXTCAXCQSYW
AUX-C 2 Q + 1 SY 250V	KXTAAXC2QSYFP	-
AUX-C 3 Q + 1 SY 250V	KXTDAXC3QSYFP	KXTCAXC3QSYW
AUX-C 3 Q + 2 SY 250V	KXTCAXC3Q2SYFP	KXTCAXC3Q2SYW
AUX-C 2 Q + 2 SY + 1 S51 250V	KXTCAXC2Q2SYS51FP	KXTCAXC2Q2SYS51W
AUX-S51-C 250V	KXTCAXCS51FP	KXTCAXCS51W
AUX-C 1 Q + 1 SY 24V DC	KXTAAXCDQSYFP	KXTCAXCDQSYW
AUX-C 3 Q + 1 SY 24V DC	KXTDAXCD3QSYFP	KXTCAXCD3QSYW
AUX-S51-C 24V DC	KXTCAXDS51FP	KXTCAXDS51W
AUX-C 1 Q + 1 SY 400V AC	KXTCAXC4QSYFP	KXTCAXC4QSYW
AUX-C 2 Q 400V AC	KXTCAXC42QFP	KXTCAXC42QW

Tmax XT ranges

XT2 Accessories

Rotary handle operating mechanisms



Direct handle



Extended handle



IP54

Rotary handle operating mechanisms

Type	Fixed/Plug-in Part number	Withdrawable Part number
RHD Standard Direct Handle	KXTCRHDSTFP	KXTCRHDSTW
RHD Emergency Direct Handle	KXTCRHDEMFP	KXTCRHDEMW
RHE Standard Extended Handle	KXTCRHESTFP	KXTCRHESTW
RHE Emergency Extended Handle	KXTCRHEEMFP	KXTCRHEEMW
RHE Standard Extended Handle with Padlock	KXTCRHESTFPPLK	KXTCRHESTWPLK
RHE Emergency Extended Handle with Padlock	KXTCRHEEMFPPLK	KXTCRHEEMWPLK
RHS-L Standard Left Side Handle	KXTCRHSLSSTFP	-
RHS-L Emergency Left Side Handle	KXTCRHSLEMFP	-
RHS-R Standard Right Side Handle	KXTCRHSRSSTFP	-
RHS-R Emergency Right Side Handle	KXTCRHSREMFP	-
Extended Handle Spare Parts		
RHE_B Base for Extended Handle	KXTCRHEBFP	KXTCRHEBW
RHE_B Base for Extended Handle with Padlock ⁽¹⁾	KXTCRHEBFPPLK	KXTCRHEBWPLK
RHE_S 500mm Shaft	KXTARHES500	KXTARHES500
RHE_H Standard Extended Handle	KXTARHEHST	KXTARHEHST
RHE_H Emergency Extended Handle	KXTARHEHEM	KXTARHEHEM
LH Standard Large Handle, NEMA 1	KXTALHNDLST	KXTALHNDLST
LH Emergency Large Handle, NEMA 1	KXTALHNDLEM	KXTALHNDLEM
Standard Pistol Handle with reset function, 65mm, NEMA 3R, 12	OHB65J10B	OHB65J10B
Emergency Pistol Handle with reset function, 65mm, NEMA 3R, 12	OHY65J10B	OHY65J10B
Standard Pistol Handle with reset function, 65mm, NEMA 4, 4X	OHB65L10B	OHB65L10B
Emergency Pistol Handle with reset function, 65mm, NEMA 4, 4X	OHY65L10B	OHY65L10B
Standard Pistol Handle with reset function, 125mm, NEMA 3R, 12	OHB125J10B	OHB125J10B
Emergency Pistol Handle with reset function, 125mm, NEMA 3R, 12	OHY125J10B	OHY125J10B
Standard Pistol Handle with reset function, 125mm, NEMA 4, 4X	OHB125L10B	OHB125L10B
Emergency Pistol Handle with reset function, 125mm, NEMA 4, 4X	OHY125L10B	OHY125L10B
148mm Pistol Handle Shaft	EXP10X148	EXP10X148
225mm Pistol Handle Shaft	EXP10X225	EXP10X225
500mm Pistol Handle Shaft	EXP10X500	EXP10X500

IP54 protection for transmitted rotary handle⁽¹⁾

Type	Part number
IP54 Protection for RHE	KXTAERHEIP54

⁽¹⁾IEC rated only.

Flange handle

Type	Part number
Flange Handle + Mechanism + 4ft Cable (NEMA 1, 3R, 12, 4)	KXT2N12FLHDL4
Flange Handle + Mechanism + 6ft Cable (NEMA 1, 3R, 12, 4)	KXT2N12FLHDL6
Flange Handle + Mechanism + 10ft Cable (NEMA 1, 3R, 12, 4)	KXT2N12FLHDL10
Flange Handle + Mechanism + 4ft Cable (NEMA 1, 3R, 12, 4, 4X) ⁽¹⁾	KXT2N4XFLHDL4
Flange Handle + Mechanism + 6ft Cable (NEMA 1, 3R, 12, 4, 4X) ⁽¹⁾	KXT2N4XFLHDL6
Flange Handle + Mechanism + 10ft Cable (NEMA 1, 3R, 12, 4, 4X) ⁽¹⁾	KXT2N4XFLHDL10

Flange Handle Spare Parts

Flange Handle only (NEMA 1, 3R, 12, 4)	KXTAN12FLHDL
Flange Handle only (NEMA 1, 3R, 12, 4, 4X) ⁽¹⁾	KXTAN4XFLHDL
Flange Handle Hardware	KXTAFLHDLHW
Flange Mounting Hardware	KXTCFLMTHW

⁽¹⁾Consult ABB for availability.