

Order code	Description	Watts (W)	Base	Volts (V)	Finish/Colour	Average life (hrs)	Filament	Initial lumens (lm)	MOL (in.) (mm)	LCL (in.) (mm)	Case qty	
BR30												
50219	50BR30/FL/5M/130V/STD	50	E26	130	Clear	5000	C-9	340	5.1 130	3.3 84	60	
¹ 50220	60BR30/FL/5M/130V/STD	60	E26	130	Clear	5000	C-9	420	5.1 130	3.3 84	60	
BR30 (Energy Saver)												
50079	65BR30/SP/5M/ES/130V/STD	65	E26	130	Clear	5000	CC-6	510	5.1 130	3.3 84	60	
50077	65BR30/FL/5M/ES/130V/STD	65	E26	130	Clear	5000	CC-6	510	5.1 130	3.3 84	60	
¹ 52000	85BR30/FL/5M/ES/130V/STD	85	E26	130	Clear	5000	CC-6	700	5.1 130	3.3 84	24	
BR38												
¹ 50055	75BR38/FL/5M/130V/STD	75	E26	130	Clear	5000	C-9	650	5.8 147	3.3 84	12	
¹ 50056	75BR38/SP/5M/130V/STD	75	E26	130	Clear	5000	C-9	765	5.8 147	3.3 84	12	
¹ 50053	100BR38/FL/5M/130V/STD	100	E26	130	Clear	5000	C-9	980	5.8 147	3.3 84	12	
¹ 14703	100BR38/SP/5M/130V	100	E26	130	Clear	5000	C-9	980	5.8 147	3.3 84	12	
BR38 (Energy Saver)												
¹ 52105	120BR38/SP/5M/ES/130V/STD	120	E26	130	Clear	5000	CC-6	1180	5.8 147	3.3 84	12	
¹ 52001	120BR38/FL/5M/ES/130V/STD	120	E26	130	Clear	5000	CC-6	1180	5.8 147	3.3 84	12	
BR40												
¹ 50062	75BR40/FL/5M/130VSTD	75	E26	130	Clear	5000	C-9	630	6.6 167	4.3 108	24	
¹ 50064	100BR40/FL/5M/130V/STD	100	E26	130	Clear	5000	C-9	930	6.6 167	4.3 108	24	
¹ 50483	200BR40/FL/5M/130V/STD	200	E26	130	Clear	5000	C-9	2050	6.6 167	4.4 111	24	
50482	300BR40/FL/5M/130V/STD	300	E26	130	Clear	5000	C-9	3000	6.6 167	4.3 108	24	
BR40 (Energy Saver)												
50080	65BR40/FL/5M/ES/130V/STD	65	E26	130	Clear	5000	CC-6	520	6.6 167	4.3 108	24	
¹ 50081	85BR40/FL/5M/ES/130V/STD	85	E26	130	Clear	5000	CC-6	760	6.6 167	4.3 108	24	
¹ 50083	120BR40/SP/5M/ES/130V/STD	120	E26	130	Clear	5000	CC-6	1180	6.6 167	4.3 108	24	
C7												
50967	4C7/CL/3M/E12/125V/STD	4	E12	125	Clear	3000	C-7A	15	2.1 54	1.5 38	500	
14686	5C7/CL/3M/E12/120V	5	E12	120	Clear	3000	C-7A	20	2.1 54	1.5 38	2000	
22008	7C7/CL/2M/E12/120V/STD/2P	7	E12	120	Clear	2000	C-7A	26	2.1 54	1.5 38	120	
CA4.5												
50634	7.5CA4.5/CL/2M/E12/120V/STD	7.5	E12	120	Clear	2000	C-7A	45	2.8 70	1.6 41	500	
50633	7.5CA4.5/CL/2M/E12/130V/STD	7.5	E12	130	Clear	2000	C-7A	36	2.8 70	1.6 41	500	
52154	7.5CA4.5/F/2M/E12/130V/STD	7.5	E12	130	Frost	2000	C-7A	34	2.8 70	1.6 41	500	
52153	10CA4.5/CL/2M/E12/130V/STD	10	E12	130	Clear	2000	C-7A	51	2.8 70	1.6 41	500	
CA8												
52155	10CA8/CL/2.5M/E12/130V/STD	10	E12	130	Clear	2500	C-7A	65	3.5 89	1.6 41	500	
52157	10CA8/F/2.5M/E12/130V/STD	10	E12	130	Frost	2500	C-7A	65	3.5 89	1.6 41	500	
50641	15CA8/CL/2.5M/E12/130V/STD	15	E12	130	Clear	2500	C-7A	90	3.6 91	1.8 45	500	
10269	15CA8/F/2.5M/E12/130V/STD	15	E12	130	Frost	2500	C-7A	88	3.6 91	1.8 45	120	
52156	25CA8/CL/2.5M/E12/130V/STD	25	E12	130	Clear	2500	C-7A	155	3.5 89	1.6 41	120	
50643	25CA8/F/2.5M/E12/130V/STD	25	E12	130	Frost	2500	C-7A	150	3.6 91	1.8 45	500	
50642	40CA8/CL/2.5M/E12/130V/STD	40	E12	130	Clear	2500	C-7A	280	3.6 91	1.8 45	500	
50644	40CA8/F/2.5M/E12/130V/STD	40	E12	130	Frost	2500	C-7A	280	3.6 91	1.8 45	500	
CA10												
50615	25CA10/CL/3M/E12/130V/STD	25	E12	130	Clear	3000	CC-2V	180	4.1 104	1.9 47	500	
50618	25CA10/F/3M/E12/130V/STD	25	E12	130	Frost	3000	CC-2V	150	4.1 104	1.9 47	500	
51051	25CA10/CL/3M/130V/STD	25	E26	130	Clear	3000	C-7A	155	3.9 99	2.1 54	120	

¹This product is no longer manufactured as per Energy Efficiency Regulations, note that it will remain available until stock is depleted.