



LED Reflector

Allowing you to focus light where it matters, these LED reflectors will not let your colours fade. Choose from many sizes, colour temperatures and beam distributions to create the perfect lighting with consistent lamp to lamp colour.

Reduce energy consumption and protect all goods and materials that are sensitive to heat and UV emissions.

STANDARD's LED reflectors are ideal for tracks, recessed luminaires and accent lighting in residential, retail, hospitality and commercial applications.



MR11



MR16



GU10

Order code	Description	Watts (W)	Base	Volts (VAC)	Colour temp. (K)	CRI	Life L70 (hrs)	Lumen output (lm)	Beam angle (°)	CBCP (cd)	Traditional equivalent (W)	Case qty (master)
MR11												
64244 ¹	LED/MR11/4W/30K/38/GU4/ND/STD	4	GU4	12	3 000	80	25 000	260	38	550	30	48
MR16												
64423	LED/MR16/6.5W/27K/25/STD	6.5	GU5.3	12	2 700	81	40 000	589	25	2 534	50	24
64007	LED/MR16/6.5W/27K/38/STD	6.5	GU5.3	12	2 700	81	40 000	599	38	1 307	50	24
63094	LED/MR16/7W/30K/25/STD	7	GU5.3	12	3 000	80	40 000	500	25	2 507	50	24
64008	LED/MR16/6.5W/30K/38/STD	6.5	GU5.3	12	3 000	83	40 000	595	38	1 213	50	24
64425	LED/MR16/6.5W/40K/25/STD	6.5	GU5.3	12	4 000	83	40 000	646	25	2 456	50	24
64009	LED/MR16/6.5W/40K/38/STD	6.5	GU5.3	12	4 000	83	40 000	667	38	1 326	50	24
64010	LED/MR16/6.5W/50K/38/STD	6.5	GU5.3	12	5 000	84	40 000	655	38	1 312	50	24
GU10												
63994	LED/GU10/5W/30K/38/STD/GRY	5	GU10	120	3 000	83	40 000	452	38	937	35	24
64415	LED/GU10/6.5W/27K/25/STD	6.5	GU10	120	2 700	82	40 000	558	25	2 451	50	24
63998	LED/GU10/6.5W/27K/38/STD	6.5	GU10	120	2 700	81	40 000	569	38	1 195	50	24
64416	LED/GU10/6.5W/30K/25/STD	6.5	GU10	120	3 000	83	40 000	574	25	2 504	50	24
64000	LED/GU10/6.5W/30K/38/STD	6.5	GU10	120	3 000	82	40 000	582	38	1 242	50	24
63999	LED/GU10/6.5W/30K/38/STD/GRY	6.5	GU10	120	3 000	82	40 000	582	38	1 242	50	24
64417	LED/GU10/6.5W/40K/25/STD	6.5	GU10	120	4 000	84	40 000	622	25	2 467	50	24
64001	LED/GU10/6.5W/40K/38/STD	6.5	GU10	120	4 000	83	40 000	635	38	1 298	50	24
64002	LED/GU10/6.5W/50K/38/STD	6.5	GU10	120	5 000	84	40 000	633	38	1 322	50	24



DAMP



DIMMABLE



3 YEARS WARRANTY



5 YEARS WARRANTY



UL US



ETL US



ENERGY STAR

Intertek

Lumen values are derived from photometric testing.
For a complete list of compatible dimmers and ENERGY STAR qualified products, please visit www.standardpro.com



PAR16



PAR20




PAR30SN



PAR30LN

Order code	Description	Watts (W)	Base	Volts (VAC)	Colour temp. (K)	CRI	Life L70 (hrs)	Lumen output (lm)	Beam angle (°)	CBCP (cd)	Traditional equivalent (W)	Case qty (master)
PAR16												
63990	LED/P16/6.5W/30K/38/STD	6.5	E26	120	3 000	82	40 000	582	38	1 242	50	24
63991	LED/P16/6.5W/40K/38/STD	6.5	E26	120	4 000	83	40 000	635	38	1 298	50	24
PAR20												
63950	LED/P20/7W/27K/25/STD	7	E26	120	2 700	92	40 000	509	25	1 497	50	12
63951	LED/P20/7W/27K/40/STD	7	E26	120	2 700	92	40 000	509	40	936	50	12
63952	LED/P20/7W/30K/25/STD	7	E26	120	3 000	93	40 000	502	25	1 411	50	12
63953	LED/P20/7W/30K/25/STD/BLK	7	E26	120	3 000	93	40 000	502	25	1 411	50	12
63954	LED/P20/7W/30K/25/STD/GRY	7	E26	120	3 000	93	40 000	502	25	1 411	50	12
63955	LED/P20/7W/30K/40/STD	7	E26	120	3 000	93	40 000	502	40	918	50	12
63956	LED/P20/7W/40K/25/STD	7	E26	120	4 000	94	40 000	551	25	1 533	50	12
63957	LED/P20/7W/40K/40/STD	7	E26	120	4 000	94	40 000	551	40	1 077	50	12
63958	LED/P20/7W/50K/25/STD	7	E26	120	5 000	95	40 000	523	25	1 451	50	12
63959	LED/P20/7W/50K/40/STD	7	E26	120	5 000	95	40 000	523	40	1 027	50	12
PAR30SN												
63968	LED/P30S/10W/27K/25/STD	10	E26	120	2 700	92	40 000	849	25	2 328	75	6
63969	LED/P30S/10W/27K/40/STD	10	E26	120	2 700	92	40 000	849	40	1 476	75	6
63970	LED/P30S/10W/30K/25/STD	10	E26	120	3 000	94	40 000	830	25	2 174	75	6
63971	LED/P30S/10W/30K/25/STD/BLK	10	E26	120	3 000	94	40 000	830	25	2 174	75	6
63972	LED/P30S/10W/30K/40/STD	10	E26	120	3 000	94	40 000	830	40	1 505	75	6
63973	LED/P30S/10W/40K/25/STD	10	E26	120	4 000	94	40 000	904	25	2 587	75	6
63974	LED/P30S/10W/40K/40/STD	10	E26	120	4 000	94	40 000	904	40	1 648	75	6
63975	LED/P30S/10W/50K/25/STD	10	E26	120	5 000	96	40 000	865	25	2 477	75	6
63976	LED/P30S/10W/50K/40/STD	10	E26	120	5 000	96	40 000	865	40	1 607	75	6
PAR30LN												
63960	LED/P30L/10W/27K/25/STD	10	E26	120	2 700	92	40 000	839	25	2 144	75	6
63961	LED/P30L/10W/27K/40/STD	10	E26	120	2 700	92	40 000	839	40	1 492	75	6
63962	LED/P30L/10W/30K/25/STD	10	E26	120	3 000	94	40 000	848	25	2 165	75	6
63963	LED/P30L/10W/30K/40/STD	10	E26	120	3 000	94	40 000	848	40	1 482	75	6
63964	LED/P30L/10W/40K/25/STD	10	E26	120	4 000	94	40 000	929	25	2 438	75	6
63965	LED/P30L/10W/40K/40/STD	10	E26	120	4 000	94	40 000	929	40	1 655	75	6
63966	LED/P30L/10W/50K/25/STD	10	E26	120	5 000	96	40 000	861	25	2 424	75	6
63967	LED/P30L/10W/50K/40/STD	10	E26	120	5 000	96	40 000	861	40	1 481	75	6



Order code	Description	Watts (W)	Base	Volts (VAC)	Colour temp. (K)	CRI	Life L70 (hrs)	Lumen output (lm)	Beam angle (°)	CBCP (cd)	Traditional equivalent (W)	Case qty (inner/master)
PAR38												
63977	LED/P38/15W/27K/25/STD	15	E26	120	2 700	92	40 000	1 138	25	3 278	100	1/6
63978	LED/P38/15W/27K/40/STD	15	E26	120	2 700	92	40 000	1 138	40	1 953	100	1/6
63979	LED/P38/15W/30K/25/STD	15	E26	120	3 000	94	40 000	1 115	25	3 445	100	1/6
63980	LED/P38/15W/30K/40/STD	15	E26	120	3 000	94	40 000	1 115	40	1 815	100	1/6
63981	LED/P38/15W/40K/25/STD	15	E26	120	4 000	94	40 000	1 215	25	3 807	100	1/6
63982	LED/P38/15W/40K/40/STD	15	E26	120	4 000	94	40 000	1 215	40	1 989	100	1/6
63983	LED/P38/15W/50K/25/STD	15	E26	120	5 000	96	40 000	1 172	25	3 837	100	1/6
63984	LED/P38/15W/50K/40/STD	15	E26	120	5 000	96	40 000	1 172	40	1 913	100	1/6
R20												
64964 ¹	LED/R20/S2/6.5W/27K/STD	6.5	E26	120	2 700	83	25 000	525	107	180	50	6/24
BR30												
64965 ¹	LED/BR30/S2/8W/27K/STD	8	E26	120	2 700	84	25 000	650	105	220	65	6/24
64966 ¹	LED/BR30/S2/8W/40K/STD	8	E26	120	4 000	82	25 000	700	105	240	65	6/24
BR40												
66032 ¹	LED/BR40/S2/16.5W/27K/STD	16.5	E26	120	2 700	82	25 000	1 252	103	445	85	6/24



DAMP



DIMMABLE



3 YEARS WARRANTY



5 YEARS WARRANTY



UL US



ENERGY STAR

Lumen values are derived from photometric testing.
For a complete list of compatible dimmers and ENERGY STAR qualified products, please visit www.standardpro.com