

INFINITY


BATTERY

IT7.2-6

RECHARGEABLE SEALED LEAD ACID (VRLA) BATTERY

Nominal Voltage **6 Volt**

20 Hour Rate Capacity **7.2 Ah**



Dimensions	Inches	mm
Length	5.94	151
Width	1.34	34
Case Height	3.74	95
Terminal Height	3.91	99

Weight (Approx.)	Lbs.	Kg
	2.87	1.30

Constant Current Discharge Characteristics at 77.0°F (25°C)

Case Material A.B.S. (UL94-HB)

Terminal Faston Type 187 (F1)

Maximum Short Duration Discharge Current	
(5 Seconds or Less)	108 Amperes
(10 Seconds or Less)	72 Amperes
(60 Seconds or Less)	43.2 Amperes

Internal Resistance (Fully Charged Battery)
(Approximately) 11 mOhm


Energy Density (@ 20 Hour Rate)
1.25 Watt-Hours/Cubic Inch (76.42 Watt-Hours/Litre)

Specific Energy (@ 20 Hour Rate)
14.96 Watt-Hours / Pound (32.98 Watt-Hours / Kg)

Operating Temperature Range	
Discharge	5°F (-15°C) ~ 122°F (50°C)
Recharge	32°F (0°C) ~ 104°F (40°C)
Storage	32°F (0°C) ~ 104°F (40°C)

Self Discharge Rate
About 3% / Month @ 68~77°F (20~25°C)

Discharge Time	Discharge Amperes	Capacity in Ah's	Final Voltage	Discharge C-Rate
20.0 Hrs	0.36	7.20	5.25	0.05
9.2 Hrs	0.72	6.62	5.25	0.10
5.0 Hrs	1.22	6.10	5.15	0.17
4.1 Hrs	1.44	5.99	5.10	0.20
2.1 Hrs	2.52	5.29	4.97	0.35
64.0 Mins	4.32	4.61	4.77	0.6
32.5 Mins	7.20	3.90	4.50	1.0
7.2 Mins	21.6	2.59	3.00	3.0



Recharge Method : Connect battery to a Current Limited, Constant Voltage Source.

- Limit the Initial Recharge Current to 1.8 Amperes or less.
- To promote satisfactory performance in Cyclic Applications, an initial Recharge Current of 720 mA is recommended.
- Employ Charge Voltage Temperature Compensation when Battery Temperature is less than 50°F (10°C) or greater than 86°F (30°C). Use the **Recommended** Voltage and Normalize to 68°F (20°C).
- The use of Compensation through the whole Temperature range is not generally necessary, but doing so may optimize Service Life.
- If the **Recommended** Recharge voltage is used, no Temperature Compensation is required within the range of 50~86°F (10~30°C).

Cyclic Application Recharge Voltage (68°F / 20°C)

Minimum	Recommended	Maximum	Volts D.C. Per Cell
7.20	7.28	7.35	
2.40	2.425	2.45	Temperature Coefficient: -2.8mV / °F / Cell (- 5mV / °C / Cell)

Standby Application Recharge Voltage (68°F / 20°C)

Minimum	Recommended	Maximum	Volts D.C. Per Cell
6.75	6.83	6.90	
2.25	2.275	2.30	Temperature Coefficient: -1.7mV / °F / Cell (- 3mV / °C / Cell)