

# INFINITY

## BATTERY

# IT26-12

RECHARGEABLE SEALED LEAD ACID (VRLA) BATTERY



**Nominal Voltage** 12 Volt

**20 Hour Rate Capacity** 26 Ah

Dimensions	Inches	mm
Length	6.54	166
Width	6.89	175
Case Height	4.92	125
Terminal Height	4.92	125

Weight (Approx.)	Lbs.	Kg
	20.75	9.41

**Case Material** A.B.S. (UL94-HB)

**Terminal** NUT & BOLT (M5)

Maximum Short Duration Discharge Current	
(5 Seconds or Less)	390 Amperes
(10 Seconds or Less)	260 Amperes
(60 Seconds or Less)	156 Amperes

**Internal Resistance** (Fully Charged Battery)  
(Approximately) 8 mOhm

**Energy Density (@ 20 Hour Rate)**  
1.41 Watt-Hours/Cubic Inch (85.92 Watt-Hours/Litre)


**Specific Energy (@ 20 Hour Rate)**  
15.04 Watt-Hours / Pound (33.15 Watt-Hours / Kg)

Operating Temperature Range	
<b>Discharge</b>	5°F (-15°C) ~ 122°F (50°C)
<b>Recharge</b>	32°F (0°C) ~ 104°F (40°C)
<b>Storage</b>	32°F (0°C) ~ 104°F (40°C)

**Self Discharge Rate**  
About 3% / Month @ 68~77°F (20~25°C)

Constant Current Discharge Characteristics at 73.4°F (23°C)

Discharge Time	Discharge Amperes	Capacity in Ah's	Final Voltage	Discharge C-Rate
20.0 Hrs	1.30	26.00	10.50	0.05
9.2 Hrs	2.60	24.05	10.50	0.10
5.0 Hrs	4.42	22.03	10.29	0.17
4.1 Hrs	5.20	21.17	10.20	0.20
2.1 Hrs	9.10	19.37	9.94	0.35
64.0 Mins	15.6	16.64	9.54	0.6
32.5 Mins	26	14.06	9.00	1.0
7.2 Mins	78	9.33	6.00	3.0



**Recharge Method :** Connect battery to a Current Limited, Constant Voltage Source.

- Limit the Initial Recharge Current to 6.5 Amperes or less.
- To promote satisfactory performance in Cyclic Applications, a minimum Recharge Current of 2.6 Amperes is recommended.
- Employ Charge Voltage Temperature Compensation when Battery Temperature is less than 50°F (10°C) or greater than 86°F (30°C). Use the **Recommended** Voltage and Normalize to 77°F (25°C).
- The use of Compensation through the whole Temperature range is not generally necessary, but doing so may optimize Service Life.
- If the **Recommended** Recharge voltage is used, no Temperature Compensation is required within the range of 50~86°F (10~30°C).

**Cyclic Application Recharge Voltage (77°F / 25°C)**

Minimum	Recommended	Maximum	Volts D.C. Per Cell
14.40	14.55	14.70	
2.40	2.425	2.45	

Temperature Coefficient: -2.8mV / °F / Cell (- 5mV / °C / Cell)

**Standby Application Recharge Voltage (77°F / 25°C)**

Minimum	Recommended	Maximum	Volts D.C. Per Cell
13.50	13.65	13.80	
2.25	2.275	2.30	

Temperature Coefficient: -1.7mV / °F / Cell (- 3mV / °C / Cell)