



Representative

Catalog Number: FBD24-1
Product ID: 7TAA014910R0070
UPC Number: 78378643365
Status: Active

Flexible Braids for Grounding, 76800 Circular Mil Area, Bolt Hole 7/16, 24 inch length, Number of Braids in Ferrule 1, 1 Bolt Hole per Ferrule

North American Specifications (UNSPSC)

UNSPSC	39121465 Flexible braid
IGCC	4695 Flexible braid
Brand Name	Blackburn
Type	Flexible Braid
Special Features	Tin-Plated Copper Braids and Ferrules for High Conductivity and Corrosion Resistance. Enables Linear Expansion, Equipment Vibration and Offset Connections.
Application	For Use in Substation and Grounding Applications
Standard	UL E3060, CSA LR29625
Conductor Material	Tin-Plated Copper
Nominal Cross Section Conductor	76800 Circular Mills
Cable Width	1.00 inch
Cable Length	24 inches
Conductor Category	Flexible
Shape Of Conductor	Flat

European Specifications (ETIM)

ETIM	EC000839 Braid wire
Conductor material	Cu, tinned
Conductor category	Class 5 = flexible
Shape of conductor	Flat
Cable height approx.	610mm

Packaging

Outer Quantity	25
Outer Dimensions (inches)	24x5.25x5.375
Weight Uom	60 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com