

Q-BIT: DRYWALL HOLE CUTTER

The Q-Bit is a revolutionary hole cutter that allows you to quickly cut out device holes. The Q-Bit is built to work with any standard oscillating tool

- Part#'s**
 42700 – Single Gang Box 2 3/8" x 3 3/4"
 42710 – Single Gang Line Voltage Box 2 1/8" x 3 5/16"
 42720 – 2 Gang Low Voltage Box 3 3/4" x 4"
 42740 – Single Gang Low Voltage Mud Ring 2 1/4" x 3 5/8"

NEW SIZES AVAILABLE!



- Part# 40905 - 1/2" thread**
40907 - 3/4" thread
40910 - 1" thread

PIPE SPINNER

Wrap a 10 foot pipe in 10 – 20 seconds!
 The Pipe Spinner allows you to speed up the process of taping IMC, galvanized conduit or black iron conduit in mil tape for underground applications. Instead of taping the pipe by hand, simply attach The Pipe Spinner to your drill and have your co-worker hold the tape while you spin the pipe.

- FEATURES:**
 3/4" drill attachment for quick change drills
 Available in 3 sizes: 1/2", 3/4" and 1"
 Saves time and money



THE GUIDE-O

The Guide-O allows you to enlarge holes utilizing a pilot bit the same size as the existing hole. By using a pilot bit that matches up to the existing hole, the hole cutter will stay centered while drilling the new, larger hole.



- FEATURES:**
 - Fits most standard carbide and bi-metal hole cutters
 - Kit includes 1/2", 3/4" and 1" pilot bits
 - Made from carbon steel
 *Hole Cutter not included

- Part#'s**
 94050 - 1/2"
 94075 - 3/4"
 94100 - 1"
 94200 – Guide-O Kit (1/2", 3/4", 1")
 94225 – 2 1/2" Shaft Replacement
 94226 – 2" Shaft Replacement
 94050B – 1/2" Bi-Metal
 94075B – 3/4" Bi-Metal
 94100B – 1" Bi-Metal
 94200B – Guide-O Bi-Metal Kit (1/2", 3/4", 1")

SEE IT IN ACTION



JAVELIN

ALL IN ONE DRILLING EXTENSION

The Javelin is here to change the way we drill holes. Never get caught in a drilling extension jam again! This all-in-one extension drill can reach up to 10 feet. It comes with a fully adjustable hole cutter and auger bit extension kit. Just cut a 3/8" - 16 threaded rod to any length you need.

- FEATURES:**
 - Holds drivers bits
 - Holds nut drivers
 - Holds drill bits
 - Reaches up to 10 feet long



Part# 95000



High Performance CARBIDE TIPPED STEEL CUTTERS

- Part#'s**
 92HC4 – Steel Cutters 7/8"
 92HC8 – Steel Cutters 1 1/8"
 92HC14 – Steel Cutters 1 3/8"
 92HC20 – Steel Cutters 1 3/4"
 92HC22 – Steel Cutters 2"
 92HC24 – Steel Cutters 2 1/2"
 92KIT4 - 4-Pc Set: 7/8", 1-1/8", 1-3/8", extra pilot bit
 92KIT8 - 8-Pc Set: 7/8", 1-1/8", 1-3/8", 1-3/4", 2", 2-1/2", 2 extra pilot bits

- FEATURES**
 - Ejector spring
 - Tapered center drill
 - Carbide tipping allows for repeated regrinding



MULTI BIT: STEP DRILLS

Hardened stepped bits for clean cuts in sheet metal, electrical boxes, arborite, etc. Handy for creating knockouts. Made from high grade cobalt.

- Part# MLT1 - Size: 1/8" - 1/2" 13 Step**
Part# MLT3 - Size: 1/4" - 3/4" 9 Step
Part# MLT4 - Size: 3/16" - 7/8" 12 Step
Part# MLT5 - Size: 7/16" - 1 1/8" 12 Step
Part# MLT7 - Size: 1/4" - 1 1/2" 11 Step

