


GE PowerMark Loadcentres



Single Phase

Single phase 30-225A

Main breaker 22KAIC rated standard - factory installed

All Loadcentres Top or Bottom Entry

Indoor and outdoor rated enclosures available

Copper bus standard

Includes Door Kits

Suitable for use as service entrance equipment when installed in accordance with the CEC



imagination at work

www.ge-ed.ca
www.geindustrial.com
1-800-GE-1STOP

GE Loadcentres

120/240 V - Single Phase

Main Breaker - 22KA MAIN BREAKER AND DOOR / THQP & THQL

AMPS (MB)	Catalogue Number Indoor Enclosure	Catalogue Number Type 3R Enclosure	Maximum Circuits				Total 1-Pole Spaces
			1" THQL		1/2" THQP		
			1P	2P	1P	2P	
100	TMC1210CCA	TMC1210RCA	12	6	24	10	24
100	TMC1610CCA		16	8	32	14	32
100	TMC2010CCA		20	10	40	18	40
100	TMC2410CCA		24	12	48	22	48
100	TMC3210CCA		32	16	64	20	64
125	TMC2012CCA		20	10	40	18	40
125	TMC1612CCA		16	8	32	14	32
125	TMC2412CCA		24	12	48	22	48
125	TMC3212CCA		32	16	64	20	64
150	TMC2015CCA		20	10	40	18	40
150	TMC2415CCA		24	12	48	22	48
150	TMC3215CCA		32	16	64	30	64
150	TMC4015CCA		40	20	80	38	80
200	TMC2020CCA	TMC2020RCA	20	10	40	18	40
200	TMC3220CCA		32	16	64	30	64
200	TMC4020CCA		40	20	80	38	80



imagination at work

www.ge-ed.ca
www.geindustrial.com
1-800-GE-1STOP

GE Loadcentres

120/240 V - Single Phase

Main Lug

AMPS (ML)	Catalogue Number Indoor Enclosure	Catalogue Number Type 3R Enclosure	Maximum Circuits				Total 1-Pole Spaces
			1" THQL		1/2" THQP		
			1P	2P	1P	2P	
40	TLC240SCU	TLC240RCU	2	1	4	1	4
70	TLC270SCU	TLC270RCU	2	1	4	1	4
100	TLC410C	TLC410R ¹	4	2	8	3	8
100	TPLC410C ¹	TPLC410R ¹	4	2	8	3	8
125	TLC612SCU/FCU ²		6	3	8	3	8
125	TLC612SCUD/FCUD ^{2 3}		6	3	12	4	12
125	TLC812SCU/FCU ²	TLC812RCU	8	4	12	4	12
125	TLC812SCUD/FCUD ^{2 3}		8	4	16	6	16
125	TLC1212CCA	TLC1212RCA	12	6	24	10	24
125	TLC1612CCA		16	8	32	14	32
125	TLC2412CCA	TLC2412RCA	24	12	48	22	48
200	TLC1620CCA		16	8	32	16	32
200	TLC2020CCA	TLC2020RCA	20	10	40	18	40
200	TLC3220CCA		32	16	64	30	64
200	TLC4020CCA	TLC4020RCA	40	20	80	38	80
225	TLC4222CCA ⁴	TLC4020RCA	42	20			42

¹ Thermoplastic Enclosure.

² SCU indicates surface mount enclosure. FCU indicates flush mount enclosure.

³ Includes optional door.


⁴ Accepts 1" THQL breakers only



imagination at work

www.ge-ed.ca
www.geindustrial.com
1-800-GE-1STOP

GE PowerMark Loadcentres



Three phase 100-225A

All Loadcentres Top or Bottom Entry

Indoor and outdoor rated enclosures available

Indoor fronts surface or flush

Copper bus standard

Includes Door Kits

Exclusive life time warranty

Suitable for use as service entrance equipment
when installed in accordance with the CEC



imagination at work

www.ge-ed.ca
www.geindustrial.com
1-800-GE-1STOP

GE Loadcentres

120/208 V - Three Phase

Main Breaker

AMPS (MB)	Catalogue Number Indoor Enclosure	Catalogue Number Type 3R Enclosure	Maximum Circuits			Total 1-Pole Spaces
			1" THQL			
			1P	2P	3P	
100	TMC12410C		12	6	4	12
100	TMC18410C		18	8	6	18
125	TMC30412C		30	14	10	30
200	TMC42420C	TMC42420R	42	20	14	42

3ph 120/208V loadcentre only accepts 1" THQL style brks.



imagination at work

www.ge-ed.ca
www.geindustrial.com
1-800-GE-1STOP

GE Loadcentres

120/208 V - Three Phase

Main Lug

AMPS (ML)	Catalogue Num- ber Indoor Enclo- sure	Catalogue Number Type 3R Enclosure	Maximum Circuits			Total 1-Pole Spaces
			1" THQL			
			1P	2P	3P	
125	TLC12412C	TLC12412R	12	6	4	12
150	TLC18415C		18	8	6	18
150	TLC24415C	TLC24415R	24	12	8	24
200	TLC18420C		18	8	6	18
200	TLC30420C	TLC30420R	30	14	10	30
200	TLC42420C	TLC42420R	42	20	14	42
225	TLC30422C		30	14	10	30
225	TLC42422C		42	20	14	42

3ph 120/208V loadcentre only accept 1" THQL style brks.



imagination at work

www.ge-ed.ca
www.geindustrial.com
1-800-GE-1STOP

GE Loadcentres

Breakers & Accessories

	1 POLE	2 POLE	1 POLE	2 POLE	3 POLE
AMPS	1/2" THQP (fits single phase only)		1" THQL		
15	THQP115	THQP215	THQL1115	THQL2115	THQL32015
20	THQP120	THQP220	THQL1120	THQL2120	THQL32020
30	THQP130	THQP230	THQL1130	THQL2130	THQL32030
40	THQP140	THQP240	THQL1140	THQL2140	THQL32040
50	THQP150	THQP250	THQL1150	THQL2150	THQL32050
60				THQL21060	THQL32060
70				THQL21070	THQL32070
80				THQL21080	THQL32080
90				THQL21090	THQL32090
100				THQL21100	THQL32100
15 Arc Fault			THQL1115AF	THQL2115AF	
15 GFI			THQL1115GF	THQL2115GF	
SUB-FEED & FEED THRU LUGS					
125				THLK2125	THLK3125
150				THLK2150	
200				THLK2200	
225					THLK3225

- Panel Filler 1/2" TFH/ 1" TQLFP1
- Door Replacement screw kit THRWKIT



imagination at work

www.ge-ed.ca
www.geindustrial.com
 1-800-GE-1STOP

GE Loadcentres

CATALOGUE #	DESCRIPTION
-------------	-------------

'1K' Loadcentre Kits 120/240 V - Single Phase

EEMAC 1 c/w 22kA Main Breaker, Door, and 1/2" Breakers: 10-1p15A, 3-2p15A, 1-2p30A, 1-2p40A

TMC1210CCA1K	100A 12/24 CCT
TMC1610CCA1K	100A 16/32 CCT
TMC2410CCA1K	100A 24/48 CCT
TMC3210CCA1K	100A 32/64 CCT
TMC2412CCA1K	125A 24/48 CCT
TMC3215CCA1K	150A 32/64 CCT
TMC2020CCA1K	200A 20/40 CCT
TMC3220CCA1K	200A 32/64 CCT
TMC4020CCA1K	200A 40/80 CCT

'2K' Loadcentre Kits 120/240 V - Single Phase

EEMAC 1 c/w 22kA Main Breaker, Door, and 1" Breakers: 10-1p15A, 3-2p15A, 1-2p30A, 1-2p40A

TMC2410CCA2K	100A 24/48 CCT
TMC3210CCA2K	100A 32/64 CCT
TMC3220CCA2K	200A 32/64 CCT
TMC4220CCA2K	200A 40/80 CCT



imagination at work

www.ge-ed.ca
www.geindustrial.com
1-800-GE-1STOP

GE Loadcentres

CATALOGUE #	DESCRIPTION
-------------	-------------

'3K' Loadcentre Kits 120/240V Single Phase

EEMAC 1 c/w 22kA Main Breaker, Door, and 1/2" Breakers: 14-1p15A, 2-2p15A, 3-2p20A, 2-2p30A, 1-2P40A

TMC4015CCA3K	150A 40/80 CCT
TMC4020CCA3K	200A 40/80 CCT

'4K' Loadcentre Kits 120/240V Single Phase

EEMAC 1c/w 22kA Main Breaker, Door, and 1" Breakers: 14-1p15A, 2-2p15A, 3-2p20A, 2-2p30A, 1-2P40A

TMC4020CCA4K	150A 40/80 CCT
--------------	----------------

Outdoor '3R' 120/240V Single Phase Main Breaker Loadcentres

EEMAC 3R c/w 22kA Main Breaker and Door:

TMC121ORCA	100A 12/24 CCT
TMC202ORCA	200A 20/40 CCT

120/240V Single Phase Main LUG ONLY Loadcentres

EEMAC 1 c/w Door:

TLC240SCU *	40A 2/4 CCT
TLC270SCU *	70A 2/4 CCT
TLC410C	100A 4/8 CCT
TPLC410C	100A 8/14 CCT
TLC612SCU/FCU *	125A 6/12 CCT
TLC612SCUD/FCUD **	100A 6/12 CCT
TLC812SCU/FCU *	100A 8/16 CCT
TLC812SCUD/FCUD **	100A 8/16 CCT
TLC1212CCA	125A 12/24 CCT
TLC1612CCA	125A 16/32 CCT
TLC2412CCA	125A 24/48 CCT
TLC1620CCA	200A 16/32 CCT
TLC2020CCA	200A 20/40 CCT
TLC3220CCA	200A 32/64 CCT
TLC4020CCA	200A 40/80 CCT
TLC4222CCA	225A 42 CCT 1" ONLY BREAKERS

* Door not included

** Add Suffix S/SCUD or F/FCUD for Surface/Flush Trim Style



imagination at work

www.ge-ed.ca
www.geindustrial.com
1-800-GE-1STOP

GE Loadcentres

CATALOGUE #	DESCRIPTION
-------------	-------------

Outdoor 120/240V Single Phase Main LUG ONLY Loadcentres

EEMAC 3R Enclosure

TLC240RCU	40A 2/4 CCT
TLC270RCU	70A 2/4 CCT
TLC410R1	125A 4/8 CCT
TPLC410R	125A 4/8 CCT
TLC812RCU	125A 8/16 CCT
TLC1212RCA	125A 12/24 CCT
TLC2412RCA	125A 24/48 CCT
TLC4020RCA	200A 40/80 CCT

120/208V Three Phase Main Breaker Loadcentres

EEMAC 1 c/w 22kA Main Breaker and Door, 1" Breakers Only

TMC12410C	100A 12 CCT
TMC18410C	100A 18 CCT
TMC30410C	100A 30 CCT
TMC42420C	200A 42 CCT

120/208V Three Phase Main LUG ONLY Loadcentres

EEMAC 1 c/w Door, 1" Breakers Only

TLC12412C	125A 12 CCT
TLC18415C	150A 18 CCT
TLC24415C	150A 24 CCT
TLC18420C	200A 18 CCT
TLC30420C	200A 30 CCT
TLC42420C	200A 42 CCT
TLC30422C	225A 30 CCT
TLC42422C	225A 42 CCT



imagination at work

www.ge-ed.ca
www.geindustrial.com
1-800-GE-1STOP

GE Loadcentres

CATALOGUE #	DESCRIPTION
-------------	-------------

Outdoor 120/208V

Three Phase Main Breaker Loadcentres

EEMAC 3R c/w 22kA Main Breaker and Door, 1" Breakers Only

TMC18410R	100A 18 CCT
-----------	-------------

Outdoor 120/208V

Three Phase Main LUG ONLY Loadcentres

EEMAC 3R c/w Door, 1" Breakers Only

TLC12412R	125A 12 CCT
TLC24415R	150A 24 CCT
TLC30420R	200A 30 CCT
TLC42420R	200A 42 CCT

Branch Breakers

1/2" THQP Breakers for Single Phase Loadcentres Only

THQP115	1P 15A
THQP120	1P 20A
THQP130	1P 30A
THQP215	2P 15A
THQP220	2P 20A
THQP225	2P 25A
THQP230	2P 30A
THQP240	2P 40A
THQP250	2P 50A



THQL115 Breaker 15A
Plug-in 2 Pole



THQL215 Breaker 15A
Plug-in 2 Pole



imagination at work

www.ge-ed.ca
www.geindustrial.com
1-800-GE-1STOP

GE Loadcentres

CATALOGUE #	DESCRIPTION
-------------	-------------

Branch Breakers

1" THQL

THQL1115	1P 15A
THQL1120	1P 20A
THQL1130	1P 30A
THQL2115	2P 15A
THQL2120	2P 20A
THQL2125	2P 25A
THQL2130	2P 30A
THQL2140	2P 40A
THQL2150	2P 50A
THQL2160	2P 60A
THQL2170	2P 70A
THQL2180	2P 80A
THQL2190	2P 90A
THQL21100	2P 100A
THQL21125	2P 125A
THQL32015	3P 15A
THQL32020	3P 20A
THQL32025	3P 25A
THQL32030	3P 30A
THQL32040	3P 40A
THQL32050	3P 50A
THQL32060	3P 60A
THQL32070	3P 70A
THQL32090	3P 90A
THQL32100	3P 100A



imagination at work

www.ge-ed.ca
www.geindustrial.com
1-800-GE-1STOP

GE Loadcentres

CATALOGUE #	DESCRIPTION
-------------	-------------

Arc Fault Breakers

1" THQL

THQL1115AF	1P 15A AFCI
THQL1120AF	1P 20A AFCI

Ground Fault Breakers

1" THQL

THQL1115GF	1P 15A GFCI
THQL1120GF	1P 20A GFCI
THQL2115GF1	2P 15A GFCI
THQL2120GF1	2P 20A GFCI
THQL2130GF1	2P 30A GFCI
THQL2140GF1	2P 40A GFCI
THQL2150GF1	2P 50A GFCI

TVSS

THQLSURGE	2P Plug-In 27kA TVSS
THQLSURGE60	Side Mount Retro-Fit TVSS 60kA

Spa Panels

TL412R250GF	SPA Panel c/w 2P 50A GFCI
TL412R260GF	SPA Panel c/w 2P 60A GFCI

Generator Panels

NEMA 1 Enclosure

TM830FCUGEN	30A, 8 cct Panel, Flush Mount
TM830SCUGEN	30A, 8 cct Panel, Surface Mount
TM860FCUGEN	60A, 8 cct Panel, Flush Mount
TM860SCUGEN	60A, 8 cct Panel, Surface Mount

Generator Panels

NEMA 3R Enclosure

TM830RCUGEN	30A, 8 cct Panel
TM860RCUGEN	60A, 8 cct Panel



THQL115GF
Ground Fault Breaker



THQLSurge
Surge Protector



TL412R250GF
Spa Panel c/w 2P 50A GFCI



imagination at work

www.ge-ed.ca
www.geindustrial.com
1-800-GE-1STOP

GE Loadcentres

Canada Single Phase

Main Amp Rating	Load Center Cat. No.	Mod. No.	Front Cat. No
100	TMC1210CCA	M01	TMC12A
	TMC1210CCU	M01	TMC12A
	TMC1610CCA	M01	TMC16A
	TMC1610CCU	M01	TMC16A
	TMC2010CCA	M01	TMC20A
	TMC2010CCU	M01	TMC20A
	TMC2410CCA	M01	TMC24A
	TMC2410CCU	M01	TMC24A
	TMC3210CCA	M01	TMC32A
	TMC3210CCU	M01	TMC32A
125	TLC1212CCA	M01	TLC12A
	TLC1212CCU	M01	TLC12A
	TLC1612CCA	M01	TLC16A
	TLC1612CCU	M01	TLC16A
	TLC2412CCA	M01	TLC24A
	TLC2412CCU	M01	TLC24A
	TLC612FCU	M01	TLC6FC
	TLC612FCUD	M01	TLC8FCD
	TLC612SCU	M01	TLC6SC
	TLC612SCUD	M01	TLC6SCD
	TLC812FCU	M01	TLC8FC
	TLC812FCUD	M01	TLC8FCD
	TLC812SCU	M01	TLC8SCD
	TLC812SCUD	M01	TLC8SCD
	TMC1612CCA	M01	TMC16B
	TMC1612CCU	M01	TMC16B
	TMC2012CCA	M01	TMC20B
	TMC2012CCU	M01	TMC20B
	TMC2412CCA	M01	TMC24B
	TMC2412CCU	M01	TMC24B
150	TMC3212CCA	M01	TMC32B
	TMC3212CCU	M01	TMC32B
	TMC2015CCA	M06	TMC20CD
	TMC2015CCU	M01	TMC20C
	TMC2015CCU	M06	TMC20CD
	TMC2415CCA	M06	TMC24CD
	TMC2415CCU	M01	TMC24C
	TMC2415CCU	M06	TMC24CD
	TMC3215CCA	M06	TMC32CD
	TMC3215CCU	M01	TMC32C
	TMC3215CCU	M06	TMC32CD
	TMC4015CCA	M06	TMC40AD
200	TMC4015CCU	M01	TMC40A
	TMC4015CCU	M06	TMC40AD
	TLC1620CCA	M01	TLC16B
	TLC1620CCU	M01	TLC16B
	TLC2020CCA	M01	TLC20A
	TLC2020CCU	M01	TLC20A
	TLC3220CCA	M01	TLC32A
	TLC3220CCU	M01	TLC32A
	TLC4020CCA	M01	TLC40A
	TLC4020CCU	M01	TLC40A
	TMC2020CCA	M06	TMC20DD
	TMC2020CCU	M01	TMC20D
	TMC2020CCU	M06	TMC20DD
	TMC3220CCA	M06	TMC32DD
	TMC3220CCU	M01	TMC32D
	TMC3220CCU	M06	TMC32DD
	TMC4020CCA	M06	TMC40BD

Main Amp Rating	Load Center Cat. No.	Mod. No.	Front Cat. No
200	TMC4020CCU	M01	TMC40B
(continued)	TMC4020CCU	M06	TMC40BD
225	TLC4222CCA	M01	TLC42A
	TLC4222CCU	M01	TLC42A

Three Phase

Main Amp Rating	Load Center Cat. No.	Mod. No.	Front Cat. No
100	TMC12410C	M01	TMC124A
	TMC18410C	M01	TMC184A
125	TMC30412C	M01	TMC304A
150	TLC18415C	M01	TLC184A
	TLC24415C	M01	TLC244A
	TLC18420C	M01	TLC184B
	TLC30420C	M01	TLC304A
	TLC42420C	M01	TLC424A
200	TMC42420C	M01	TMC424A
	TLC30422C	M01	TLC304B
	TLC42422C	M01	TLC424B

International

Single Phase

Main Amp Rating	Load Center Cat. No.	Mod. No.	Front Cat. No
125	TLM1212CCUX2	M01	TLM12ACX
	TLM1612CCUX2	M01	TLM16ACX
	TLM2412CCUX2	M01	TLM2412
	TLM612FCUDX2	M01	TLM6FCD
	TLM612SCUDX2	M01	TLM6SCD
	TLM812FCUDX2	M01	TLM8FCD
	TLM812SCUDX2	M01	TLM8SCD
	TL1615CCUX2	M01	TL16CX
150	TL2015CCUX2	M01	TL20CX
200	TL2020CCUX2	M01	TL20ACX
	TL3220CCUX2	M01	TL32CX
	TL4020CCUX2	M01	TL40CX
225	TL4222CCUX2	M01	TL42DCX

Three Phase

Main Amp Rating	Load Center Cat. No.	Mod. No.	Front Cat. No
100	TM12410CBX2	M01	TM12CBX2
	TM12410CBX2	M01	TM12CBX2
	TM12410CX2	M02	TM12ACX
	TM12410CX2LB	M02	TM12ACX
	TM18410CX2	M02	TM18ACX
125	TL12412CX2	M02	TL12ACX
	TM30412CX2	M02	TM30BCX
150	TL18415CX2	M02	TL18ACX
	TL24415CX2	M02	TL24ACX
	TM24415CBX2	M02	TMB24BCX
	TM24415CBX2LB	M02	TMB24BCX
	TM24415CX2	M02	TM24BCX
	TM24415CX2LB	M02	TM24BCX
	TM30415CX2	M02	TM30BCX
	TM30415CX2LB	M02	TM30BCX
	TM42415CX2	M02	TM42DCX
	TL18420CX2	M02	TL18BCX
200	TL30420CX2	M02	TL30DCX
	TL42420CX2	M02	TL42BCX
	TM24420CX2	M02	TM24DCX
	TM24420CX2	M02	TM24DCX
	TM30420CX2	M02	TM30DCX
	TM42420CX2	M02	TM42ECX
	TM42420CX2	M02	TM42ECX
	TM42420CX2LB	M02	TM42ECX
	TL30422CX2	M01	TL30ACX
	TL42422CX2	M01	TL42ACX
225	TM42422CX2	M01	TM42BCX
	TM42422CX2	M01	TM42BCX

Most of the items in the shaded rows are obsolete. In addition to ordering the replacement front with the largest model number, order a new THQMV (KR main). The catalog number will be THQMVXXXD where XXX is the main breaker amp rating. Example: THQMV200D for a 200A main breaker.

GE
41 Woodford Avenue, Plainville, CT 06062
www.geelectrical.com
© 2008 General Electric Company





imagination at work

1 - 16




GE Loadcentres




TMC1210CCA1K
TMC1210CCA
TMC1270CCA
TMC1610CCA1K
TMC1610CCA
TMC1612CCA
TMC1670CCA
TLC1212CCA
TLC1612CCA



GE Loadcentres



TMC2010CCA
TMC2012CCA




SH3




imagination at work

www.ge-ed.ca
www.geindustrial.com
1-800-GE-1STOP

GE Loadcentres




GE Loadcentres



imagination at work

www.ge-ed.ca
www.geindustrial.com
 1-800-GE-1STOP



GE Loadcentres



imagination at work

www.ge-ed.ca
www.geindustrial.com
1-800-GE-1STOP

GE Loadcentres



SH7

- A - 9/32 K.O.
- B - 3/8 x 1/2 K.O.
- C - 1/2 x 3/4 K.O.
- D - 3/8 x 1/2 x 3/4 x 1 K.O.
- E - 1/2 x 3/4 x 1 x 1 1/4 x K.O.
- F - 1 x 1 1/4 x 1 1/2 x 2 K.O.
- G - 1 x 1 1/2 x 2 x 2 1/2 K.O.
- H - 3/4 x 1 x 1 1/4 x 1 1/2 x 2 x 2 1/2 K.O.
- J - 1/2 K.O.
- K - 3/4 K.O.



TMC2410CCA1K
TMC2410CCA2K
TMC2410CCA
TMC2412CCA1K
TMC2412CCA
TMC2470CCA
TLC2412CCA



imagination at work

www.ge-ed.ca
www.geindustrial.com
1-800-GE-1STOP

GE Loadcentres



TLC1620CCA



- A - 9/32 K.O.
- B - 3/8 x 1/2 K.O.
- C - 1/2 x 3/4 K.O.
- D - 3/8 x 1/2 x 3/4 x 1 K.O.
- E - 1/2 x 3/4 x 1 x 1 1/4 x K.O.
- F - 1 x 1 1/4 x 1 1/2 x 2 K.O.
- G - 1 x 1 1/2 x 2 x 2 1/2 K.O.
- H - 3/4 x 1 x 1 1/4 x 1 1/2 x 2 x 2 1/2 K.O.
- J - 1/2 K.O.



imagination at work

www.ge-ed.ca
www.geindustrial.com
 1-800-GE-1STOP

GE Loadcentres



SH9

- A - 9/32 K.O.
- B - 3/8 x 1/2 K.O.
- C - 1/2 x 3/4 K.O.
- D - 3/8 x 1/2 x 3/4 x 1 K.O.
- E - 1/2 x 3/4 x 1 x 1 1/4 x K.O.
- F - 1 x 1 1/4 x 1 1/2 x 2 K.O.
- G - 1 x 1 1/2 x 2 x 2 1/2 K.O.
- H - 3/4 x 1 x 1 1/4 x 1 1/2 x 2 x 2 1/2 K.O.
- J - 1/2 K.O.
- K - 3/4 K.O.


TMC2015CCA
TMC2020CCA1K
TMC2020CCA
TMC2415CCA
TLC2020CCA



imagination at work

www.ge-ed.ca
www.geindustrial.com
1-800-GE-1STOP

GE Loadcentres




imagination at work

www.ge-ed.ca
www.geindustrial.com
 1-800-GE-1STOP

www.ge-ed.ca
www.geindustrial.com
1-800-GE-1STOP




GE Loadcentres



imagination at work

www.ge-ed.ca
www.geindustrial.com
 1-800-GE-1STOP

GE Loadcentres



imagination at work

www.ge-ed.ca
www.geindustrial.com
 1-800-GE-1STOP