

# D4/8.SF.I.ADO

[Print View..](#)  
[Print to Pdf..](#)

## General Information

<b>Extended Product Type:</b>	D4/8.SF.I.ADO
<b>Product ID:</b>	1SNA399785R0300
<b>EAN:</b>	3472593997857
<b>Catalog Description:</b>	D4/8.SF.I.ADO IDC Terminal Blocks - For 5 x 20 and 5 x 25 fuses - with test socket ADO - screw clamp - Grey
<b>Long Description:</b>	D4/8.SF.I.ADO IDC Terminal Blocks - Fuse - Grey, 1.5mm <sup>2</sup> RatedCrossSection, 8mm Spacing TH 35-7.5, TH 35-15 Rail



## Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks » IDC Terminal Blocks

## Ordering

<b>EAN:</b>	3472593997857
<b>Minimum Order Quantity:</b>	50 piece
<b>Customs Tariff Number:</b>	85361010

## Dimensions

<b>Product Net Width:</b>	8.0 mm
<b>Product Net Height:</b>	68.2 mm
<b>Product Net Depth:</b>	40.9 mm
<b>Product Net Weight:</b>	13.00 g

## Container Information

<b>Package Level 1 Units:</b>	50 piece
<b>Package Level 1 Width:</b>	75 mm
<b>Package Level 1 Height:</b>	107 mm
<b>Package Level 1 Length:</b>	225 mm
<b>Package Level 1 Gross Weight:</b>	0.65000 kg
<b>Package Level 1 EAN:</b>	3472593997857
<b>Package Level 2 Units:</b>	700 piece
<b>Package Level 2 Width:</b>	300 mm
<b>Package Level 2 Height:</b>	300 mm
<b>Package Level 2 Length:</b>	500 mm
<b>Package Level 2 Gross Weight:</b>	9.6 kg
<b>Package Level 3 Units:</b>	16800 piece
<b>Product Packing Type:</b>	Box

## Environmental

<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment
---------------------	---

## Technical UL/CSA

<b>Connecting Capacity-Main Circuit UL/CSA:</b>	Screw Clamp / Flexible 1x 22-10 AWG
---	-------------------------------------

Flammability According to UL94: V0

---

### Additional Information

---

<b>Color:</b>	Grey
<b>Connecting Capacity-Main Circuit:</b>	Screw Clamp / Flexible 1x 0.22-4 mm <sup>2</sup> Screw Clamp / Rigid 1x 0.2-4 mm <sup>2</sup>
<b>Connection Type:</b>	Screw clamp - ADO System
<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
<b>Function:</b>	Fuse
<b>Gauge Type:</b>	A4
<b>IIT Publishing Status:</b>	Level 0 - Information enabled
<b>Mounting on DIN Rail:</b>	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
<b>Number of Levels:</b>	1
<b>Pollution Degree:</b>	3
<b>Product Main Type:</b>	D4/8.SF.I.ADO
<b>Product Name:</b>	Terminal block
<b>Rated Cross-Section:</b>	1.5 mm <sup>2</sup>
<b>Rated Current (I<sub>n</sub>):</b>	Main Circuit 6.3 A
<b>Rated Impulse Withstand Voltage (U<sub>imp</sub>):</b>	8000 V
<b>Rated Short-time Withstand Current (I<sub>cw</sub>):</b>	for 1.0s 180 A
<b>Rated Voltage (U<sub>r</sub>):</b>	630 V
<b>Recommended Screw Driver:</b>	4 mm
<b>Spacing:</b>	8 mm
<b>Sub-Function:</b>	for 5x20 and 5x25 Fuses
<b>Wire Stripping Length:</b>	9.5 mm

---

### Certificates and Declarations (Document Number)

---

<b>Declaration of Conformity - CE:</b>	1SND225014C1005
<b>GOST Certificate:</b>	1SND161005A1104
<b>RoHS Information:</b>	1SND230472F0201

---

### Classifications

---

<b>ETIM 4.0:</b>	EC000899 - Fuse terminal block
<b>ETIM 5.0:</b>	EC000899 - Fuse terminal block
<b>Object Classification Code:</b>	X

---