

# Technical Information Bulletin


## CHOICE LED Lamps



Date: \_\_\_\_\_ Name of distributor: \_\_\_\_\_  
 In hands date of project: \_\_\_\_\_ Client #: \_\_\_\_\_  
 Project name/Number: \_\_\_\_\_ Name of end user: \_\_\_\_\_

### ORDERING INFORMATION

Order code: 66296  
 Description: P30S/12W/40K/40/CHOICE/STD  
 UPC: 69549662964  
 Case quantity: 6



MOL : 3 3/4 in. (85mm) Dia. : 3 3/4 in. (95 mm)

### PERFORMANCE DATA

Shape: PAR30SN  
 Base: E26  
 Watts(W): 12  
 Volts (VAC): 120  
 Colour temperature (K)\*\*: 4 000  
 Life L70 (hrs): 15 000  
 Initial lumens (lm)\*: 977  
 Initial lumens per watt (lm/W): 81  
 CRI: 93  
 Beam angle (°): 40  
 CBCP: 1 740  
 Power factor: 0.93  
 Operating temperature range: -20 °C to 40 °C (-4 °F to 104 °F)  
 Traditional equivalent (W): 75

\*Initial lumens range: +/- 10 % \*\*Typical colour temperature range: +/- 10 %

### COMPATIBLE DIMMERS

Legrand	HCL453P, RH703PTUTC
Cooper	AAL06, DAL06P, SLC03P
Leviton	6615, 6674, DSL06-1LZ, DSM10-1LZ, IPE04-1LZ, IPL06
Lutron	AYCL-253P, CTCL-153P, DVCL-153P, DVCL-253P, DVELV-300P, MACL-153P, PD-6WCL, SELV-300P



### CAUTIONS

- Turn power off before inspection, installation, or removal.
- Risk of electrical shock – do not use where directly exposed to water or weather.
- Not for use in totally enclosed luminaires.
- Suitable for use in wet locations.
- Do not open – no user serviceable parts inside.
- Use only on 120 VAC, 60Hz circuits.
- This device is not intended for use with emergency exit fixtures or emergency exit lights.
- Compatible with most dimmers.
- For complete dimmer and warranty information visit [www.standardpro.com](http://www.standardpro.com).

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: \_\_\_\_\_  
 Company: \_\_\_\_\_  
 Signature: \_\_\_\_\_ Date: \_\_\_\_\_

This lighting equipment complies with Canadian standard ICES-005 for use in residential applications.  
 Data is based upon tests performed in a controlled environment and representative of relative performance.  
 Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.