

# PatchRunner™ 2 Vertical Cable Managers

## specifications

The vertical cable manager shall consist of a metal backbone with cable management fingers that align with EIA rack spacing. The fingers shall be molded out of plastic and provide integral bend radius control throughout the entire length. The backbone shall have pass through holes for front to back cabling, with the option to blank off with a plug. The manager shall accept a metal, hinged, push-to-close door that can open to the right or left. The door support brackets shall be integrated into the manager with no assembly required. The manager shall accept plastic slack management spools that can be repositioned as required. The vertical panel shall be able to manage all the cable on the rack without the aid of horizontal cable managers.



## key features and benefits

<b>NEW Improved door function</b>	“Push-to-close” door design allows for easy operation
<b>NEW Dual hinged doors are included</b>	Doors ship with managers, simplifying ordering process with less packaging waste
<b>NEW Integrated door brackets</b>	No brackets to install; faster installation while reducing labor costs
<b>NEW Color options</b>	Managers and doors are available in black and white
<b>NEW High Density with increased cable capacity</b>	Up to 17% more usable capacity over existing PRV Vertical Managers
<b>Curved fingers</b>	Support cables as they transition to vertical pathway eliminating need for horizontal managers
<b>Individual fingers</b>	Aligns with rack spaces to simplify cable routing changes
<b>Integral bend radius control</b>	Maintains cable bend radius ensuring network performance and system reliability
<b>Optional snap on vertical retainers</b>	Can be placed on fingers to help retain cables in channel for improved cable management and appearance
<b>Optional slack management spools</b>	Organize and manage patch cord slack allowing for standardization of patch cord lengths

## applications

PatchRunner™2 Vertical Cable Managers are designed to manage high-density networking equipment in, up to, half the area required by traditional cable management systems. Molded cable management fingers, with integral bend radius control, combine with Panduit angled patch panels to eliminate the need for horizontal cable managers. This frees up rack space for additional patch panels, active equipment, or cable pathways reducing the

number of racks that may be required for the network layout. The reduction in square footage combined with fewer components ordered, inventoried and installed results in significant cost savings for the network infrastructure. When used with Panduit connectivity, patch cords, and racks, the user receives a complete cable management solution that maximizes density while minimizing the area required for their network.

### Vertical Cable Managers w/doors – 6.5 foot

<b>Dual-sided with two doors:</b>	
6" wide:	PR2VD0679
12" wide:	PR2VD1279
<b>Dual-sided with one door:</b>	
6" wide:	PR2VSD0679
12" wide:	PR2VSD1279
<b>Single-sided with one door:</b>	
6" wide:	PR2VFD0679
12" wide:	PR2VFD1279

### Standard EIA Racks – 6.5 foot

2 post rack:	R2P79
4 post rack:	R4P79
4 post rack:	R4PCN79

### Vertical Cable Managers w/doors – 7 foot

<b>Dual-sided with two doors:</b>	
6" wide:	PR2VD06^A
8" wide:	PR2VD08^A
10" wide:	PR2VD10^A
12" wide:	PR2VD12^A
<b>Dual-sided with one door:</b>	
6" wide:	PR2VSD06^A
8" wide:	PR2VSD08^A
10" wide:	PR2VSD10^A
12" wide:	PR2VSD12^A
<b>Single-sided with one door:</b>	
6" wide:	PR2VFD06^A
8" wide:	PR2VFD08^A
10" wide:	PR2VFD10^A
12" wide:	PR2VFD12^A

### Vertical Cable Managers w/doors – 8 foot

<b>Dual-sided with two doors:</b>	
6" wide:	PR2VD0696^A
8" wide:	PR2VD0896^A
10" wide:	PR2VD1096^A
12" wide:	PR2VD1296^A
<b>Dual-sided with one door:</b>	
6" wide:	PR2VSD0696^A
8" wide:	PR2VSD0896^A
10" wide:	PR2VSD1096^A
12" wide:	PR2VSD1296^A
<b>Single-sided with one door:</b>	
6" wide:	PR2VFD0696^A
8" wide:	PR2VFD0896^A
10" wide:	PR2VFD1096^A
12" wide:	PR2VFD1296^A

### Standard EIA Racks – 7 foot

<b>2-Post aluminum rack with #12-24 threaded rails:</b>	
	R2P^A
<b>4-Post steel rack with #12-24 threaded rails:</b>	
	R4P^A
<b>4-Post steel rack with cage nut rails:</b>	
	R4PCN^A

### Accessories

<b>7" front slack management spool:</b>	
	PRSP7
<b>5" rear slack management spool:</b>	
	PRSP5
<b>End panel:</b>	PR2VEP^A
<b>Cable retainer:</b>	WR5E-X
<b>Waterfall for use with 2-post rack and PR2V managers:</b>	
	R2PPR2VWF^A
<b>Waterfall for use with R4P 4-post rack and PR2V managers:</b>	
	R4PPR2VWF^A
<b>Pass-through hole blanking plugs (kit of five plugs):</b>	
	PR2VBPK

\* For part numbers 8 feet tall, add "96" to end of part number.  
Ex: PR2VEP96 or R2P96  
^ For part numbers in white, add "WH" to end of part number.  
Ex: PR2VD06WH or R2PWH

# PatchRunner™ 2 Vertical Cable Managers

## technical information

### 6.5 Foot Managers and Doors

Part Number	RU	Height in (mm)	Width in (mm)	Depth in (mm)
<b>Dual Sided</b>				
PR2VD0679	42	78.9 (2003)	6.0 (152)	20.7 (526)
PR2VD1279	42	78.9 (2003)	12.0 (305)	20.7 (526)
<b>Single Sided</b>				
PR2VFD0679	42	78.9 (2003)	6.0 (152)	12.0 (305)
PR2VFD1279	42	78.9 (2003)	12.0 (305)	12.0 (305)

### 7 Foot Managers and Doors


Part Number	RU	Height in (mm)	Width in (mm)	Depth in (mm)
<b>Dual Sided</b>				
PR2VD06*	45	83.9 (2130)	6.0 (152)	20.7 (526)
PR2VD08*	45	83.9 (2130)	8.0 (203)	20.7 (526)
PR2VD10*	45	83.9 (2130)	10.0 (254)	20.7 (526)
PR2VD12*	45	83.9 (2130)	12.0 (305)	20.7 (526)
<b>Single Sided</b>				
PR2VFD06*	45	83.9 (2130)	6.0 (152)	12.0 (305)
PR2VFD08*	45	83.9 (2130)	8.0 (203)	12.0 (305)
PR2VFD10*	45	83.9 (2130)	10.0 (254)	12.0 (305)
PR2VFD12*	45	83.9 (2130)	12.0 (305)	12.0 (305)

\* Add "WH" to end of part numbers for white products

### 8 Foot Managers and Doors

Part Number	RU	Height in (mm)	Width in (mm)	Depth in (mm)
<b>Dual Sided</b>				
PR2VD0696*	52	95.9 (2435)	6.0 (152)	20.7 (526)
PR2VD0896*	52	95.9 (2435)	8.0 (203)	20.7 (526)
PR2VD1096*	52	95.9 (2435)	10.0 (254)	20.7 (526)
PR2VD1296*	52	95.9 (2435)	12.0 (305)	20.7 (526)
<b>Single Sided</b>				
PR2VFD0696*	52	95.9 (2435)	6.0 (152)	12.0 (305)
PR2VFD0896*	52	95.9 (2435)	8.0 (203)	12.0 (305)
PR2VFD1096*	52	95.9 (2435)	10.0 (254)	12.0 (305)
PR2VFD1296*	52	95.9 (2435)	12.0 (305)	12.0 (305)

\* Add "WH" to end of part numbers for white products



#### 1. R2P - 19" Standard EIA Rack 19" x 7, 45 RU

#### PatchRunner™ 2 Vertical Cable Managers and Doors

- 2a. PR2VD06 - 6" wide
- 2b. PR2VD08 - 8" wide
- 2c. PR2VD12 - 12" wide

#### Angled Modular Patch Panels

- 3a. CPPLA48WBLY - 2 RU, 48-Port
- 3b. CPPA48HDWBLY - 1 RU, High Density 48-Port

#### Cable Management Accessories

- 4. NM4 - Cable Manager, 4 RU
- 5. CMT4 - Trough, 4 RU
- 6. PR2VEP - End Panel
- 7. R2PPR2VWF - Waterfall

#### WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA  
Phone: 800.777.3300

PANDUIT EUROPE LTD.  
London, UK  
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.  
Republic of Singapore  
Phone: 65.6305.7575

PANDUIT JAPAN  
Tokyo, Japan  
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA  
Guadalajara, Mexico  
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.  
Victoria, Australia  
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to [www.panduit.com/warranty](http://www.panduit.com/warranty)

# PANDUIT®

Visit us at [www.panduit.com](http://www.panduit.com)

[edi@panduit.com](mailto:edi@panduit.com)

©2018 Panduit Corp.  
ALL RIGHTS RESERVED.  
RKSP172--WW-ENG  
6/2018