

Technical Information Bulletin


CHOICE LED Lamps



Date: _____ Name of distributor: _____
 In hands date of project: _____ Client #: _____
 Project name/Number: _____ Name of end user: _____

ORDERING INFORMATION

Order code: 66311
 Description: MR16/12V/6.5W/40K/35/CHOICE/STD
 UPC: 69549663114
 Case quantity: 24



PERFORMANCE DATA

Shape: MR16
 Base: GU5.3
 Watts(W): 6.5
 Volts (VAC): 12
 Colour temperature (K)**: 4 000
 Life L70 (hrs): 25 000
 Initial lumens (lm)*: 563
 Initial lumens per watt (lm/W): 87
 CRI: 86
 Beam angle (°): 35
 CBCP: 778
 Power factor: 0.92
 Operating temperature range: -20 °C to 40 °C (-4 °F to 104 °F)
 Traditional equivalent (W): 50

*Initial lumens range: +/- 10 % **Typical colour temperature range: +/- 10 %



CAUTIONS

- Turn power off before inspection, installation, or removal.
- Risk of electrical shock – do not use where directly exposed to water or weather.
- Not for use in totally enclosed luminaires.
- Suitable for use in damp locations.
- Do not open – no user serviceable parts inside.
- Use only on 120 VAC, 60Hz circuits.
- This device is not intended for use with emergency exit fixtures or emergency exit lights.
- Compatible with most dimmers.
- For complete dimmer and warranty information visit www.standardpro.com.

| Qty | Description | Price |
|-----|-------------|-------|
| | | |

I accept the specifications of the luminaire configuration mentioned above.

Name: _____
 Company: _____
 Signature: _____ Date: _____

This lighting equipment complies with Canadian standard ICES-005 for use in residential applications.
 Data is based upon tests performed in a controlled environment and representative of relative performance.
 Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.