

OWP-NC-301-LED

LED Large No Cut-Off Wall Pack Series

up to 105 Wattage / up to 13000 Lumens

Catalog Number:

Project Name:

Note:

Type:




APPLICATIONS:

This large size no cut-off LED wall pack provides long lasting, energy efficient lighting with a variety of options to customize fixture performance to the required task. Keeping with the look of a traditional MH wall pack, while reducing energy consumption up to 80% and lasting over 50,000 hours. Easily mounts to building and is ideal for industrial, educational, multi-family, institutional, and government applications.


FEATURES:

- 120-277V
- Lumen output up to 13000 lm with efficacy 121 lm/W and higher
- Polycarbonate optical lens with UV stabilizers
- Photocell optional
- Replacing 320W MH - 4000W MH
- Operating temperature is -40°C to 40°C (-40°F to 104°F)
- UL/cUL wet location listed
- DLC Listed

DIMENSION:



PHOTOMETRICS:



B	U	G
1	4	5

SPECIFICATIONS:

LUMENS	9000 / 12000 lumens
WATTAGE	87W / 105W
CCT	40K-50K
CRI	80
LIGHT EFFICIENCY	+121 lumens/watt
VOLTAGE	120-277 VAC
POWER FREQUENCY	50/60 Hz
FINISH	Bronze
APPLICABLE ENVIRONMENT	Dry/Damp/Wet location
WORKING TEMPERATURE	-40°C to 50°C



Ordering Guide > Example: OWP-NC-301-LED-12000L-MVOLT-40K-BZ

OWP-NC-301-LED						
SERIES	PERFORMANCE	VOLTAGE	CCT	FINISH	EMERGENCY	ACCESSORIES
OWP-NC-301-LED	9000L - 9000 lumens 12000L - 12000 lumens	MVOLT - 120-277V	40K - 4000K 50K - 5000K	BZ - Bronze	O-EMG-LED	PHC - Photocell FS-P211-B - Remote Motion Sensor

** DesignLights Consortium® (DLC) qualified product. Not all versions of this product may be DLC qualified. Please check the DLC Qualified Products List at www.designlights.org to confirm which versions are qualified.



Submittal form is available @ www.oraclelighting.com
Tel: 323-888-1973 • Fax: 323-888-1977

Specifications and Dimensions subject to change without notice.

Issued-B1118-Rev. 1