



Catalog Number
Notes
Type

Contractor Select™  
**TDD LED**  
 Area Light

Replace your 100W Metal Halide “barn light” with the powerful TDD LED luminaire that consumes only 31 watts, providing energy savings of up to 75%. The slim housing style offers a fresh update to the traditional appearance.

**FEATURES:**

- Replaces 100W HID lamps, energy savings of up to 75%
- Cost effective and energy efficient, Payback within two years
- Built-in photo cell for dusk to dawn operation



Catalog Number	UPC	Description	Replaces Up To	Lumens	Wattage	Voltage	CCT	Finish	Pallet qty.
TDD LED P1 40K 120 PE DNA M4	190887149562	AREA	100W Metal Halide	3,096	31W	120V	4000K	GRAY	72
TDD2 LED P1 50K 120 PER DNA M4	190887149593	AREA	175W Mercury Vapor	4,700	41W	120V	5000K	GRAY	72

More configurations are available. [Click here](#) or visit [www.acuitybrands.com](http://www.acuitybrands.com) and search for TDD LED.

<b>Accessories:</b> Order as separate catalog number.	
OMA	Mounting Arm



## Specifications

### INTENDED USE:

The energy savings, long life and easy-to-install design of the TDD LED make it the smart choice for building- and post-mounted doorway, pathway and yard illumination for nearly any facility.

### CONSTRUCTION:

Die-cast aluminum housing with span aluminum shroud, has an impact-resistant, polycarbonate lens which protects the LEDs. The fixture is sealed against moisture and environmental contaminants.

### ELECTRICAL:

Light engine consists of two multi-chip, high-output LEDs mounted on an integral aluminum heat sink to maximize heat dissipation and promote long life (L98/50,000 hours at 40°C). 2.5kV surge protection. Electronic driver operates at 120V. Integrated photocell is standard. No user serviceable parts.

### INSTALLATION:

Easily mounts to a wooden post or pole using 2" lag screws, included. Compatible with OMA-1-5/8" mounting arm, sold separately.

### LISTINGS:

UL Listed to U.S. and Canadian safety standards for wet locations. ENERGY STAR® certified product.

DesignLights Consortium® (DLC) qualified product. Not all versions of this product may be DLC qualified. Please check the DLC Qualified Products List at [www.designlights.org/QPL](http://www.designlights.org/QPL) to confirm which versions are qualified.

### WARRANTY:

5-year limited warranty. Complete warranty terms located at:

[www.acuitybrands.com/CustomerResources/Terms\\_and\\_conditions.aspx](http://www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx)

**Note:** Actual performance may differ as a result of end-user environment and application. All values are design or typical values, measured under laboratory conditions at 25 °C. Specifications subject to change without notice.

## Dimensions

All dimensions are inches (centimeters) unless otherwise indicated.


### TDD LED P1:

Width: 11" (28 cm)

Height: 4.7" (13.3 cm)

Depth: 13-1/2" (34 cm)

Weight: 2.45 lbs (1.11kg)



### TDD2:

Width: 9-1/2" (24.0 cm)

Height: 9-1/8" (23.0 cm)

Depth: 11-3/8" (29.0 cm)

Weight: 4.8 lbs. (2.17 kg)

