



Environmental

Open frame allows air flow, eliminating the need for cooling.

HUBBELL
Advantage

- Supports Heavy or Deep Equipment in Locations with Limited Floor Space
- Quick Release Latches — Rack Frame Hinges Left and Right
- Cable Tie Slots Along Both Sides and Inside Top and Bottom
- Ships Knocked-Down to Conserve Transportation

Flexibility

Left or right door mounting, quick release hinge pin.



Cable Management

Integrated loop management ties along the back rail.



Versatility

Swing racks are available in various sizes to accommodate today's applications.



Specifications

- Material: 16ga braces; 12ga equipment frame
- Finish: durable black powder coat
- 70lb load capacity
- 16" on center mounting for easy attachment to standard wall studs
- 3" deep rack uprights

Standards/Listings/Verifications

- EIA-310-D universal spacing tapped #12-24 front and back

Wall Mount Swing Frame

Contents: 1 rack frame
1 kit mounting hardware (50 - 12/24 screws)

Rack Units	Height Inches (mm)	Width Inches (mm)	Depth Inches (mm)	Finish	Catalog No.
12	24" (610)	20.7" (526)	18" (457)	Black	HPWWMR24
19	36" (914)	20.7" (526)	18" (457)	Black	HPWWMR36
26	48" (1219)	20.7" (526)	18" (457)	Black	HPWWMR48