# DT-355 Dual Technology Line Voltage Ceiling Sensor

Architecturally appealing . low profile appearance Operates at 120, 230 (single phase), 277 or 347 VAC, 50/60 Hz

> • Terminal wiring for quick and easy installation

Walk-through mode increases savings potential

Ultrasonic diffusers give more comprehensive • coverage

## Product Overview

#### Description

WattStopper's low profile DT-355 dual technology occupancy sensor combines the benefits of passive infrared (PIR) and ultrasonic technologies. The sensor mounts on the ceiling with a flat, unobtrusive appearance and provides 360 degrees of coverage.

#### Operation

The DT-355 is line voltage and operates on a single phase at 120, 230, 277 or 347 VAC. The sensor turns lighting on when both PIR and ultrasonic technologies detect occupancy. PIR technology senses the difference between infrared energy from a human body in motion and the background space. Ultrasonic technology uses high frequency (40KHz) ultrasound to sense motion within the space. Once lighting is on, detection by either technology holds lighting on. When no occupancy is detected for the length of the time delay, lighting turns off. The DT-355 can also be set so that only one technology is needed to trigger or both technologies are needed to hold lighting on.

Features

- Advanced control logic based on RISC microcontroller provides:
  - Detection Signature Processing eliminates false triggers and provides immunity to RFI and EMI
  - Walk-through mode turns lights off 3 minutes after the area is initially occupied – ideal for brief visits such as mail delivery
  - Built-in light level sensor featuring simple, one-step setup
- Zero-crossing for long relay life

#### **Time Delay Options**

PROJECT Location/type

> The DT-355 is factory set for a 20 minute time delay, ideal for both energy savings and user satisfaction in most applications. Installers can quickly select other fixed time delays (5, 10, 15 or 30 minutes) via DIP switches. Fixed time delays eliminate the occupant dissatisfaction associated with an automatically adjusted time delay option, and reduce callbacks. Walk-through mode may be enabled for added energy savings in spaces with frequent transient traffic.

#### Application

WattStopper's patented dual technology has the flexibility to work in a variety of applications, where one technology alone could encounter false triggers. Ideal applications include classrooms, open office spaces, large offices, and computer rooms. In addition, because the DT-355 can be mounted onto a variety of junction boxes, the sensor has the flexibility to be used in a wide range of spaces. The sensors eliminate the need for a power pack by using line voltage wiring.

- Ultrasonic diffusion technology spreads coverage to a wider area (patent pending)
- DIP switch simplifies sensor adjustments
- LEDs indicate occupancy detection
- Uses existing line voltage wiring and doesn't require a power pack
- Six occupancy logic options give users the ability to customize control to meet application needs
- Qualifies for ARRA-funded public works projects
- Sensor coverage tested to NEMA Guide Publication WD 7-2000

Watt Stopper<sup>®</sup> www.wattstopper.com 800.879.8585

• Multi-level, 360° Fresnel lens for superior

• Dimensions: 4.50" diameter x 1.45" deep

• Mounting options: 4 square junction box with

double gang mudring; 4 inch octagonal junction

occupancy detection

(114.3mm x 25.9mm)

UL and cUL listed

Ceiling Mounting

Five year warranty

box

**i**((


### **Specifications**

- 120/230 (single phase)/277/347 VAC, 50/60 Hz
- Ultrasonic frequency of 40kHz

DT-355 Wiring Diagram

- Time delays: 5, 10, 15, 20, or 30 minutes, walkthrough, test-mode
- Sensitivity adjustment: High/low (for PIR sensitivity); ultrasonic sensitivity is variable with trimpot
- Built-in light level sensor works from 10 to 300 footcandles (107.6 to 3,229.2 lux)

# Wiring & Mounting



Sensors are white

-U = ARRA compliant. Product produced in the U.S.

 $\bigcirc$