

WIREMOLD® Tele-Power® Poles

Bring Wire & Cable Down to Business

Routing power, data, and A/V – neatly and simply – from up there to down here; that's what Wiremold® Tele-Power® Poles are all about. Their sole purpose is to get the business end of your wire and cabling needs down to your workstation, equipment, or modular furniture. Specifically, in away-from-the-wall locations in open commercial office areas, schools, labs, stores, nurses stations, and other sites.

Whatever power, data, or A/V wiring you need to bring down to the desk, workstation, or cash registers, Wiremold Tele-Power Poles handle all of your needs effortlessly. For modular office furniture – our poles easily provide the hook up to feed office partitions. The poles are also available with specialized electrical circuits such as dedicated/isolated ground. Vertical drop poles give you the flexibility and capacity to devote both sides of the pole for single or dual service feeds. Legrand/Wiremold offers the broadest selection of open space solutions. With standard, custom and configurable products, you can rest assured that the right solution is readily available and adaptable to your current and future work environments.



The right vertical solution for any situation.

FEATURES & BENEFITS

- Promote sustainable design. Allowing services to be routed to the center of an open space rather than by building a wall increases the use of natural daylight and reduces energy consumption.
- Bring power, data, and A/V services into open space environments quickly & easily. Easy to install. Reduces costs for moves, adds and changes.
- Wide selection of standard options. Stocked in a variety of materials, finishes, sizes, and device configurations. Provides what you want, when you need it.
- Relocatable. Ready for service in 30 minutes or less. Can be quickly reconfigured or relocated as work space uses and service needs change.
- Dual-channel. Allows a single drop point for access to multiple services.
- Accessory packs included. Furnished with feed fittings, ceiling trim plates, T-Bar mounting hardware, and carpet/floor grippers. Everything you need for a complete and stationary installation accommodating a variety of installation scenarios.
- Custom capabilities. Modify receptacle type and location, change color finish, alter pole heights, add fixture whips and more. Affording you more choice in appearance and configuration.

- On-site configurability. In-field modifications, including adding devices and changing the height, make Tele-Power poles even more flexible.
- A/V Compatibility. 30TP Series are now compatible with A/V devices to allow for a full range of services to your work stations.
- Datacom connectivity options. Accepts industry standard and proprietary devices from a wide range of manufacturers to provide a seamless and aesthetically pleasing interface for voice, data, audio, and video applications at the point of use.
- New TPP-E Series Tele-Power Pole Extenders combine quick installation with easy job-site handling. Snap together 5' sections to create a pole or extend the length of your existing 25TP series pole. These new extenders accommodate a variety of ceiling heights, can ship UPS or air freight for quick & reliable delivery.

New Tele-Power Pole Extenders make transporting and installing power poles a snap, literally.





		Field M	odificati	ons for	Tele-Po	wer Pol	es								
		TELE-POWER POLE SERIES													
MODIFICATION	30TP-4V	30TC-4V	30TP-2V	30TC-2V	25DTP-4	25DTP-4D	25DTC-4	AMDTP-4	AMDTP-4D	AMTC-4					
Can the receptacles in the standard pole be rewired in order to have a two circuit pole with standard duplexes?	Yes	N/A	Yes	N/A	No	Yes	N/A	No	Yes	N/A					
Can the receptacles in the standard pole be replaced with other types? (i.e. Hospital Grade, TVSS, GFCI, etc.)	Yes – Using the proper device cover	N/A	Yes – Using the proper device cover	N/A	Yes – with 2507C Bracket & only with NEMA duplex receptacles	Yes - only with NEMA duplex receptacles	N/A	Yes – with 2507C Bracket & only with NEMA duplex receptacles	Yes - only with NEMA duplex receptacles	N/A					
Can receptacles be added to blank poles?	N/A	Yes	N/A	Yes - Using the proper device cover	N/A	N/A	Yes	N/A	N/A	Yes					
Can blank poles be used for furniture feed applications by field punching KOs on poles for power and voltage?	N/A	Yes	N/A	Yes	N/A	N/A	Yes	N/A	N/A	Yes					
Can more than one add-on device cover be used?	N/A	N/A	N/A	N/A	Yes	Yes	N/A	Yes	Yes	N/A					
Can receptacles be installed in both sides of the pole?	Yes – Power only on both sides	Yes – Power only on both sides	N/A	N/A	No	No	N/A	No	No	N/A					
Can poles be field cut for use in lower ceiling applications?	Yes*	Yes*	Yes*	Yes*	Yes*	Yes*	Yes*	Yes*	Yes*	Yes*					
Can poles be mounted to hard or open ceilings?	Yes**	Yes**	Yes**	Yes**	Yes**	Yes**	Yes**	Yes**	Yes**	Yes**					

^{*} Review instruction sheet for instructions for cutting poles.

NOTE: All receptacles, additions, rewiring and other electrical modifications must be made by a qualified electrician in accordance with the NEC or other applicable local codes and adhering to the wire fill capacity charts for the respective pole.




Specially-designed Tele-Power Poles can be fitted with lighted signage while also bringing power and data to cash wraps and counter areas, or used to feed services to display cases, photo kiosks and price check stations.

^{**} Pole housing cannot be penetrated. Ceiling mounting hardware must provide firm support and must be supplied by installer.

Steel Tele-Power Poles

Steel Tele-Power Poles are the workhorse of vertical wire and cable management solutions. They are available either prewired with electrical devices or as blanks to feed services to other wire and cable management systems, such as electrified modular furniture. As the long time industry standard, steel Tele-Power Poles are available with an ivory enamel finish and are available in a variety of lengths. They also offer the flexibility of field configuration or can be customized to customer specifications.



NOTE: Custom colors, other lengths (20' [6.1m] max.) or additional circuits are available on custom orders.

Consult factory for more information. Can be factory or field wired with many commercially available devices.

	2	5DTP	& 30TP	Series 7	Геlе-Р	ower	Pole	s Wire	e Fill	Capa	cities	6				
CATALOG NUMBER	NUMBER & TYPE OF POWER OUTLETS	POLE Inches	HEIGHT [mm]	FINISH	-	Size /THWN #12		at 5 [5.6mm] 40%**	0.25" 20%*	at 6 [6.3mm] 40%**		58/U [5.0mm] 40%**	1	2A/U [6.1mm] 40%**		36/U [6.9mm] 40%**
25DTP-4 25DTP-412 25DTP-415 25DTP-E10	Two Duplex Receptacles (20A, 125V)	10' 5" 12' 5" 15' 5" 10' 5"	[3.175m] [3.780m] [4.700m] [3.175m]	Ivory/Gray Ivory/Gray Ivory/Gray Ivory/Gray	10 10 10 10	15 15 15 15	10 10 10 10	19 19 19 19	9 9 9	17 17 17 17	13 13 13 13	25 25 25 25	8 8 8	16 16 16 16	7 7 7 7	13 13 13 13
25DTP-4D	Two Duplex Receptacles (20A, 125V), One Dedicated/Isolated & One Standard Branch Circuit	10' 5"	[3.175m]	Ivory/Gray	10	15	10	19	9	17	13	25	8	16	7	13
25DTP-4ACT	Two Duplex Receptacles (20A, 125V), One Communications Insert Mounting Adapter, One Dual Cat 5e Insert, Two Blank Inserts & Labeling Supplies	10' 5"	[3.175m]	Ivory/Gray	10	15	10	19	9	17	13	25	8	16	7	13
30TP-2V 30TP-212V 30TP-215V	Two Duplex Receptacles (20A, 125V)	10' 5" 12' 5" 15' 5"	[3.175m] [3.780m] [4.700m]	Ivory Ivory Ivory	9 9 9	14 14 14	61 61 61	31 31 31	13 13 13	26 26 26	20 20 20	40 40 40	13 13 13	25 25 25	10 10 10	20 20 20
30TP-4V 30TP-412V 30TP-415V 30TP-4V3S2 30TP-412V3S2	Two Duplex Receptacles (20A, 125V)	10' 5" 12' 5" 15' 5" 10' 5" 12' 5"	[3.175m] [3.780m] [4.700m] [3.175m] [3.780m]	Ivory Ivory Ivory Ivory Ivory	18 18 18 18 18	18 18 18 18 18	19 19 19 19 19	37 37 37 37 37	15 15 15 15 15	30 30 30 30 30	24 24 24 24 24 24	47 47 47 47 47	15 15 15 15 15	30 30 30 30 30	12 12 12 12 12	24 24 24 24 24

^{* 20%} cable fill is calculated to approximate reduction in cable capacity due to connectors mounted within pole section that may restrict cross-sectional areas.

^{** 40%} cable fill is the maximum designed cable fill based on a proposed revision to TIA/EIA 569-A.


	25DTC & 30TC Series Vertical Drop Poles Communications Fill Capacities												
CATALOG NUMBER	POLE Inches	E HEIGHT [mm]	FINISH	Cat 0.22" Sm. Comp.	[5.6mm]	Cat 0.25" Sm. Comp.	[6.3mm]	RG5 0.195" Sm. Comp.	58/U [5.0mm] Lg. Comp.	RG62 0.242" Sm. Comp.	2A/U [6.1mm] Lg. Comp.	RG 0.270" Sm. Comp.	6/U [6.9mm] Lg. Comp.
25DTC-4	10' 5"	[3.175m]	Ivory/Gray	19	26	16	22	25	33	16	21	12	17
25DTC-412	12' 5"	[3.780m]	Ivory/Gray	19	26	16	22	25	33	16	21	12	17
25DTC-415	15' 5"	[4.700m]	Ivory/Gray	19	26	16	22	25	33	16	21	12	17
25DTC-E10	10' 5"	[3.175m]	Ivory/Gray	19	26	16	22	25	33	16	21	12	17
30TC-2V	10' 5"	[3.175m]	Ivory	n/a	33	n/a	30	n/a	47	n/a	30	n/a	24
30TC-212V	12' 5"	[3.780m]	Ivory	n/a	33	n/a	30	n/a	47	n/a	30	n/a	24
30TC-215V	15' 5"	[4.700m]	Ivory	n/a	33	n/a	30	n/a	47	n/a	30	n/a	24
30TC-4V	10' 5"	[3.175m]	lvory	37	37	30	30	47	47	30	30	24	24
30TC-412V	12' 5"	[3.780m]	lvory	37	37	30	30	47	47	30	30	24	24
30TC-415V	15' 5"	[4.700m]	lvory	37	37	30	30	47	47	30	30	24	24
30TC-3S2	10' 5"	[3.175m]	lvory	37	37	30	30	47	47	30	30	24	24
30TP-412V3S2	12' 5"	[3.780m]	lvory	37	37	30	30	47	47	30	30	24	24

Steel Tele-Power Poles (continued)

Steel Tele-Power Poles Ordering Information Catalog No./Item **Description/Specifications** 25DTP-4 Tele-Power Pole - Two-25DTP-4-DG compartment pole (power and 25DTP-412 communications). Nominal material 25DTP-412-DG thickness .030" [0.8mm]. Ivory or gray bootbase. Factory wired with 25DTP-415 25DTP-415-DG fed-specgeneral grade 20A125V duplex style receptacles. An 8" [203mm] cover at top front of pole is removable for making power wiring connections. KOs provided in removable cover for RJ11/RJ45 and modular furniture communication connectors. Mounting hardware, entrance end plate and two ceiling trim plates furnished. Available in standard lengths of 10' 5" [3.2m] (25DTP-4), 12' 5" [3.8m] (25DTP-412) and 15' 5" [4.7m] (25DTP-415). Also increase the length of any 25 Series pole with the 25DTC-E5 Tele-Power Pole Extender. Back 25DTP-4ACT Tele-Power Pole - Identical to 25DTP-4ACT-DG 25DTP-4 except with one communications insert mounting adapter, one dual Cat 5e insert. two blank inserts & labels. 25DTP-4D Tele-Power Pole - Identical to 25DTP-4D-DG 25DTP-4 except has one 20A 125V dedicated/isolated ground duplex receptacle and one 20A 125V standard duplex receptacle. Tele-Power Pole Extender -25DTP-E10 25DTP-E10-DG [↑] Two sections of a two-compartment (power and communication) pole (5' 4" [1.626m] base + 5' [1.524m] extender) assembles to form a 10' 4" [3.148m] pole. Nominal material thickness .040" [1.0mm]. Ivory or gray boot base. Factory wired with fed-spec general grade 20A 125V duplex style receptacles. An 8" [203mm] cover at top front (power side) of pole is removable for making power wiring connections. KOs provided in removable cover for RJ11/RJ45 and modular furniture communication connectors. Mounting hardware, entrance end plate and two ceiling trim plates furnished. Front Back


NOTE: Custom colors, custom lengths (20' [6.1m] max.) or additional circuits are available on custom order. Consult factory for more information. Can be factory or field-wired with many commercially available devices.

Catalog No./Item **Description/Specifications** 30TP-2V Tele-Power Pole - Two-30TP-212V compartment pole (power and communications). Nominal material thickness .040" [1.0mm]. Factory wired with two specification grade 20A. 125V duplex receptacles. Mounting hardware, entrance end fitting, and ceiling trim plate furnished. Available in standard lengths of 10' 5" [3.2m] (30TP-2V)



Tele-Power Pole - Twocompartment pole (one power; one communication with crossover below power devices). Nominal material thickness .040" [1.0mm]. Factory wired with two specification grade 20A, 125V duplex receptacles. Mounting hardware, entrance end fitting, and ceiling trim plate furnished. Available in standard lengths of 10' 5" [3.2m] (30TP-4V) and 12' 5" [3.8m] (30TP-412V).

and 12' 5" [3.8m] (30TP-212V).



Tele-Power Pole – Two duplex receptacles (20A, 125V). One Ortronics® Series II adapter. One Ortronics® Series II dual Cat. 5e insert, two blank inserts and labeling supplies. Available in standard lengths of 10' 5" [3.2m] (30TP-4V3S2) and 12' 5" [3.8m] (30TP-412V3S2).



Wiremold Tele-Power Poles offer relocation flexibility to support open office designs. Quickly and easily reconfigure poles to meet changes in floor plans or capacity needs.

Steel Tele-Power Poles (continued)

Steel Vertical Drop Poles Ordering Information

Catalog No./Item

Description/Specifications

25DTC-4 25DTC-4-DG 25DTC-412 25DTC-412-DG 25DTC-415 25DTC-415-DG



Blank Steel Pole – Two-compartment pole. Nominal material thickness .040" [1.0mm]. Ivory or gray boot base. Furnished unwired without outlets. Mounting hardware, entrance end plate and ceiling trim plates furnished.

Available lengths: 10' 5" [3.2m] (25DTC-4), 12' 5" [3.8m] (25DTC-412) and 15' 5" [4.7m] (25DTC-415).

30TC-2V 30TC-212V 30TC-215V



Blank Steel Pole – Single-compartment pole. Furnished unwired without outlets. Nominal wall thickness .040" [1.0mm]. Mounting hardware, entrance end fitting, and ceiling trim plate furnished. Available lengths: 10' 5" [3.2m] (30TC-2V), 12' 5" [3.8m] (30TC-212V) and 15' 5" [4.7m] (30TC-215V).


30TC-4V 30TC-412V 30TC-415V



Blank Steel Pole – Two-compartment pole. Furnished unwired without outlets. Nominal wall thickness .040" [1.0mm]. Mounting hardware, entrance end fitting, and ceiling trim plate furnished. Available lengths: 10' 5" [3.2m] (30TC-4V), 12' 5" [3.8m] (30TC-412V) and 15' 5" [4.7m] (30TC-415V).

Catalog No./Item






Description/Specifications

Blank Steel Tele-Power Pole Extender – Two sections of a two-compartment pole (5' 4" [1.626m] base and 5' [1.52m] extender) assembles to form a 10' 4" [3.148m] pole. Nominal material thickness .040" [1.0mm]. Ivory or gray boot base. Furnished unwired without outlets. Mounting hardware, entrance end plate and ceiling trim plate furnished. An 8" [203mm] cover at top of pole is removable for making power wiring connections.

25DTC-E5 25DTC-E5-DG



Blank Steel Tele-Power Pole Extender – Two-compartment extender mounts onto existing 25DTP or 25DTC series pole. Nominal material thickness .040" [1.0mm]. Furnished unwired without outlets. Use existing pole mounting hardware, entrance end plate and ceiling trim plate. Available in 5' [1.524m] length. Can be cut to desired length.

NOTE: All poles have removable cover sections with KOs for modular jacks and openings to accept modular furniture adapters for communication devices.





Wiremold Tele-Power
Poles offer a wide variety
of custom and service
configuration options to
accommodate most
installation requirements.

Steel Tele-Power Poles (continued)


A full range of accessories enables fast and easy field configurability. Additional receptacles or devices can be added to existing poles for maximum flexibility. While the new Tele-Power Pole Extender allows for easy, on-site modifications to accommodate a variety of height requirements.

g No.	/Item	Description/Sp	ecifications	Catalog No./Item	Description/Specification
OTP-A TP-A		Power Poles. In mounting brack of single recept [35mm - 36mm	eptacles or ing modular Tele- cludes receptacle et. Face diameter acle: 1.38" -1.40"	30TP-C	Single Gang Cover – Acc to 30A shallow-style device flushplate. G3007 Device included. Ivory finish. Use mount industry standard s and angled communication faceplates.
IDTP-B	25DTP-A AMDTP-A	COLOR Ivory Steel (25DTP-4) Anodized Aluminum (AMDTP-4) Add-On Power	DIMENSIONS 1" x 2 1/4" x 28" [25mm x 57mm x 711mm]	30TP-J	Single Receptacle Cover field installation of single receptacles with face dian 1.56" [40mm] diameter. G Device Bracket included.
DTP-B			ing modular Tele- cludes receptacle	30TP-L	lvory finish. Rectangular Device Cov
8	25DTP-B	COLOR Ivory Steel (25DTP-4) Anodized Aluminum	DIMENSIONS 1" x 2 1/4" x 28" [25mm x 57mm x 711mm]		Rectangular faceplate to accommodate Sentrex sur receptacles, GFCI and oth decorator style devices. G
MDTP-L		(AMDTP-4) Add-On Power	: Cover –		Device Bracket included. Ivory finish.
SDTP-L		Add power recedevices to exist	eptacles or ing modular Tele- icludes receptacle	25DTC-3S2	Data & A/V Add-On Cove 25DTP Series Poles – Accepts Ortronics® Series Modular Connectivity Solu
		COLOR	DIMENSIONS		
8	25DTP-L AMDTP-L	Ivory Steel (25DTP-4) Anodized Aluminum (AMDTP-4)	1" x 2 1/4" x 28" [25mm x 57mm x 711mm]		
80TP-A	°	receptacle cove of receptacles v of 1.38" - 1.40"	acle Cover - Single or fro field installation with face diameters [25mm - 36mm]. Bracket included.	25DTC-CVR	
30ТР-В	Ö	installations of receptacles. G3			
		Bracket include	d. Ivory finish.	30TC-CVR	Data & A/V Add-On Cove 30TC Series Poles – Accepts discrete jacks.

	A	ccessories for Steel Tele-Power	Poles Ordering Informa	ation (continued)
Catalog No./It	em	Description/Specifications	Catalog No./Item	Description/Specifications
30TP-AAP	9 9	Add-On A/V Cover – Accepts three (3) Extron® Electronics AAP plates 12" L x 2.75" W [305mm x 70mm]. Includes three adapters to accommodate Ortronics® or Wiremold Open System devices.	CM-SAP	Data & A/V Add-On Cover for 30TC Series Poles – Single-gang, angled faceplate accepts CM Series Connectors. (Requires 30TP-C Mounting Plate
			25AM10FO	Data & A/V Add-On Cover for 25DTP Series Poles –
30ТР-МААР		Add-On A/V Cover − Accepts five (5) Extron® Electronics MAAP plates 12" L x 2.75" W [305mm x 70mm]. Includes three adapters to accommodate Ortronics® or Wiremold Open System devices.	dif	2" [51mm] radius control Entrance End Fitting.
			25AM-AP 30TP-AP	Replacement Accessory Pack – For 25DTP and 25DTC Series Poles (25AM-AP) or 30TP-2 and 30TP-4 Series Poles (30TP-AP).
CM-SFP		Data & A/V Add-On Cover for 30TC Series Poles – Single-gang faceplate accepts CM Series Connectors. (Requires 30TP-C Mounting Plate.)		Includes: gripper pad, ceiling trim plate, bracket and grommet.
Ų				

Aluminum Tele-Power Poles

When looking to dress up a vertical solution, Tele-Power Poles with a satin anodized aluminum finish in either rectangular or round styles can provide the answer. Light weight aluminum construction makes these poles easy to install and maneuver on the job site. Available prewired with electrical devices or blank to drop services feeding another wire and cable management system, such as electrified modular furniture. A full range of accessories enables field configurability, or have them delivered to your specifications.



NOTE: Custom colors, other lengths (20' [6.1m] max.) or additional circuits are available on custom order.

Consult factory for more information. Can be factory or field wired with many commercially available devices.

Aluminum Tele-Power Poles Wire Fill Capacities																
CATALOG NUMBER	NUMBER & TYPE OF POWER OUTLETS	POLE Inches	HEIGHT [mm]	FINISH		Size /THWN #12		t 5 [5.6mm] 40%**		at 6 [6.3mm] 40%**		58/U [5.0mm] 40%**	1	62A/U [6.1mm] 40%**		
AMDTP-4 AMDTP-412 AMDTP-415	Two Duplex Receptacles (20A, 125V)	10' 5" 12' 5" 15' 5"	[3.175m] [3.780m] [4.700m]	Satin Anodized Aluminum	10 10 10	15 15 15	10 10 10	19 19 19	8 8 8	16 16 16	13 13 13	25 25 25	8 8 8	16 16 16	7 7 7	13 13 13
AMDTP-4D	Two Duplex Receptacles (20A, 125V), One Dedicated/ Isolated & One Standard Branch Circuit	10' 5"	[3.175m]	Satin Anodized Aluminum	10	15	10	19	8	16	13	25	8	16	7	13
ALTP-20W	Four Single Receptacles	10' 4"	[3.150m]	Painted Office White	-	-	2	5	2	4	3	6	2	4	1	3
ALTP-2P	Four Single Receptacles	10' 4"	[3.150m]	Polished Anodized Aluminum	-	-	2	5	2	4	3	6	2	4	1	3
ALTP-2S	Four Single Receptacles	10' 4"	[3.150m]	Satin Anodized Aluminum	-	-	2	5	2	4	3	6	2	4	1	3

^{* 20%} cable fill is calculated to approximate reduction in cable capacity due to connectors mounted within pole section that may restrict cross-sectional areas.



Use Wiremold Tele-Power Poles to deliver multiple services to your desired point-of-use or simply as a feeder system for modular furniture.

^{** 40%} cable fill is the maximum designed cable fill based on a proposed revision to TIA/EIA 569-A.

Aluminum Tele-Power Poles (continued)

	Aluminum Vertical Drop Poles Communications Fill Capacities													
CATALOG NUMBER	POLE Inches	HEIGHT [mm]	FINISH	0.22" Sm. Comp.	t 5 [5.6mm] Lg. Comp.	0.25" Sm. Comp.	nt 6 [6.3mm] Lg. Comp.	RG5 0.195" Sm. Comp.	58/U [5.0mm] Lg. Comp.	RG62 0.242" Sm. Comp.	[6.1mm]	RG 0.270" Sm. Comp.	66/U [6.9mm] Lg. Comp.	
AMDTP-4 AMDTP-412 AMDTP-415	10' 5" 12' 5" 15' 5"	[3.175m] [3.780m] [4.700m]	Satin Anodized Aluminum	10 10 10	19 19 19	8 8 8	16 16 16	13 13 13	25 25 25	8 8 8	16 16 16	7 7 7	13 13 13	
ALTP-20W	10' 4"	[3.150m]	White	10	D .	8	3	1	3	8	3	6	5	
ALTP-2P	10' 4"	[3.150m]	Aluminum	10	0	3	3	1	3	8	3	6	3	
ALTP-2S	10' 4"	[3.150m]	Aluminum	10	0	3	3	1	3	8	3	6	3	
NP800C-12-2B NP800C-12-8B NP800C-15-2B	10' 2" 12' 8" 15' 2"	[3.098m] [3.860m] [4.620m]	Aluminum					page for W of the NP80			es			

Catalog No./Item	Description/Specifications	Catalog No./Item	Description/Specifications
AMDTP-4 AMDTP-412 AMDTP-415	Tele-Power Pole – Two-compartment pole (power and communications). Nominal material thickness .050" [1.8mm]. Length: 10' 5" [3.2m]. Factory wired with fed-spec general grade 20A125V duplex style receptacles. An opening for communications and a 1/2" [12.7mm] hole for power is provided at top. The 8" [203mm] cover at the top front of the pole is removable for making power wiring connections. Communication KOs provided for RJ11/RJ45 and modular furniture connectors. Mounting hardware, entrance end	ALTP-2S OO Front Back	Round Tele-Power Pole – Satin anodized extruded aluminum pole. Nominal wall thickness .060" [1.5mm]. Length 10' 5" [3.2m]. Two-compartment (power and communication channels). Factory wired with four 15A 125V NEMA 5-15R devices. Provided with one 1/2" trade size KO in cover at base for communications. T-Bar mounting hardware, ceiling trim kit, and feed box furnished.
Front Back	plate and two ceiling trim plates furnished. Available in standard lengths of: 10' 5" [3.2m] (25DTP-4), 12' 5" [3.8m] (25DTP-412) and 15' 5" [4.7m] (25DTP-415).	ALTP-20W	Round Tele-Power Pole – Identical to ALTP-2S, with painted office white finish.
AMDTP-4D	Tele-Power Pole – Identical to AMDTP-4 except factory wired with one 20A 125V dedicated/ isolated ground duplex receptacle and one 20A 125V standard duplex receptacle.	ALTP-2P	Round Tele-Power Pole – Identical to ALTP-2S, with polished anodized aluminum finish.

NOTE: Custom colors, custom lengths (20' [6.1m] max.) or additional circuits are available on custom order. Consult factory for more information. Can be factory or field wired with many commercially available devices.

Aluminum Tele-Power Poles (continued)

Aluminum Vertical Drop Poles

A full range of accessories enables fast and easy field configurability. Additional receptacles or devices can be added to existing poles for maximum flexibility. The NP800 pole is the epitome of flexibility, featuring a snap-in divider which permits up to six channels of varying sizes and accommodates up to 60A devices (#6 AWG max). The NP800 may be wired with up to 12 receptacles with the number of circuits limited by the feed method.

Aluminum Vertical Drop Poles Ordering Information Catalog No./Item **Description/Specifications** Catalog No./Item **Description/Specifications** ALTC-2S Blank Round Aluminum Pole -Blank Aluminum Pole - Two-AMTC-4 ALTC-20W Nominal wall thickness .060" **AMTC-412** compartment pole. Nominal ALTC-2P [1.5mm], length 10'3" [3.1mm]. **AMTC-415** material thickness .050" [1.8mm]. ALTC-2S has a satin anodized finish Furnished unwired without outlets. and ALTC-2P has a polished Two 8" [203mm] removable covers **CUSTOM OPTIONS:** aluminum finish. Provided with one with KOs for modular jacks and Features such as 1/2" [12.7mm] trade size KO at modular furniture communication colors or other base. T-bar mounting hardware, outlets. Mounting hardware, lengths (20' [6.1m] ceiling trim kit, foot assembly, and maximum) available entrance end plate, and ceiling trim on custom orders. grommet included. Feed box not plates furnished. Available lengths: furnished. 10' 5" [3.2m] (AMTC-4), 12' 5" [3.8m] (AMTC-412) and 15' 5" [4.7m] (AMTC-415). NP800C-10-2B Blank Aluminum Pole - Twocompartment large capacity pole. Furnished unwired without outlets. Box ended with industry sized knockouts. Standard heights: 10'2" [3.1m] (NP800C-10-2B), 12'8" [3.9m] (NP800C-12-8B), 15'2" [4.6m] (NP800C-15-2B). Other heights available - consult factory. 30" [762mm] communication cover with industry standard knockouts.

log No./	Item	Description/Sp	pecifications	Catalog I	No./Item	Description/Specifications
OTP-A TP-A		Power Poles. Ir mounting brack of single recept [35mm - 36mm	eptacles or ting modular Tele- ncludes receptacle set. Face diameter acle: 1.38" -1.40"	30TP-C		Single Gang Cover – Accepto 30A shallow-style device a flushplate. G3007 Device Braincluded. Ivory fishs. Used to industry standard straight an angled communication facep
	25DTP-A AMDTP-A	COLOR Ivory Steel (25DTP-4) Anodized Aluminum (AMDTP-4)	DIMENSIONS 1" x 2 1/4" x 28" [25mm x 57mm x 711mm]	30TP-J		Single Receptacle Cover – field installation of single receptacles with face diamet 1.56" [40mm] diameter. G300
DTP-B TP-B		Power Poles. Ir	eptacles or ting modular Tele- ncludes receptacle			Device Bracket included. Ivory finish.
8	25DTP-B AMDTP-B	COLOR Ivory Steel (25DTP-4) Anodized Aluminum (AMDTP-4)	DIMENSIONS 1" x 2 1/4" x 28" [25mm x 57mm x 711mm]	30TP-L	o o	Rectangular Device Cover Rectangular faceplate to accommodate Sentrex surge receptacles, GFCI and other decorator style devices. G30 Device Bracket included. Ivory finish.
TP-L TP-L	25DTP-L		eptacles or ting modular Tele- ncludes receptacle	25DTC-3	S2	Data & A/V Add-On Cover 1 25DTP Series Poles – Accepts Ortronics® Series II Modular Connectivity Solutio
P-A	AMDTP-L	Anodized Aluminum (AMDTP-4) Single Recepta	[25mm x 57mm x 711mm] acle Cover – Single	25DTC-C	EVR	Data & A/V Add-On Cover 1 25DTP Series Poles –
	Ç	receptacle cove of receptacles of 1.38" - 1.40"	er fro field installation with face diameters [25mm - 36mm]. e Bracket included.			Accepts discrete jacks.
P-B		installations of receptacles. G3				
		Bracket include	ea. Ivory tinisn.	30TC-CV	R	Data & A/V Add-On Cover f 30TC Series Poles – Accepts discrete jacks.

Add-On A/V Cover — Accepts three (3) Extron₀ Electronics AAP plates 12" L x 2.75" W [305mm x 70mm]. Includes three adapters to accommodate Ortronics⁰ or Wiremold Open System devices. Add-On A/V Cover — Accepts five (5) Extron₀ Electronics MAAP plates 12" L x 2.75" W [305mm x 70mm]. Includes	CM-SAP 25AM10FO	Data & A/V Add-On Cover for 30TC Series Poles – Single-gang, angled faceplate accepts CM Series Connectors. (Requires 30TP-C Mounting Plate.) Data & A/V Add-On Cover for 25DTP Series Poles – 2" [51mm] radius control Entrance End Fitting.
Accepts five (5) Extron₀ Electronics MAAP plates 12" L x	25AM10FO	25DTP Series Poles – 2" [51mm] radius control Entrance
	00	
three adapters to accommodate Ortronics® or Wiremold Open System devices.	25AM-AP	Replacement Accessory Pack – For 25DTP and 25DTC Series
Data & A/V Add-On Cover for 30TC Series Poles – Single-gang faceplate accepts CM Series Connectors. (Requires	SUTP-AP	Poles (25AM-AP) or 30TP-2 and 30TP-4 Series Poles (30TP-AP). Includes: gripper pad, ceiling trim plate, bracket and grommet.
	Data & A/V Add-On Cover for 30TC Series Poles – Single-gang faceplate accepts CM	Data & A/V Add-On Cover for 30TC Series Poles – Single-gang faceplate accepts CM Series Connectors. (Requires


Aluminum Vertical Drop Poles Ordering Information (continued)

Catalog No./Item

Description/Specifications

NP800

Jumbo Tele-Power Pole – Two separate compartments can accommodate up to 60A devices (#6 AWG maximum). Snap-in divider permits up to six channels of varying sizes.



General Specifications:

Receptacles: Each pole compartment may be wired with up to 12 receptacles, with the number of circuits limited by the feed method.

Feed method: All poles are provided with a utility box (4" x 4" x 2 1/8" [102mm x 102mm x 54mm]) for all poles with a cord up to 10' [3m].

Accessories: Ceiling trim plates, pole clamp, and

non-adjustable foot with carpet gripper/adhesive pad furnished.


NP800 SERIES WIRE FILL CAPACITIES FOR COMMUNICATIONS															
CABLE TYPE		UNSHIEL	DED TWIS	TED PAIR	(24 AWG)		SHIELD	ED TWIST	ED PAIR		COAXIA	L CABLE		TWINAX	FIBER*
Description Nom. O.D. Inches	Cat 3 2 Pair 0.14	Cat 3 3 Pair 0.15	Cat 3 4 Pair 0.19	Cat 5 4 Pair 0.22	Cat 6 4 Pair 0.25	Cat 3 4 Pair 0.41	Type 1 22 AWG 0.39	Type 2 22 AWG 0.465		RG58/U 20 AWG 0.195	RG58/U 22 AWG 0.242	RG6/U 22 AWG 0.242	RG6/U 18 AWG 0.27	100 OHM 0.33	0.19
Capacity of Cross-Section (IN²)															
2.4	62	54	33	25	19	7	8	5	20	32	20	20	16	11	33
2.8	72	63	39	29	22	8	9	6	23	37	24	24	19	13	39
3.2	83	72	45	33	26	9	10	7	27	42	27	27	22	14	45
4.2	109	95	59	44	34	12	14	9	35	56	36	36	29	19	59
4.3	111	97	60	45	34	13	14	10	36	57	37	37	30	20	60
4.8	124	108	67	50	38	14	16	11	40	64	41	41	33	22	67
5.0	129	113	70	52	40	15	16	11	42	66	43	43	34	23	70
5.2	135	117	73	54	42	15	17	12	44	69	45	45	36	23	73
5.8	150	131	81	61	46	17	19	13	49	77	50	50	40	27	81
6.2	161	140	87	65	50	18	20	14	52	83	53	53	43	28	87
7.0	181	158	98	73	56	21	23	16	59	93	60	60	48	32	98
7.7	200	174	108	81	62	23	25	18	65	103	66	66	53	36	108
8.0	207	181	112	84	64	24	26	18	67	107	69	69	55	37	112
12.0	311	271	169	126	96	36	40	28	101	160	104	104	83	56	169

^{*}Two Strand (Duplex) Multimode, 625/125µm. Capacity range is calculated at 40% of raceway areas as stated in the Commercial Buildings Standard for Telecommunication Pathways and Spaces, EIA/TIA 569-A.

NP800 SERIES WIRE FILL CAPACITIES FOR POWER										
	WIRE SIZE THHN/THWN	40% FILL	CIRCUITS							
POWER WIRING	10 AWG	12	4							
	12 AWG	13	4							
l	14 AWG	15	5							

NOTES: Wire fill capacities calculated for a pole with a 4" x 4" x 2 1/8" [102mm x 102mm x 54mm] box. Larger boxes can be used if higher capacity is needed.

All of the standard profiles can be easily modified. Contact the factory or the field sales representative for specifics.



NOTES

NOTES

NOTES



Electrical Wiring Systems

www.legrand.ca

60 Woodlawn Street West Hartford, CT 06110 Phone: 1.877.BY.LEGRAND (295-3472) www.legrand.us 570 Applewood Crescent Vaughan, Ontario L4K 4B4 Phone:905.738.9195