Maestro C·L PRO Dimmer

Phase-selectable dimmer for LED, ELV, MLV and Incandescent lamp loads.

Features

- Large tapswitch with a rocker-style dimmer for a standard designer wallplate opening
- Advanced dimming technology designed for compatibility with a broader range of high-efficacy bulbs
- UL_® Listed to control:
 - Dimmable LED with integrated driver
 - Electronic Low-Voltage (ELV)
 - Magnetic Low-Voltage (MLV)
 - Dimmable Compact Fluorescent Lamps (CFLs) with integrated ballast
 - Incandescent and Halogen
 - Philips Advance Mark 10_® ballasts
 - Hi-lume 1% 2-Wire (LTE) LED Driver
- Low-end adjustment to accommodate a wide range of bulbs
- Can be used in single-pole or in multi-location (using MA-R) applications
- Coordinating Claro and Stainless Steel wallplates available separately
- 100% factory-tested

Product Specific Features

- NEMA SSL-7A-2015 compliant (in forward-phase mode)
- Neutral optional See Load Type and Capacity table on page 5
- RTISS Equipped circuitry compensates in real time for incoming line-voltage variations (neutral connection required)
- Capable of controlling up to 250 W dimmable LED or 500 W incandescent/Halogen or mixed bulb type per Multigang and Mixed Bulb Type Ratings table (see page 5)
- Capable of controlling up to 500 W of ELV or 400 VA of MLV or up to 20 Hi-lume 1% 2-Wire (LTE) LED drivers
- UL_® Listed for field interchangeable plastics



Wallplate sold separately

Model Number

MA-PRO-XX¹ Single-pole/3-way²/Multi-location

Color Change Kit Model Numbers

MK-D-XX 1, 3 1 Piece Color Change Kit MK-D-5-XX^{1,3} 5 Piece Color Change Kit

- ¹ "XX" in the model number represents color/finish code. See Colors and Finishes on page 4.
- ² For 3-way and 4-way dimming, Maestro companion dimmers must be used.
- ³ Color change kits do not include wallplates.

\$LUTRON	SPECIFICATION	SUBMITTAL

LUTRON SPECIFICA	ATION SUBMITTAL	Page
Job Name:	Model Numbers:	
Job Number:		

3691112c 2 06.05.19

Specifications

Regulatory Approvals

- UL_® Listed to U.S. and Canadian safety requirements (UL 1472/CSA C22.2 184.1)
- NOM
- NEMA SSL-7A-2015 forward phase compliant

Power and Ratings

- 120 V∼ 50/60 Hz
- Maximum Load
 - 250 W Dimmable LED

OI

- 500 W Incandescent/Halogen/ELV

or

- 400 VA MLV

or

- 20 Lutron Hi-lume 1% 2-Wire (LTE) LED Driversor
- Mixed bulb type per Multigang and Mixed Bulb
 Type Ratings table (see page 5)
- Minimum Load
 - See approved lamp list for LED/CFL at www.lutron.com/ledfinder

Environment

- For indoor use only
- Operating temperatures 32 °F (0 °C) to 104 °F (40 °C)
- Relative humidity: 0% to 90% non-condensing

Performance

- Power failure memory: Should power be interrupted, the control will return to its previous state when power is restored.
- Tested to withstand surge voltages without damage or loss of operation, in accordance with IEEE C62.41-1991 Recommended Practice on Surge Voltages in Low-Voltage AC Power Circuits.
- Tested to withstand electrostatic discharge without damage or memory loss.
- For 3-way and 4-way dimming, use Maestro Companion Dimmers. One dimmer can be used with up to 9 multi-location companion dimmers.
- Total multi-location wire length (blue wire) between all units must not exceed 150 ft (45 m).
- Includes a Front Accessible Service Switch (FASS) for safe bulb replacement.

Application Requirements

- When using LEDs or CFLs, only bulbs marked or rated as Dimmable can be used.
- For a complete list of approved DIMMABLE LEDs and CFLs please visit www.lutron.com/ledfinder

Mounting

 Requires a U.S. wallbox. 3.5 in (89 mm) deep recommended, 2.25 in (57 mm) deep minimum.

Warranty

1 Year Limited Warranty
 For additional Warranty information, please visit www.lutron.com/TechnicalDocumentLibrary/ 369-119_Wallbox_Warranty.pdf


Dago

3/1/2	ITDON	SPECIFICATION	CHDMITTAL
2.5		SPECIFICATION	SUBWILLAR

WESTITOH OF LOTHOATIO	N OODWITTAL	1 agc
Job Name:	Model Numbers:	
Job Number:		

3691112c 3 06.05.19

Operation



IMPORTANT NOTICE:

FASS - Front Accessible Service Switch

To replace lamp(s), remove power by pulling the FASS out fully on all main controlling devices. After replacing lamp(s), push the FASS back in fully to restore power to the control(s).


LUTRON SPECIFICATION SUBMITTAL


Job Name:	Model Numbers:
Job Number:	

3691112c 4 06.05.19

Dimensions

All dimensions are shown as $\underset{(mm)}{\text{in}}$





Colors and Finishes

Gloss Finishes

WH AL GR BL	White Almond Gray Black	IV LA BR	lvory Light Almond Brown
Satin C	colors		
SW	Snow	MN	Midnight
TP	Taupe	BI	Biscuit
ES	Eggshell	PD	Palladium
HT	Hot	MR	Merlot
PL	Plum	SI	Sienna
TC	Terracotta	BG	Bluestone
GB	Green Briar	GS	Goldstone
MS	Mocha Stone	ST	Stone
DS	Desert Stone	LS	Limestone

For the latest color offerings see our website: http://www.lutron.com/satincolors

LUTRON SPECIFICATION SUBMITTAL

Job Name:	Model Numbers:
Job Number:	

Multigang and Mixed-Bulb-Type Ratings

Total LED Wattage Installed (Watts per bulb X # of bulbs)		Maximum Allowable ncandescent/Halogen Wattage		
		Not ganged	End of gang	Middle of gang
0 W	+	500 W	400 W	300 W
1 W – 50 W	+	400 W	300 W	200 W
51 W – 100 W	+	300 W	200 W	100 W
101 W – 150 W	+	200 W	100 W	0 W
151 W – 200 W	+	100 W	0 W	0 W
201 W – 250 W	+	0 W	0 W	0 W

Ganging and Derating

When combining controls in the same wallbox, derating is required. See **Load Type and Capacity**. No derating is required for companion devices.

Load Type and Capacity

Model	Model Description Voltage		oltage Load Type	Minimum Load	Maximum Load			Neutral	Required Phase	
Number	Description	voltage	Load Type	Willillian Load	Not Ganged	End of Gang	Middle of gang	Neutrai	Mode	
				LED ²	1 bulb	250 W	200 W	150 W	Optional ⁸	Either
			CFL ^{2,3}	1 bulb	250 W	200 W	150 W	Optional ⁸	Forward	
			MLV Transformer with LED	Can Arallantina Nata (ISEO (DALOGOSEO) at manufatura and					Forward	
			ELV Transformer with LED	Set	e Application Note	Application Note #559 (P/N 048559) at www.lutron.com			Reverse	
			MLV Transformer with Halogen ^{4,5,6,}	10 W	400 VA (300 W)	No Deratir	ng Required	Required	Forward	
MA-PRO-XX ^{1,2}	Phase- Selectable	le 120 Va	electable 120 Va	ELV Transformer with Halogen ^{4,5}	10 W	500 W	400 W	300 W	Required	Reverse
	Neutral Optional Dimmer	Incandescent/ Halogen	5 W	500 W	400 W	300 W	Optional ⁸	Either		
			Dimmable Fluorescent Ballast 7	1 ballast	3.3 A (400 VA)	No Deratir	ng Required	Required	Forward	
			Hi-lume 1% 2-Wire (LTE) LED Drivers ³	1 driver	3.3 A (400 W) 20 drivers max	No Deratir	ng Required	Required	Forward	
			PHPM-PA/3F and GRX-TVI	1 interface	3 interfaces	No Deratir	ng Required	Required	Forward	

- 1 Designed for use with permanently installed LED, incandescent, tungsten halogen, or magnetic low-voltage transformers with halogen based lamps.
- ² See bulb list at www.lutron.com/ledfinder
- SSL-7A-2015 compliant when in forward-phase.
- When using magnetic (core and coil) low-voltage transformers with halogen lamps set the dimmer to forward-phase. When using with dimmable electronic (solid-state) low-voltage transformers set the dimmer to reverse-phase.
- Operation of a low-voltage circuit with lamps inoperative or removed may result in transformer overheating and premature failure. Lutron strongly recommends the following:
 - Do not operate low-voltage circuits without operative lamps in place.
 - Replace burned-out lamps as soon as possible.
 - Use transformers that incorporate thermal protection or fused transformer primary windings to prevent transformer failure due to overcurrent.
- When using the dimmer/switch to control MLV halogen fixtures, the maximum lamp wattage is determined by the efficiency of the transformer, with 70%–85% as typical. For actual transformer efficiency, contact either the fixture or transformer manufacturer. The total VA rating of the transformer(s) shall not exceed the VA rating of the dimmer/switch.
- Includes Philips Advance Mark 10₀ ballasts, Sylvania, Tu-Wire, and POWERSENSE₀.
- ⁸ Neutral is recommended for best dimming performance, if available, but is not required for this load type.

LUTRON SPECIFICATION SUBMITTAL

Job Name:	Model Numbers:
Job Number:	

3691112c 6 06.05.19

Advanced Programming Mode

Maestro dimmers and switches contain an Advanced Programming Mode (APM) that allows users to customize the control to meet their specific needs. For a detailed description of APM features and uses please refer to Lutron Application Note #703 (P/N 048703) at www.lutron.com

Available Advanced Features			
Feature	Description		
High-end trim	Select the maximum available light limit.		
Low-end trim	Select the minimum available light limit.		
Enable/Disable/Dim Indicator Lights	Select the brightness of the LEDs when the dimmer is Off.		
Delayed long fade-to-off	Set the length of time to wait before entering a long fade-to-off.		
Fade off time	Control the rate at which the dimmer fades from full intensity to Off when the tapswitch is pressed.		
Fade on time	Control the rate at which the dimmer fades from Off to preset intensity when the tapswitch is pressed.		
Protected preset	Set the intensity that the dimmer will always turn on to when the tapswitch is pressed once.		
Phase selectable	Select between forward-phase, reverse-phase, and phase auto-select. The default with no neutral connection is phase auto-select. The default with neutral connected is reverse-phase .		
Restore default	Select to return dimmer to its original factory settings		

Instructions for selecting phase:

- 1. Open the FASS.
- 2. Press and hold ... Close the FASS and continue to hold ... for 5 seconds.


Note: The current phase selection will illuminate:

IL7 (top, forward-phase)

IL4 (middle, phase auto-select-default with no neutral)*

IL1 (bottom, reverse-phase-default with neutral)

- 4. Press **1** to exit Phase Selection mode.



^{*}Phase auto-select defaults to reverse-phase unless the LED load cannot operate correctly. It will then switch to forward-phase automatically. Phase auto-select is only available when no neutral wire is connected.


LUTRON SPECIFICATION SUBMITTAL

Job Name:	Model Numbers:
Job Number:	

3691112c 7 06.05.19

Wiring Diagrams

Single-Pole Wiring




 $\ensuremath{\textbf{Note:}}$ Dimmer can be installed on the line side or load side

of the circuit.

Note: See Load Type and Capacity table on page 5 for

neutral wire requirements.

3-Way Wiring (Using MA-R or MSC-AD Companion Dimmer)



Continued on next page...


LUTRON SPECIFICATION SUBMITTAL

Job Name:	Model Numbers:
Job Number:	

Wallbox Controls

Wiring Diagrams (continued)

4-Way Wiring (Using MA-R or MSC-AD Companion Dimmer)



Note: Dimmer can be installed on the line side, load side, or in the middle of the circuit.

Note: See **Load Type and Capacity** table on page 5 for neutral wire requirements.

\$\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\textup{\text

UL and the UL logo are trademarks of UL LLC.

Mark 10 is a registered trademark of Philips Electronics North America Corporation.

POWERSENSE is a trademark of Community Light & Sound, Inc.

LUTRON SPECIFICATION SUBMITTAL

Job Name:	Model Numbers:
Job Number:	