


DEVICES THAT MAKE ENERGY MANAGEMENT AUTOMATIC



designed to be better.™

CONTROL THAT'S CONVENIENT, CONNECTED AND CODE-COMPLIANT.

New requirements for reducing energy consumption in commercial buildings are here. Standards such as CA Title 24 - 2013 and ASHRAE 90.1 - 2010, 2013 now require that at least 50 percent of all receptacles in designated spaces of a building be “controllable”— automatically turning themselves off and on as needed. Legrand is making it easy for installers to stay code-compliant with a full line of Plug Load controllable solutions. Devices that are so easy to understand, install and use, they take a load off your mind and a load off your customers' electric bills.



Control multiple dual- and half-controlled receptacles on the same circuit with feed-thru capability of the RF receptacle.

By installing the RF Receptacle into a building's branch wiring system and tying the low-voltage RF Signal Pack into an occupancy sensor and 24VDC power pack, you can control both lighting and receptacle usage.

DESIGNED WITH SIMPLICITY IN MIND

Whether you're upgrading an existing layout or configuring an entirely new system, P&S® Plug Load Controllable Devices help keep it simple. From code-required permanent markings that make them easy for end users to identify, to the ability to wirelessly control them via traditional occupancy sensors, these devices take installation, convenience and simplicity to a new level.

Designed to help improve energy efficiency and reduce costs for building owners, they're easy to install, reliable and compliant with all new energy codes and standards.



Can be wired to standalone or systems-based plug load control solutions

Back and side wire termination

Permanent markings on the face of the device for easy identification of the controlled receptacle

Feed-thru capability allows for downstream control of multiple receptacles

.032" brass, triple-wipe power contacts for lasting retention

cULus Fed Spec Listed

FOR RF RECEPTACLES ONLY

Simple, three-step binding process for wireless communication

Listed to standard UL498B for Receptacles with Integral Switching Means

LED indicator light on the receptacle indicates binding status as well as on/off status

Power symbol permanently marked on face of receptacles

Compliant with 2014 NEC, CA Title 24 - 2013, and ASHRAE 90.1 - 2010, 2013

RF26352CDW





RF RECEPTACLE AND SIGNAL PACK

Now you can control receptacles and lights with one seamless solution. The RF receptacle's built-in relay switch communicates with the signal pack, turning itself on and off according to the sensor's command. And because one signal pack can control multiple receptacles, it's a cost-effective and easy way to save energy and money.

SIGNAL PACK

Operates in a quiet 915 MHz band

Compliant with Part 15 of the FCC Rules

Low-profile design suits any décor

Mounting options: acoustic tile and keyhole

One Signal Pack can control multiple RF receptacles

Communication ranges of 150 feet possible with clear line of sight

Push-in locking tabs allow for convenient rotation of RF Signal Pack after installation to improve RF communication

HALF- AND DUAL-CONTROLLED PLUG LOAD RECEPTACLES

Our rugged Plug Load Controllable receptacles are designed to save energy and money. The permanent markings make it easy for end users to differentiate them. And the corrosion-resistant plated steel straps and high-strength nylon faces make them ideal for any commercial environment.



Permanently marked power symbols indicate dual- or half-controlled

Factory-broken split-circuit tab allows for half of the receptacle to be controlled

Plug Load Timer Receptacle

A smart, simple way to provide standalone plug load control to connected devices and equipment

P&S® Plug Load Controllable Devices

PART NO.	DESCRIPTION	RATINGS		COLORS	NEMA Config.
		A.	V.		
RF Plug Load Controllable Receptacles*					
RF26252CH*	Half-Controlled Receptacles	15	125	I, LA, W, GRY, BK, -, RED	5-15R
RF26352CH*		20	125		5-20R
RF26252CD*	Dual-Controlled Receptacles	15	125		5-15R
RF26352CD*		20	125		5-20R
RFP	RF Signal (Ceiling) Pack	White			
Plug Load Controllable Timers**					
PLT26251*	Heavy-Duty Spec Grade Plug Load Timer Receptacles	15	125	I, LA, W, GRY, BK, -, RED	5-15R
PLT26351*		20	125		5-20R
ADORNE® Plug Load Controllable Receptacles***					
ARCH152W10	Half-Controlled Receptacles Tamper-Resistant	15	125	White	5-15R
ARCH152M10				Magnesium	
ARCD152W10	Dual-Controlled Receptacles Tamper-Resistant	15	125	White	
ARCD152M10				Magnesium	
ARCD202W10	Dual-Controlled Receptacles Tamper-Resistant	20	125	White	5-20R
ARCD202M10				Magnesium	
Decorator Plug Load Controllable Receptacles***					
26252CH*	Half-Controlled Receptacles	15	125	I, LA, W, GRY, BK, -, BL, RED, GN	5-15R
26352CH*		20	125		5-20R
26252CD*	Dual-Controlled Receptacles	15	125		5-15R
26352CD*		20	125		5-20R
TR26262CH*	Half-Controlled Receptacles Tamper-Resistant	15	125	I, LA, W, GRY, -	5-15R
TR26362CH*		20	125	I, LA, W, GRY, BK, -	5-20R
TR26262CD*	Dual-Controlled Receptacles Tamper-Resistant	15	125	I, LA, W, GRY, -	5-15R
TR26362CD*		20	125	I, LA, W, GRY, BK, -	5-20R
Duplex Plug Load Controllable Receptacles***					
5262CH*	Half-Controlled Receptacles	15	125	I, LA, W, GRY, BK, -, RED, GN	5-15R
5362CH*		20	125		5-20R
5262CD*	Dual-Controlled Receptacles	15	125		5-15R
5362CD*		20	125		5-20R
TR5262CH*	Half-Controlled Receptacles Tamper-Resistant	15	125	I, LA, W, GRY	5-15R
TR5362CH*		20	125	I, LA, W, GRY, BK, -	5-20R
TR5262CD*	Dual-Controlled Receptacles Tamper-Resistant	15	125	I, LA, W, GRY, -	5-15R
TR5362CD*		20	125	I, LA, W, GRY, BK, -	5-20R

***COLOR DESIGNATION**

I	Ivory
LA	Light Almond
W	White
GRY	Gray
BK	Black
-	Brown
BL	Blue
RED	Red (made to order only)
GN	Green

***Third-Party Certification:** UL Listed to Standards 498B, 498, 244A, Fed Spec WC596, CSA C22.2 No. 42; RFP—Transmitter in compliance with Part 15 of FCC Rules, Class B. Tested to UL 244A

****Third-Party Certification:** UL Listed to Standards 498B, 498, 244A, Fed Spec WC596, CSA C22.2 No. 42, Title 24 Compliant

*****Third-Party Certification:** UL Listed, File Number E140596, Standard UL498, Fed Spec WC596, CSA Certified File Number LR16063, Standard CSA C22.2 No. 42 General Use Receptacles

P&S® Plug Load Controllable Devices — PlugTail®

PART NO.	DESCRIPTION	RATINGS		COLORS	NEMA Config.
		A.	V.		
Decorator Plug Load Controllable Receptacles — PlugTail					
PT26252SCCH*	Half-Controlled Receptacles	15	125	I, LA, W, GRY, -	5-15R
PT26352SCCH*		20	125	I, LA, W, GRY, BK, -	5-20R
PT26252CD*	Dual-Controlled Receptacles	15	125	I, LA, W, GRY, -	5-15R
PT26352CD*		20	125	I, LA, W, GRY, BK, -	5-20R
PTTR26262SCCH*	Half-Controlled Receptacles Tamper-Resistant	15	125	I, LA, W, GRY, -	5-15R
PTTR26362SCCH*		20	125	I, LA, W, GRY, BK, -	5-20R
PTTR26262CD*	Dual-Controlled Receptacles Tamper-Resistant	15	125	I, LA, W, GRY, -	5-15R
PTTR26362CD*		20	125	I, LA, W, GRY, BK, -	5-20R
Duplex Plug Load Controllable Receptacles — PlugTail					
PT5262SCCH*	Half-Controlled Receptacles	15	125	I, LA, W, GRY, -	5-15R
PT5362SCCH*		20	125	I, LA, W, GRY, BK, -	5-20R
PT5262CD*	Dual-Controlled Receptacles	15	125	I, LA, W, GRY, -	5-15R
PT5362CD*		20	125	I, LA, W, GRY, BK, -	5-20R
PTTR5262SCCH*	Half-Controlled Receptacles Tamper-Resistant	15	125	I, LA, W, GRY, -	5-15R
PTTR5362SCCH*		20	125	I, LA, W, GRY, BK, -	5-20R
PTTR5262CD*	Dual-Controlled Receptacles Tamper-Resistant	15	125	I, LA, W, GRY, -	5-15R
PTTR5362CD*		20	125	I, LA, W, GRY, BK, -	5-20R

***COLOR DESIGNATION**

I	Ivory
LA	Light Almond
W	White
GRY	Gray
BK	Black
-	Brown

Third-Party Certification:

cULus Listed, File Number E140596, Standard UL498, Federal Specification WC596



PlugTail Electrical Wiring Devices

With their factory-built connectors and six-inch leads, these code-compliant devices can literally be “plugged in,” making changeouts and future upgrades a snap.



Electrical Wiring Systems

P.O. Box 4822
Syracuse, NY 13221-4822
800.776.4035
www.legrand.us/PassandSeymour

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
905.738.9195
www.legrand.ca

For additional technical or application-specific information, call 800-223-4185 or visit our website at www.legrand.us/PassandSeymour. We're eager to put our expertise to work for you.

FOLLOW US

