

MPD3-11B



MPD3-11B Double Pushbutton

General Information

Extended Product Type	MPD3-11B
Product ID	1SFA611132R1106
EAN	7320500277270
Catalog Description	MPD3-11B Double Pushbutton
Long Description	Modular Double Pushbutton - Momentary - Flush/Flush - Green/Red Actuator, Black Indicator - NonIlluminated - No contact block - Lower Button: OFF - Upper Button: ON

Ordering

EAN	7320500277270
Minimum Order Quantity	10 piece
Customs Tariff Number	8536501999

Dimensions

Product Net Width	0.054 m
Product Net Height	0.03 m
Product Net Depth / Length	0.038 m
Product Net Weight	0.025 kg

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	0.11 m
Package Level 1 Height	0.03 m
Package Level 1 Depth / Length	0.15 m
Package Level 1 Gross Weight	0.025 kg
Package Level 1 EAN	7320500277270

Environmental

Ambient Air Temperature	Storage -30 ... +85 °C Operation -25 ... +70 °C
RoHS Status	Following EU Directive 2011/65/EU

Additional Information

Actuator Type	Flush/Flush
Bezel Material	Black plastic
Block	No contact block
Color	Green/Red Actuator
Degree of Protection	Front IP66 Terminals IP20
Function	Momentary
Illumination	Non-illuminated
Lower Button Color	Red
Lower Button Text	OFF
Mechanical Durability	2 million
Product Main Type	MPD3
Product Name	Double Pushbutton
Product Range	Modular
Product Type	MPD
RoHS Date	0635 4
Symbol / Text	ON/OFF
Upper Button Color	Green
Upper Button Text	ON

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	1SFC151007C02__
Declaration of Conformity - CE	2CMT2015-005452
Environmental Information	1SFC151010D0201
Instructions and Manuals	1SFC151011M0201
RoHS Information	2CMT2015-005452

Classifications

ETIM 4	EC002024 - Accessories for control circuit devices
ETIM 5	EC000221 - Front element for push button
ETIM 6	EC000221 - Front element for push button
ETIM 7	EC000221 - Front element for push button
Object Classification Code	S
UNSPSC	39121512

Categories

Low Voltage Products and Systems → Control Products → Pilot Devices → Modular Plastic Range

