


SLC

STEEL BATTERY UNIT

6V, 12V or 24V
160W-360W Capacity
120/347VAC Input

Approvals:
CSA Certified to C22.2 #141.15



DESCRIPTION

The SLC series of commercial steel battery units is designed to provide efficient and reliable emergency lighting. Utilizing a sturdy, all steel housing, the SLC presents a modern and unobtrusive design. On higher capacity models, the cabinet front is sloped to allow better internal access and superior low angle light distribution. The SLC series is available in 6VDC, 12VDC or 24VDC versions in a range of wattage capacities up to 360W, for 30 minutes duration. Units are typically supplied with two top mounted PAR18 or PAR36 type heads, however a wide range of head type, number and placement are available including MR16 type. The SLC can also accommodate a wide variety of options, including auto-testing self-diagnostics and remote testing.

MECHANICAL

- Rugged steel cabinet with ultraguard rust-coating
- 120VAC line cord supplied standard
- Universal spider knockout pattern and keyhole mounting slots stamped into back of cabinet
- Multiple conduit entry knockouts
- White powder coat finish standard, other finishes and Colours optional
- Lamp heads include PAR18 small style, PAR36 large style and die cast metal MR16 type
- Top head mounting is standard, side mount is optional

CIRCUITRY

- 120/347VAC 60Hz Input, field selectable
- High efficiency, rapid recovery, precision control charging system
- 6VDC, 12VDC or 24VDC emergency power output versions (as specified)
- Wattage capacities up to 360W
- 30 Minutes emergency power duration standard
- Momentary push button test switch
- Diagnostic/pilot LEDs for AC ON and CHARGE
- Fully automatic, current limited charger
- Line latched, low voltage protection
- Solid state design and construction
- Brownout and short circuit protection
- Temperature compensated
- Complete battery recharge in 24 hours
- Maintenance free, sealed lead acid battery
- Optional automatic-testing, self-diagnostic charger board:
 - Continuously monitors the operational status of the battery unit
 - Automatically performs battery and lamp load testing at preset intervals
 - Indicates any component malfunctions or automated test failures

ORDERING GUIDE

Series	Voltage	Wattage	Battery	Head/Lamp	Lamp	Colour	Options [†]
SLC	06 - 6VDC 12 - 12VDC 24 - 24VDC	See model rating below	Blank - Regular HP - High power factor	0 - No Heads 1N - One PAR18 2N - Two PAR18 1L - One PAR36 2L - Two PAR36	1S - One MR16 2S - Two MR16 1M - One MR16 2M - Two MR16	See lamp list below	WH - White (standard) BK - Black GY - Grey AT, TD*, LD, BD, V, A, ACTB, DCTB, FD4, RDS*, OBM, TLP, CT, TP, MTS, WG, IRT, IRC

[†] For detailed options descriptions, please consult the options page. * Specify AC voltage.

QUICK SHIP: Not all products are Quick Ship. To view our Quick Ship qualified products, please consult our Quick Ship Product Guide at stanprols.com/quick-ship-product-guide. Product availability is subject to change without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.

LAMP SELECTION

	6 Volts	12 Volts	24 Volts
PAR18 - Small head or LED Lamp			
LED	3WLJ, 4WLJ, 5WLA	3WLJ, 4WLJ, 5WLA, 6WLA, 7WLA	4WLR, 5WLA, 6WLA, 7WLA
Quartz halogen	08WQ, 10WQ, 12WQ	10WQ, 12WQ	12WQ
Tungsten	09WT	09WT, 12WT, 18WT	09WT, 18WT
MR16 - Small head c/w MR16 or LED Lamp			
LED	4WLR, 5WLA	4WLR, 5WLA, 6WLA, 7WLA	4WLR, 5WLA, 6WLA, 7WLA
Quartz halogen	08WQ, 10WQ, 12Q, 20WQ	08WQ, 10WQ, 12WQ, 20WQ, 35WQ	10WQ, 12WQ, 20WQ
PAR36 - Large head			
Quartz halogen	08WQ, 10WQ, 12WQ, 20WQ	10WQ, 12WQ, 20WQ, 35WQ	12WQ
Tungsten	09WT, 18WT, 25WT	09WT, 18WT, 25WT	09WT, 18WT, 25WT
Quartz sealed beam	08WSBQ, 10WSBQ, 12WSBQ, 20WSBQ	08WSBQ, 12WSBQ	70WSBQ
Tungsten sealed beam	08WSBT, 09WSBT, 18WSBT	25WSBT	N/A

Note: Due to cabinet/space limitations, not all options are available for all models in any given combination. Please consult with your factory representative regarding specific options and exact cabinet dimension information.

MODEL RATINGS

Model	Voltage	Wattage capacities			
		30 min.	60 min.	90 min.	120 min.
SLC-06160	6V	160	80	53	40
SLC-06180	6V	180	90	60	45
SLC-12160	12V	160	80	53	40
SLC-12200	12V	200	100	66	50
SLC-12250	12V	250	125	83	62
SLC-12360	12V	360	180	120	90
SLC-24144	24V	144	72	48	36
SLC-24200	24V	200	100	66	50
SLC-24320	24V	320	160	106	80