

# VTE4-L

## LED VAPOUR TIGHT LINEAR FIXTURE

IP RATING  
**65**



### Approvals:

cULus Certified

Suitable for damp & wet locations

### DESCRIPTION

A luminaire ideal for a variety of industrial, commercial and residential applications. Installed either indoors or outside, the VTE4-L provides superior light distribution. Intended for applications where moisture and/or dust may be present.

### HOUSING

- Lightweight, flexible and durable polycarbonate construction makes the luminaire highly impact resistant
- The housing is sealed with a uniform gasket that blocks the ingress of moisture and dust and reinforced snap clips lock the luminaire together
- As well, the UV stabilized polycarbonate housing and lens with LED diffusing pigment are impervious to rust or rot and are unaffected by extreme temperatures
- Row mount aligners molded into housing ends
- Sealed strain relief/cable gland kit included

### SPECIFICATIONS AND CERTIFICATIONS

- Easy to clean and service
- LED technology for long term energy savings
- IP65, UL suitable for wet locations
- 0-10V dimming standard
- 80+ CRI
- Ambient temperature: -20°C to +35°C
- Colour consistency (SDCM) is 3 step MacAdam ellipse
- Meets requirements of ICES-005 issue 4 for class A products

### MOUNTING

Stainless steel mounting hardware for wall, ceiling or suspended mounting.

66  
wet  
location



quick  
ship


5  
yr  
warranty



Not all products are qualified on the DLC QPL. To view our DLC qualified products, please consult the DLC Qualified Products List at [www.designlights.org/search](http://www.designlights.org/search).



### DIMENSIONS



### ORDERING GUIDE

Series	Lamp type	Lumen package delivered	Voltage	Colour temperature
VTE4	L - LED	S3 - 5200 lumens (40W) S4 - 7900 lumens (60W)	W - 120-277V H - 347V	40K - 4000K 50K - 5000K