



# PL-T Triple 4-Pin Base

## PL-T 26W/830/A/4P/ALTO

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

### Product data

General Information		Operating and Electrical	
Cap-Base	GX24Q-3 [ GX24q-3]	Power (Rated) (Nom)	26 W
LSF Preheat 2000 h Rated	99 %	Lamp Current (Nom)	0.335 A
LSF Preheat 4000 h Rated	98 %		
LSF Preheat 6000 h Rated	97 %		
LSF Preheat 8000 h Rated	90 %		
Light Technical		Temperature	
Color Code	830 [ CCT of 3000K]	Design Temperature (Nom)	28 °C
Initial lumen (Nom)	1750 lm		
Luminous Flux (Rated) (Nom)	1750 lm		
Color Designation	Warm White (WW)		
Correlated Color Temperature (Nom)	3000 K		
Luminous Efficacy (Rated) (Nom)	64.8 lm/W		
Color Rendering Index (Nom)	>80		
LLMF 2000 h Rated	92 %		
LLMF 4000 h Rated	88 %		
LLMF 6000 h Rated	85 %		
LLMF 8000 h Rated	84 %		
LLMF 12000 h Rated	81 %		
		Controls and Dimming	
		Dimmable	Yes
		Mechanical and Housing	
		Cap-Base Information	4P
		Approval and Application	
		Energy Efficiency Label (EEL)	B
		Mercury (Hg) Content (Nom)	1.4 mg
		Product Data	
		Order product name	PL-T 26W/830/A/4P/ALTO
		EAN/UPC - Product	046677268237
		Order code	458257

PL-T Triple 4-Pin Base


Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	927910983050
Net Weight (Piece)	64.000 g

ILCOS Code	FSM-26/30/1B-E-GX24q=3
------------	------------------------

Warnings and Safety

- Lamp contains mercury. Manage in Accord with Disposal Laws. See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050


Dimensional drawing




PL-T ALTO 26W/830/4P A

Product	D (max)	A (max)	B (max)	C (max)
PL-T 26W/830/A/4P/ALTO	41 mm	86.7 mm	111.0 mm	126.7 mm

Photometric data





Lightcolor /830




Lightcolor /830

PL-T Triple 4-Pin Base

Lifetime



Lumen Maintenance 3 h and 12 h cycle



Life Expectancy 3 h cycle

Life Expectancy 12 h cycle

