

**A**



### TYPE ACO

#### Features

- Manufactured from high strength aluminum alloy
- Pin is knurled
- Pin is off center
- Chamfered barrel
- UL Listed and CSA Certified for 600 volts, 90° C
- Clearly marked with wire size and die index for IlSCO tools, proper number and location of crimps
- Prefilled with DE-OX
- Color coded end caps inserted in barrel
- Supplied with insulating cover

#### Benefits

- Provides maximum conductivity and excellent crimping characteristics
- Permits greater surface contact
- Allows connectors to be rotated for parallel applications. Multiple conductor lugs hole spacing does NOT permit insertion of straight pin connectors
- Provides easy conductor insertion
- Ensures reliability for aluminum or copper conductors
- Provides easy identification and tooling recommendation
- Prevents oxides from forming
- Prevents foreign materials from entering the connector prior to usage and color code identifies the proper compression die
- Eliminates taping



Lug Will Not Accept Straight Pin      Offset Pin Design - Application

Catalog Number	Wire Size	Die Color Code	Die Index	Pin Size	Dimensions				O.D.	I.D.
					F	C	A	D (cover)		
ACO-2/0	2/0	White	12	#1	2-7/32	1-3/8	11/32	2	55/64	7/16
ACO-3/0	3/0	White	12	1/0	2-19/32	1-3/8	3/8	2	55/64	1/2
ACO-4/0	4/0	White	12	2/0	2-19/32	1-3/8	27/64	2	55/64	35/64
ACO-250	250kcmil	Brown	14	3/0	2-5/8	1-13/32	15/32	2-1/4	1-7/64	19/32
ACO-300	300kcmil	Brown	14	4/0	2-3/4	1-13/32	17/32	2-1/4	1-7/64	21/32

CONTINUED ON NEXT PAGE.

Cover and connector are packaged together (ONLY).

### Tooling Information

Catalog Number	ILSCO				Burdny						Thomas & Betts		Color Code
	ILC-12-N ILC-12H-N Die No. No. of Crimps	ILCB-12-N Die No. No. of Crimps	ILC-15H Die No. No. of Crimps	IDT-12-N Die No. No. of Crimps	Y750 Family Die Index No. of Crimps	Y-35 Die Index No. of Crimps	Y-39 Die Index No. of Crimps	Y-45 Die Index No. of Crimps	Y-46 Die Index No. of Crimps	Y644M Dieless No. of Crimps	13642 12 Ton Die Index No. of Crimps	13100A 15 Ton Die Index No. of Crimps	
ACO-2/0	ILD-12 (1)	ILD-12 (1)	ILD-12 (1)	(1)	298 (2*)	298 (2*)	298 (2*)	298 (2*)	298 (2*)	(1)	66H (2)	66 (2)	White
ACO-3/0	ILD-12 (1)	ILD-12 (1)	ILD-12 (1)	(1)	298 (2*)	298 (2*)	298 (2*)	298 (2*)	298 (2*)	(1)	66H (2)	66 (2)	White
ACO-4/0	ILD-12 (1)	ILD-12 (1)	ILD-12 (1)	(1)	298 (2*)	298 (2*)	298 (2*)	298 (2*)	298 (2*)	(1)	66H (2)	66 (2)	White
ACO-250	ILD-14 (1)	ILD-14 (1)	ILD-14 (1)	(1)	299 (2*)	299 (2*)	299 (2*)	299 (2*)	299 (2*)	(1)	87H (2)	87 (2)	Brown
ACO-300	ILD-14 (1)	ILD-14 (1)	ILD-14 (1)	(1)	299 (2*)	299 (2*)	299 (2*)	299 (2*)	299 (2*)	(1)	87H (2)	87 (2)	Brown

All wire sizes, unless noted otherwise, are American Wire Gauge (AWG)

\* Overlap Crimps

See stuffer sheet for complete information on tooling.

Tested to UL 486A/B, UL File E62525