# CSRP-2L/CSRP12-2L

# **RUNNING MAN STEEL COMBO "WAY2GO"**

# CSRP-2L

6VDC 36W Battery Capacity (Over 4 hours Duration Standalone Unit) 2 x 2W Crisp White LED Heads

# CSRP12-2L

12VDC 72W Battery Capacity (Over 8 hours Duration Standalone Unit) 2 x 2.5W Crisp White LED Heads



## Approvals:

CSA Certified to C22.2 #141.15, C860

Energy Verified

## DESCRIPTION

The commercial CSRP-2L/CSRP12-2L features a slim profile that prevents light leaks. Easy to install design, available in 6VDC 36W with over 4 hours duration and 12VDC 72W with over 8 hours duration.

#### **CIRCUITRY**

- 120/347V AC 60Hz input, field selectable
- 1.9W power consumption on AC input for LED exit portion of combination sign
- LED Emergency DC wattages as follows: 6VDC = 0.9W; 12VDC = 1.8W
- 6VDC 36W or 12VDC 72W emergency power output versions (as specified)
- Momentary push button test switch
- Pilot LED for AC ON and CHARGE
- · Fully automatic, current limited charger
- Solid state design and construction
- Brownout and short circuit protection
- Temperature compensated
- Maintenance free, sealed lead acid battery


#### **MECHANICAL**

- 20 Gauge steel construction
- Slide out faceplates and backplates for rapid and simple installation
- Universal spider knockout pattern stamped into backplate for junction box mounting
- Universal models include ceiling or end mount, field installable canopy kit c/w spider plate
- · Front head mounting is standard
- Multiple conduit entry knockouts
- White powder coat finish standard
- PAR18 small style, high impact thermoplastic heads
- LED heads with limited lifetime warranty\*

# **DIMENSIONS**



Type RMSM - PAR18 Thermoplastic









Comes standard with three pictogram legends for direction selection.

# **ORDERING GUIDE**



<sup>\*</sup> For complete warranty details, please see our terms and conditions in our website

# MODEL RATING

		Wattage capacities			
Model	Voltage	30 min.	60 min.	90 min.	120 min.
CSRP-2L	6V	36	18	12	9
CSRP12-2L	12V	72	36	24	18

