


IG5262, IG5362

Isolated ground receptacle with durable, solid construction.

Featuring an impact-resistant nylon face, plated steel strap, and triple-wipe brass power contacts, these receptacles are built tough. They also feature our patented screw-pressure plate back wire clamp on ground for fast installation.



Features & Benefits

IG symbol and "Isolated Ground" markings for easy I.D. and circuit delineation.

Triple-wipe brass contacts ensure lasting, positive contact with plug blades.

High-impact resistant nylon face resists impacts and scrapes.

Corrosion-resistant plated steel strap.

Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

Plastic barrier isolates grounding terminal from mounting strap and metal boxes.

Side and internal screw-pressure-plate back wire capability with #14 – #10 AWG copper or copper-clad, solid or stranded wire.

Auto-ground clip assures positive ground.

IG5262

Field Uses/Vertical Markets

- Education
- Office
- Institutional
- Hospitality/Lodging
- Retail



Pass & Seymour

TVSS & Isolated Ground Devices Specification Grade IG 15 & 20A, 125V

Ordering Information

Catalog Number	Rating A. V.	NEMA Config. No.	Color
Duplex Receptacles Back & Side Wire			
IG5262	15 125	5-15R	Orange
IG5262-I	15 125	5-15R	Ivory
IG5262-GRY	15 125	5-15R	Gray
IG5262-RED	15 125	5-15R	Red
IG5262-LA	15 125	5-15R	Light Almond
IG5362	20 125	5-20R	Orange
IG5362-I	20 125	5-20R	Ivory
IG5362-W	20 125	5-20R	White
IG5362-GRY	20 125	5-20R	Gray
IG5362-RED	20 125	5-20R	Red
IG5362-LA	20 125	5-20R	Light Almond



NEMA
5-15R



NEMA
5-20R

For more information on these and other P&S products refer to our Catalog or visit our web site.

SF1306R1 — Updated June 2006 — For latest specs visit www.legrand.us/passandseymour

TVSS & Isolated Ground Devices Specification Grade IG 15 & 20A, 125V



Pass & Seymour

Technical Specifications

3rd Party Compliance

UL Listed, File Number E140596, Standard UL498.
Federal Specification WC596.
CSA Certified.

Performance

Electrical


Dielectric Voltage	Withstands 2000V minimum
Maximum Working Voltage	250V
Current Interrupting	Certified for current interrupting at full-rated current
Temperature Rise	Max 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current

Mechanical

Terminal Identification	Terminal Identification in accordance with UL498 (Brass, White, Green)
Terminal Accommodation	#14 AWG – #10 AWG copper conductor only
Product Identification	Ratings are a permanent part of the device

Environmental

Flammability	UL94 V2
Operating Temperature	Maximum continuous +60°C, minimum -40° (without impact)



Dimensions for
15 & 20 Amp

Materials

Face	Nylon	Ground Screw	#8 Hex Tri-Drive Steel
Back Body	PVC	Assembly Drive Screw	Plated Steel
Line Contacts	.032 688 Brass	Auto-Ground Clip	Steel
Mounting Strap	.042 Plated Steel	Mounting Screws	Tri-Drive Steel
Ground Contacts	.040 260 Brass	Ground Wire Pressure Plate	Brass
Pressure Plate	.080 Steel		
Terminal Screws	#8 Tri-Drive Steel		

Warranty

1 Year