



PRODUCT SEARCH

[> SUPP](#)  
[> DIST](#)[HOME](#)[WHAT'S NEW](#)[SERVICE / SUPPORT](#)[WHERE TO BUY](#)[INSTRUCTION MANUALS](#)[CO](#)**PRODUCTS**[Hand Tools](#)[Holemaking](#)[Bending](#)[Fishing](#)[Cable Pulling](#)[Wire & Cable Termination](#)[Voice Data Video](#)[Testing & Measurement](#)[Storage & Material Handling](#)[Hydraulic Pumps &  
Miscellaneous](#)**Name:**

ACTUAL HOLE SIZE 2-1/2 in. 63.5 mm HOLE DIAMETER ISO: ISO-63  
copper pipe: 2"

**Cat #:**

925-2-1/2

**UPC #:**

10162

**Spec:****Description:**

Made of high-speed steel. Lasts 10 times longer than standard hole saws. Precision-ground teeth cut smooth, burr-free holes with ease. Durability and speed provide low cost per hole. Split-point pilot drill prevents "walking" - makes accurate hole placement easy. Spring-loaded slug ejector saves time. No tool required to change cutter sizes. Less chance of broken teeth because the saw body is machined out of solid, high-speed steel.