



PRODUCT SEARCH

[HOME](#)[WHAT'S NEW](#)[SERVICE / SUPPORT](#)[WHERE TO BUY](#)[INSTRUCTION MANUALS](#)[CO](#)**TERMINATION**[Hand Tools](#)[Holemaking](#)[Bending](#)[Fishing](#)[Cable Pulling](#)[Wire & Cable Termination](#)[Voice Data Video](#)[Testing & Measurement](#)[Storage & Material Handling](#)[Hydraulic Pumps & Miscellaneous](#)**Name:**

Reel Stand 13" - 28" (330.2 - 711.2 mm)

Cat #:

687

UPC #:

17076

Spec:

Size: 14-1/2" x 20" (368.3 x 508 mm) base; 28" (711.2 mm) maximum height Capacity: 2,500 lbs. (1134 kg) each, 28" - 56" (711.2 x 1422 mm) reel diameter Weight: 25 lbs. (11.3 kg)

Description:

Wide welded steel base for added stability.

- Roller bearings fit in the spindle groove to keep the spindle in place and turning freely.
- Two stands and a spindle are required for a complete set-up.

