

Multi-Bit Cushion-Grip Screwdrivers/Nut Drivers

Ratcheting Multi-Bit Screwdriver/Nut Driver

- High torque 3-way ratcheting mechanism, forward, reverse and locked positions for tough applications
- Interchangeable shaft holds six universal tips; converts to three nut driver sizes and one hex driver
- Strong, heat-treated nut drivers for improved torque



32558









Cat. No.	Nut Driver Sizes	Phillips Bits	Slotted Bits	Square Bits	Hex Bits	Shank Length	Handle Color	Overall Length	Weight
32558	1/4", 5/16", 3/8"	#1, #2	1/4" (6.4 mm), 3/16" (4.8 mm)	#1, #2	3/8"	2.953" (75 mm)	Yellow/Black	7.891" (200.4 mm)	0.48 lb (0.22 kg)

6-in-1 Ratcheting Stubby Screwdrivers

Ratcheting mechanism allows user to work faster with more efficiency



32593









Cat. No.	Nut Driver Sizes	Phillips Bits	Slotted Bits	Square Bits	Shank Length	Handle Color	Overall Length	Weight
32593	1/4", 5/16"	#1, #2	1/4" (6.4 mm), 3/16" (4.8 mm)	_	1.297" (32.9 mm)	Yellow/Black	3.5" (88.9 mm)	0.10 lb (0.05 kg)
32594	1/4", 5/16"	#2	3/16" (4.8 mm)	#1, #2	1.297" (32.9 mm)	Yellow/Black	3.5" (88.9 mm)	0.10 lb (0.05 kg)

Heavy-Duty Multi-Bit Screwdriver/Nut Driver

- Superior torque for tough applications
- Interchangeable shaft holds six universal tips; converts to three nut driver sizes and one hex driver
- Strong, heat-treated nut drivers for improved torque



32557










Cat. No.	Nut Driver Sizes	Phillips Bits	Slotted Bits	Square Bits	Hex Bits	Shank Length	Handle Color	Overall Length	Weight
32557	1/4", 5/16", 3/8"	#1, #2	1/4" (6.4 mm), 3/16" (4.8 mm)	#1, #2	3/8"	2.953" (75 mm)	Yellow/Black	7.891" (200.4 mm)	0.48 lb (0.22 kg)



57









Multi-Bit Cushion-Grip Screwdrivers/Nut Drivers

Multi-Bit Screwdriver/Nut Drivers

Integrated screwdriver/nut driver shaft holds popular tips and converts nut driver sizes



32476











Cat. No.	Nut Driver Sizes	Phillips Bits	Slotted Bits	Square Bits	TORX® Bits	Shank Length	Handle Color	Overall Length	Weight
32476	5/16"	#1, #2	1/4" (6.4 mm), 3/16" (4.8 mm)	_	_	4" (101.6 mm)	Yellow/Black	7.75" (196.9 mm)	0.48 lb (0.22 kg)
32477	5/16", 1/4"	#1, #2	1/4" (6.4 mm), 3/16" (4.8 mm)	#1, #2	T10, T15	4" (101.6 mm)	Yellow/Black	7.75" (196.9 mm)	0.50 lb (0.23 kg)
32500	3/8", 5/16", 1/4"	#1, #2	1/4" (6.4 mm), 3/16" (4.8 mm)	#1, #2	T10, T15	3" (76.2 mm)	Yellow/Black	7.25" (184.2 mm)	0.50 lb (0.23 kg)

TORX® is a registered trademark of Acument Intellectual Properties, LLC

Stubby Multi-Bit Screwdriver/Nut Driver

- Compact design features standard 1-1/4" (32 mm) shaft allowing easy access to tight work spaces
- Shaft holds four universal tips and converts to two nut driver sizes











Cat. No.	Nut Driver Sizes	Phillips Bits	Slotted Bits	Square Bits	Shank Length	Handle Color	Overall Length	Weight
32561	1/4", 5/16"	#1, #2	3/16" (4.8 mm), 1/4" (6.4 mm)	_	1.266" (32.2 mm)	Yellow/Black	3.406" (86.5 mm)	0.16 lb (0.07 kg)
32562	1/4", 5/16"	#2	3/16" (4.8 mm)	#1, #2	1.266" (32.2 mm)	Yellow/Black	3.406" (86.5 mm)	0.16 lb (0.07 kg)

Extended-Reach Multi-Bit Screwdrivers/Nut Drivers

- Interchangeable shaft holds four universal tips and converts to two nut driver sizes
- Extended shafts and blades provide 39% longer reach
- Small diameter shaft for comfortable grip and quick, easy turning



32559







