

 **0-10V fluorescent dimmer** (current sink control)

 (also for 0-10V LED drivers)

(small control)

**Slide-to-off dimmer**

Single-pole	NTFTV- <b>XX</b> <sup>1</sup>
30 mA max control current	

Control provides dimming signal only. For dimming with on/off switching, **use with Lutron Power Pack**: PP-120H, PP-277H, or PP-347H.

Consult ballast manufacturer for specific ballast current draw to determine maximum number of ballasts per control.

For information on using Lutron dimmers to control Advance Mark 7 dimming ballasts, visit [www.lutron.com/advance](http://www.lutron.com/advance); Universal dimming ballasts, visit [www.lutron.com/universal](http://www.lutron.com/universal).

No derating required if ganged.

For compatible 0-10V LED drivers by others, visit [www.lutron.com/LED](http://www.lutron.com/LED).

 **Tu-Wire® fluorescent dimmers**

(small controls)

**Slide-to-off dimmers**

Single-pole	NTFTU-5A- <b>XX</b> <sup>1</sup>
120V 5A	
Single-pole*	NTFTU-5A-277- <b>XX</b> <sup>1</sup>
277V 5A	

Also compatible with Advance Mark 10 ballasts, for further information visit [www.lutron.com/advance](http://www.lutron.com/advance).

For information on use with Universal and OSRAM ballasts, contact Technical Support at 1.800.523.9466; Universal dimming ballasts visit [www.lutron.com/universal](http://www.lutron.com/universal).

**XX**<sup>1</sup>: Architectural matte color codes, see pg. 26 (1-gang wallplate included)

**Slide-to-off dimmers**



- Higher capacity dimmers require larger heat sink behind wallplate
- Slide up to brighten, down to dim
- Measures 4.56 in x 4.56 in
- Requires large wallplate
- Most can fit in a 1-gang electrical backbox

 **Incandescent/halogen dimmers** (large controls)

**Slide-to-off dimmers**

Single-pole	NT-1500- <b>XX</b> <sup>1</sup>
120V 1500W	
Single-pole	NT-2000- <b>XX</b> <sup>1</sup>
120V 1920W	

NT-2000 dimmers must be ganged with no fins broken. See ganging and derating on pg. 179 for further information.

NT-2000 requires a 2-gang electrical backbox.

 **Magnetic low-voltage dimmers** (large controls)

**Slide-to-off dimmers**

Single-pole	NTLV-1500- <b>XX</b> <sup>1</sup>
1500 VA (1200W)	

The stated VA (Volt-Ampere) rating includes the magnetic transformer heat losses and the lamp load. The stated W (Watt) rating is the maximum lamp wattage based on assumed 20% transformer loss.

All models must be derated if ganged, unless otherwise noted, see pg. 179.

\* **Requires neutral wire connection.**