



KLU225

by Burndy
Catalog ID: KLU225

Prop 65 Notice

Copper Terminal, Offset Tongue, 1 Hole, 2-4/0 AWG (Str), 5/16" Stud, 1 Screw.

Features: Convenient Range-Taking Design: One Conductor Accommodates Several Conductor Sizes, High Conductivity Copper Alloy: Long Lasting Reliable Contact, Compact Design: Easy To Use, Reduces Labor Time, Slot Robertson Screw, Hex Head/Hex Socket Bolt: No Special Installation Tools Required, Eliminates Over-Torquing/Potential Conductor Damage, High Copper Alloy Terminal With Offset Tongue For Joining A Wide Range Of Cable To Equipment Pads Or Bar, Easy To Install With Screwdriver Or Wrench, Connector Is Reusable, Plain Copper Finish, For Copper Cable, Wire Strip Length: 1-5/16 IN, Stud/bolt Size: 7/16 IN, Stud/bolt Hole Size: 5/16 IN, Dimension N: 0.51 IN, Set Screw Type: Hex Socket, Installation Torque: 204 IN-LB, Length: 2.56 IN, Width: 0.99 IN, Tongue Width : 1 IN, Dimension B: 0.77 IN, Dimension K: 0.33 IN, Dimension T: 0.12 IN

Product Details

General

Application	For Joining A Wide Range Of Copper Cable To Equipment Pads Or Bar
Connector Type	Terminal
Hardware Type	7/16 UNF Socket/HexScrew
Installation Torque Recommended in-lb	120
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Sub Brand	SCRULUG
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	781810351413

Dimensions

Dimension - B Length fraction	15/16 in
Dimension - B Length inch	0.94 in
Dimension - Hole Size inch	0.34 in
Dimension - Hole Size mm	9 mm
Dimension - L Length Overall mm	65 mm
Dimension - Length Overall inch	2.55 in
Dimension - N inch	0.51 in
Dimension - Pad Width inch	0.99 in

Dimension - Screw Size inch	7/16
Dimension - Strip Length inch	1-5/16
Dimension - Stud Size inch	5/16

Conductor Related

Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	2 AWG-4/0 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)