

## GENERAL INFORMATION

12 V 7.2 Ah is a general purpose battery with 3 to 5 years in standby service or more than 400 cycles at 50 % depth of discharge in cycle service.

## 57337 - 12 V 7.2 Ah

## SPECIFICATIONS

Nominal Voltage:	12 V
Nominal Capacity (20 hrs):	7.2 Ah
Dimensions	
Total Height:	101 mm (3 <sup>11</sup> / <sub>32</sub> in.)
Container Height:	95 mm (3 <sup>3</sup> / <sub>4</sub> in.)
Length:	151 mm (5 <sup>15</sup> / <sub>16</sub> in.)
Width:	65 mm (2 <sup>9</sup> / <sub>16</sub> in.)
Weight:	Approx 2.18 Kg (4.80 lbs)
Container Material:	UL94HB ABS UL94HB ABS
Internal Resistance (25 °C, 77 °F):	~17 mΩ
Discharge Capacity Under Different Temperatures	
40 °C:	~102 %
25 °C:	~100 %
0 °C:	~85 %

## CHARACTERISTICS

### Capacity 25 °C / 77 °C

20 hrs @ 0.36 A:	7.2 Ah
5 hrs @ 1.15 A:	5.76 Ah
1 hrs @ 4.32 A:	4.32 Ah
1 C @ 7.2 A:	3.6 Ah

### Charging Voltage (25 °C, 77 °F)

Standby Use:	13.65 V ± 0.15 V
Cycle Use:	14.7 V ± 0.3 V


Max Discharge Current: 90 A (5 sec)

Max Charging Current: 2.16 A


### Self-Discharge Residual Capacity (25 °C, 77 °F)

After 3 Months:	~90 %
After 6 Months:	~82 %
After 12 Months:	~70 %


## DISCHARGE CURRENT VS TIME



## DISCHARGE CHARACTERISTICS 25 °C (77 °F)




## DIMENSIONS



Tolerances are +/-1/32 in. (+/-1mm) and +/-3/32 in. (+/-2mm) for height dimensions.

## TERMINAL



Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

August 28, 2014

