



# T8 900 Series Rapid Start

## F32T8/TL950 SLV

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

### Product data

General Information	
Cap-Base	G13 [ Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	15000 h
Life to 50% Failures Preheat (Nom)	20000 h
Life 3-Hr Start [Hrs]	20000 h
Life 12-Hr Start [Hrs]	20000 h
Light Technical	
Color Code	TL950 [ CCT of 5000K (950)]
Luminous Flux (Nom)	2000 lm
Color Designation	TL950
Lumen Maintenance 10000 h (Nom)	84 %
Lumen Maintenance 2000 h (Nom)	90 %
Lumen Maintenance 5000 h (Nom)	89 %
Design Mean Lumens	1860 lm
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (Rated) (Nom)	63.9 lm/W
Color Rendering Index (Nom)	98

Operating and Electrical	
Power (Rated) (Nom)	31.3 W
Lamp Current (Nom)	0.265 A
Voltage (Nom)	139 V


Controls and Dimming	
Dimmable	Yes

Approval and Application	
Energy Efficiency Label (EEL)	B
Mercury (Hg) Content (Nom)	5.0 mg

Product Data	
Order product name	F32T8/TL950 SLV
EAN/UPC - Product	046677209056
Order code	927942009520
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927942009520
Net Weight (Piece)	137.500 g

# T8 900 Series Rapid Start

## Dimensional drawing





### Product

F32T8/TL950 SLV

### F32T8/TL950

## Photometric data



### Lightcolor /950

### Lightcolor /950

