

KSU23

by Burndy
Catalog ID: KSU23

Prop 65 Notice

Tin-plated, high strength copper alloy SERVIT with spacer. Spacer separates dissimilar conductors and provides long contact length that prevents high pressure point contacts between run and tap conductors, 1.48 IN L.

Features: Tin-Plated, High Strength Copper Alloy SERVIT With Spacer, Spacer Separates Dissimilar Conductors And Provides Long Contact Length That Prevents High Pressure Point Contacts Between Run And Tap Conductors, Use Of PENETROX Joint Compound Recommended With Aluminum And ACSR, Conductor Type: Run: ACSR, 5005, AAAC, Commercial Stranded Aluminum, Commercial Stranded And Solid Copper, Tap: ACSR, 5005, AAAC, Commercial Stranded Aluminum, Commercial Stranded And Solid Copper, Steel (Nominal Diameter), Installation Torque: 275 IN-LB, Width: 0.59 IN, Cross Flats: 0.81 IN, Length: 1.48 IN



Product Details

General

Application	For All Combinations Of Copper, Aluminum, ACSR, AAAC, 5005, And Steel
Material	Copper
Plated	Y
Plating Type	Tin Plated
Sub Brand	UNIVERSAL SERVIT
Trade Name	SERVIT®
Type	KSU, Universal
UPC	781810036006

Dimensions

Dimension - Length Overall inch	1.56
Width	0.59 in

Conductor Related

Conductor - ACSR Str Run Range	3 AWG - 2 AWG
Conductor - ACSR Str Tap Range	6 AWG - 2 AWG
Conductor - AL Str Run Range	8 AWG - 2 AWG
Conductor - AL Str Tap Range	8 AWG - 2 AWG
Conductor - Copper Str Run Range	8 AWG - 2 AWG
Conductor - Copper Str Tap Range	8 AWG - 2 AWG

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)