

MR11 AND MR16 LAMPS are well suited to a variety of applications that require directional lighting of low to medium intensity.

MR11 (G4)



MR16 (GX5.3)



MR16 (E26)



Order code	Description	ANSI code	Watts (W)	Base	Volts (V)	Colour temp. (K)	Beam angle (°)	Beam spread	CBCP (cd)	Average life (hrs)	Initial lumens (lm)	Case qty
MR11 - Cover Glass												
MOL : 1 3/8 in. (35 mm) Dia. : 2 in. (51 mm)												
55093	H5MR11/NSP/CG/2M/G4/6V/STD	N/A	5	G4	6	2 900	10	Narrow Spot	700	2 000	45	100
55094	H10MR11/NSP/CG/2M/G4/6V/STD	N/A	10	G4	6	2 900	10	Narrow Spot	700	2 000	80	100
55054	H5MR11/NSP/CG/2M/G4/12V/STD	N/A	5	G4	12	2 900	10	Narrow Spot	700	2 000	45	120
50900	H20MR11/NFL/CG/2M/G4/12V/FTC STD	FTC/CG	20	G4	12	2 900	17	Narrow Flood	1 600	2 000	200	200
51050	H20MR11/MFL/CG/2M/G4/12V/FTD STD	FTD/CG	20	G4	12	2 900	27	Flood	600	2 000	200	120
50901	H35MR11/NFL/CG/2M/G4/12V/FTF STD	FTF/CG	35	G4	12	2 900	18	Narrow Flood	3 000	2 000	345	200
50899	H35MR11/MFL/CG/2M/G4/12V/FTH STD	FTH/CG	35	G4	12	2 900	28	Flood	1 300	2 000	345	120
MR11 - Open												
MOL : 1 3/8 in. (35 mm) Dia. : 2 in. (51 mm)												
50894	H20MR11/NSP/AX/G4/12V/FTB STD	FTB	20	G4	12	2 900	11	Narrow Spot	5 000	2 000	200	200
50895	H20MR11/NFL/AX/G4/12V/FTC STD	FTC	20	G4	12	2 900	19	Narrow Flood	1 600	2 000	200	120
51054	H20MR11/MFL/AX/G4/12V/FTD STD	FTD	20	G4	12	2 900	29	Flood	600	2 000	200	120
50897	H35MR11/NFL/AX/G4/12V/FTF STD	FTF	35	G4	12	2 900	19	Narrow Flood	3 000	2 000	345	200
50898	H35MR11/MFL/AX/G4/12V/FTH STD	FTH	35	G4	12	2 900	30	Flood	1 300	2 000	345	120
MR16 - Cover Glass												
MOL : 1 7/8 in. (45 mm) Dia. : 2 in. (51 mm)												
51134	H20MR16/FL/CG/4M/GX5.3/12V/BAB STD	BAB/CG	20	GX5.3	12	2 950	38	Flood	500	4 000	260	100
50892	H35MR16/FL/CG/4M/GX5.3/12V/FMW STD	FMW/CG	35	GX5.3	12	3 000	38	Flood	1 000	4 000	530	100
50893	H50MR16/FL/CG/4M/GX5.3/12V/EXN STD	EXN/CG	50	GX5.3	12	3 050	38	Flood	1 600	4 000	850	100
MR16 - Cover Glass - Line Voltage												
MOL : 2 1/2 in. (55 mm) Dia. : 2 in. (51 mm)												
55570*	H35MR16/FL/CG/2M/E26/120V/STD	N/A	35	E26	120	2 800	38	Flood	800	2 000	240	100
57312*	H50MR16/FL/CG/2M/E27/120V/STD	N/A	50	E27	120	2 800	30	Flood	1 100	2 000	420	200
55569*	H50MR16/FL/CG/2M/E26/120V/STD	N/A	50	E26	120	2 800	38	Flood	1 100	2 000	420	100
59590*	H35MR16/FL/CG/E26/130V/STD	N/A	35	E26	130	2 800	38	Flood	800	2 500	180	100
59589*	H50MR16/FL/CG/E26/130V/STD	N/A	50	E26	130	2 800	38	Flood	1 100	2 500	315	100
MR16 - Open												
MOL : 1 7/8 in. (45 mm) Dia. : 2 in. (51 mm)												
51066	H20MR16/FL/4M/GX5.3/12V/BAB STD	BAB	20	GX5.3	12	2 950	36	Flood	500	4 000	260	100
50888	H35MR16/FL/4M/GX5.3/12V/FMW STD	FMW	35	GX5.3	12	3 000	38	Flood	1 000	4 000	530	200
50889	H50MR16/NSP/4M/GX5.3/12V/EXT STD	EXT	50	GX5.3	12	3 050	13	Narrow Spot	9 800	4 000	850	100
50890	H50MR16/NFL/4M/GX5.3/12V/EXZ STD	EXZ	50	GX5.3	12	3 050	24	Narrow Flood	3 200	4 000	850	100
50891	50MR16/FL/4M/GX5.3/12V/EXN STD	EXN	50	GX5.3	12	3 050	38	Flood	1 600	4 000	850	100



MR11 & MR16 Lamps