

Order code	Description	Watts (W)	Base	Volts (V)	Colour temp. (K)	Beam angle (°)	Beam spread	CBCP (cd)	Average life (hrs)	Initial lumens (lm)	Case qty
PAR36											
MOL : 2 3/4 in. (70 mm) Dia. : 4 1/2 in. (114 mm)											
15269	H36PAR36/NSP/4M/ST/12V	36	**ST G53	12	3 000	13	Narrow Spot	3 500	4 000	N/A	12
15268	H36PAR36/WFL/4M/ST/12V	36	**ST G53	12	2 950	30	Wide Flood	1 000	4 000	N/A	12
15271	H50PAR36/NSP/4M/ST/12V	50	**ST G53	12	3 050	8	Narrow Spot	10 000	4 000	400	12
PAR38											
MOL : 5 5/16 in. (135 mm) Dia. : 4 3/4 in. (121 mm)											
51109*2	H60PAR38/FL/5M/MS/130V/STD	60	E26SKT	130	2 800	36	Flood	1 800	5 000	585	15
50113*2	H75PAR38/FL/2.5M/MS/120V/STD	75	E26SKT	120	2 800	36	Flood	2 400	2 500	1 100	15
50744*1 2	H75PAR38/FL/5M/MS/130V/STD	75	E26SKT	130	2 800	36	Flood	2 400	5 000	825	15
10390*1 2	H90PAR38/SP/5M/MS/130V/STD	90	E26SKT	130	2 800	12	Spot	3 000	5 000	950	15
10106*2	H90PAR38/FL/2.5M/MS/120V/STD	90	E26SKT	120	2 800	36	Flood	3 000	2 500	1 270	15
50745*2	H90PAR38/FL/5M/MS/130V/STD	90	E26SKT	130	2 800	36	Flood	3 000	5 000	950	15
51082*2	H120PAR38/FL/2.5M/MS/120V/STD	120	E26SKT	120	2 800	36	Flood	4 000	2 500	1 740	15
51108*1 2	H120PAR38/FL/5M/MS/130V/STD	120	E26SKT	130	2 800	36	Flood	4 000	5 000	1 270	15
PAR56											
MOL : 4 7/16 in. (113 mm) Dia. : 7 in. (173 mm)											
43494	Q500PAR56NSP	500	GX16d	120	2 950	32	Narrow Spot	96 000	4 000	8 000	6
43495	Q500PAR56MFL	500	GX16d	120	2 950	42	Flood	43 000	4 000	8 000	6
43496	Q500PAR56WFL	500	GX16d	120	2 950	66	Wide Flood	19 000	4 000	8 000	6
PAR64											
MOL : 6 1/2 in. (153 mm) Dia. : 8 in. (203 mm)											
43497	Q1000PAR64NSP	1 000	GX16d (Ext.)	120	3 000	31	Narrow Spot	200 000	4 000	19 400	90
11190	Q1000PAR64MFL	1 000	GX16d (Ext.)	120	3 000	45	Flood	80 000	4 000	19 400	15
43499	Q1000PAR64/WFL	1 000	GX16d (Ext.)	120	3 000	72	Wide Flood	33 000	4 000	19 400	15

**ST = Screw terminal

COOL BEAM REFLECTOR LAMPS have a dichroic coating that allows for the heat to be released through the back of the lamp; resulting in lower temperature in front of the lamp.

Cool Beam lamps are ideal for restaurants and other heat sensitive environments.



Order code	Description	Watts (W)	Base	Volts (V)	Colour temp. (K)	Beam angle (°)	Beam spread	CBCP (cd)	Average life (hrs)	Initial lumens (lm)	Case qty
PAR30											
MOL : 3 25/32 in. (93 mm) Dia. : 3 3/4 in. (95 mm)											
10145 ^{1 2}	H75PAR30/CLB/5M/130V/STD	75	E26	130	2 800	40	Flood	1 700	5 000	1 100	15
PAR38											
MOL : 5 5/16 in. (135 mm) Dia. : 4 3/4 in. (121 mm)											
10146 ^{1 2}	H60PAR38/CLB/5M/MS/130V/STD	60	E26SKT	130	2 900	36	Flood	1 700	5 000	800	15
51180 ^{1 2}	H90PAR38/CLB/5M/MS/130V/STD	90	E26SKT	130	2 900	36	Flood	3 000	5 000	1 140	15

¹This product is no longer manufactured as per Energy Efficiency Regulations, note that it will remain available until stock is depleted.
²Cannot be sold in Ontario as per provincial regulations on energy efficiency of lighting products.



Reflector Lamps