



Flex 12™

Flex 12 satin aluminum ribbon-like track and pure geometrical forms make it unique among monorail systems. Use it in straight runs or field-curve it to echo the natural rhythms of curved walls or to introduce pleasing visual contrast into an angular space. Whether mounted close to the ceiling, suspended from stainless steel cable or extended off of a wall, Flex 12 offers unlimited possibilities with a system that is widely recognized for its simple installation with minimum number of components. Flex 12 inspires inventive, unique solutions that integrate art and architecture.



Juno® Flex 12™ Spotlights

Geometrics


The timeless simplicity of cones and spheres. Choose the MR16 Cone for a more sophisticated design statement or the Orb for balanced, consistent appearance regardless of aiming angle.

Cone

Lamp

12V or 24V
20-50W
MR16

Dimensions



Finish:  Silver

Optional Accessories


Color Filters
UV Filters
Dichroic Lenses
Diffuse Spread Lens
Linear Spread Lens
Prismatic Spread Lens
Uniformity Lens
Hexcell Louver

Orb

Lamp

12V or 24V
20-50W
MR16

Dimensions



Optional Accessories

Color Filters
UV Filters
Dichroic Lenses
Diffuse Spread Lens
Linear Spread Lens
Prismatic Spread Lens
Uniformity Lens
Hexcell Louver

Delta 200 Series®


An angular, die-cast fixture body and rod-supported lamp bezel create a semi-exposed, technical appearance. Choose the Gallery model to throw light back onto vertical surfaces, signage or displays.

Gallery

Lamp

12V or 24V
20-50W
MR16

Dimensions



Finish:  Silver

Optional Accessories


Black Barn Doors
Color Filters
UV Filters
Dichroic Lenses
Diffuse Spread Lens
Linear Spread Lens
Prismatic Spread Lens
Uniformity Lens
Hexcell Louver
Snoot

Pendant

Lamp

12V or 24V
20-50W
MR16

Dimensions



Optional Accessories



Black Barn Doors
Color Filters
UV Filters
Diffuse Spread Lens
Dichroic Lenses
Linear Spread Lens
Prismatic Spread Lens
Uniformity Lens
Hexcell Louver
Snoot



Juno® Flex 12™ Spotlights

Gyrus™ with Integral Dual Accessory Holder

A new spin on an old idea, the Gyrus™ combines dramatic aerodynamic styling with an integral accessory holder that accepts up to two standard 2" diameter lenses and louvers. The snap-on design makes this an easy to accessorize fixture for more demanding display lighting applications.



Lamp	Dimensions	Finish
12V or 24V 20-50W MR16		 Silver

Optional Accessories

Color Filters	Linear Spread Lens
UV Filters	Prismatic Spread Lens
Dichroic Lenses	Uniformity Lens
Diffuse Spread Lens	Hexcell Louver

Gimbal Ring

This sculpted dual yoke design is an elegant interpretation of the classic gimbal ring.



Lamp	Dimensions	Finish
12V or 24V 20-50W MR16		 Silver

Optional Accessories

Color Filters	Linear Spread Lens
UV Filters	Prismatic Spread Lens
Dichroic Lenses	Uniformity Lens
Diffuse Spread Lens	Hexcell Louver

Universal

Use the minimalist universal by itself for a do everything basic lampholder, or in combination with the scoop accessory for a metallic accent.



Lamp	Dimensions	Finish
12V or 24V 20-50W MR16CG Cover Glass		 Silver

Optional Accessories

Accessory Holder	Diffuse Spread Lens*
Barn Doors*	Linear Spread Lens*
Color Filters*	Prismatic Spread Lens*
UV Filters*	Uniformity Lens*
Dichroic Lenses*	Hexcell Louver*



Accessory Scoop

Universal halogen spotlights take on a whole new appearance when you dress them up in a luxurious metal scoop.

Lamp	Dimensions	Finish
Perforated Metal Scoop		 Silver

Trapezia™

Trapezia™ suspends the MR16 lamp down from the trac with the grace of a trapeze artist. Slender 9-inch long tubes conceal supply wires feeding into an elegantly sculpted die-cast lamp housing. The light airy appearance is great for display, exhibition and gallery lighting and the downward reach can make pendant mounting of trac unnecessary.

Lamp	Dimensions	Finish
12V or 24V 20-50W MR16CG Cover Glass		 Silver

Optional Accessories

Accessory Holder	Diffuse Spread Lens*
Barn Doors*	Linear Spread Lens*
Color Filters*	Prismatic Spread Lens*
UV Filters*	Uniformity Lens*
Dichroic Lenses*	Hexcell Louver*

* Filters, lenses and barn door require accessory holder for installation.

Gyrus and Trapezia patent pending.
Gyrus US Patent No. D508,792
Trapezia US Patent No. D504,974

Photo Credits:
Cover: University of Chicago Hospital, Chicago, IL (Pirello Photography)



©2017 Acuity Brands Lighting, Inc. The marks appearing in this catalog are trademarks of Acuity Brands Lighting, Inc. Products shown in this brochure may be covered by U.S. and international patents and patents pending. Specifications subject to change without notice. Printed in the U.S.A.