

Electronic/Glass Fuses

GSB/GSB-V

- Glass body
- Fast-acting
- 5mm x 20mm
- 1-1/2" Axial leads optional



1/16A through 10A, 250VAC, UL and CSA Recognized
 1/16A through 6-3/10A, 250VAC, SEMKO Approved
 1/16A through 6-3/10A, 250VAC, VDE Approved
 IEC-127-2 Standard Sheet 2*



Standard Fuse Ampere Ratings

| Catalog Number | Axial Lead Cat. No | Ampere Rating | Volts | I.R. |
|----------------|--------------------|---------------|-------|------|
| GSB1/16 | GSB-V1/16 | 1/16A | 250V | 1 |
| GSB8/100 | GSB-V8/100 | 8/100A | 250V | 1 |
| GSB1/10 | GSB-V1/10 | 1/10A | 250V | 1 |
| GSB1/8 | GSB-V1/8 | 1/8A | 250V | 1 |
| GSB16/100 | GSB-V16/100 | 16/100A | 250V | 1 |
| GSB2/10 | GSB-V2/10 | 2/10A | 250V | 1 |
| GSB1/4 | GSB-V1/4 | 1/4A | 250V | 1 |
| GSB315/1000 | GSB-V315/1000 | 315/1000A | 250V | 1 |
| GSB4/10 | GSB-V4/10 | 4/10A | 250V | 1 |
| GSB1/2 | GSB-V1/2 | 1/2A | 250V | 1 |
| GSB630/1000 | GSB-V630/1000 | 630/1000A | 250V | 1 |
| GSB8/10 | GSB0-V8/10 | 8/10A | 250V | 1 |
| GSB1 | GSB-V1 | 1A | 250V | 1 |
| GSB1-1/4 | GSB-V1-1/4 | 1-1/4A | 250V | 1 |
| GSB1-6/10 | GSB-V1-6/10 | 1-6/10A | 250V | 1 |
| GSB2 | GSB-V2 | 2A | 250V | 1 |
| GSB2-1/2 | GSB-V2-1/2 | 2-1/2A | 250V | 1 |
| GSB3-15/100 | GSB-V3-15/100 | 3-15/100A | 250V | 1 |
| GSB4 | GSB-V4 | 4A | 250V | 2 |
| GSB5 | GSB-V5 | 5A | 250V | 3 |
| GSB6-3/10 | GSB-V6-3/10 | 6-3/10A | 250V | 4 |
| GSB8 | GSB-V8 | 8A | 250V | 5 |
| GSB10 | GSB-V10 | 10A | 250V | 6 |

1. 250VAC @ 35A I.R.
2. 250VAC @ 40A I.R.
3. 250VAC @ 50A I.R.
4. 250VAC @ 63A I.R.
5. 250VAC @ 80A I.R.
6. 250VAC @ 100A I.R.

*IEC Standards for 5x20mm fuses do not include ratings above 6.3 amperes.

GDG/GDG-V

- Glass body
- Time-delay
- 5mm x 20 mm
- 1-1/2" Axial leads optional



1/16A through 10A, 250VAC, UL & CSA Recognized
 1/16A through 6-3/10A, 250VAC, SEMKO Approved
 1/16A through 6-3/10A, 250VAC, VDE Approved
 IEC 127-2 Standard Sheet 3*



Standard Fuse Ampere Ratings

| Catalog Number | Axial Lead Cat. No | Ampere Rating | Volts | I.R. |
|----------------|--------------------|---------------|-------|------|
| GDG1/16 | GDG-V1/16 | 1/16A | 250V | 1 |
| GDG8/100 | GDG-V8/100 | 8/100A | 250V | 1 |
| GDG1/10 | GDG-V1/10 | 1/10A | 250V | 1 |
| GDG1/8 | GDG-V1/8 | 1/8A | 250V | 1 |
| GDG16/100 | GDG-V16/100 | 16/100A | 250V | 1 |
| GDG2/10 | GDG-V2/10 | 2/10A | 250V | 1 |
| GDG1/4 | GDG-V1/4 | 1/4A | 250V | 1 |
| GDG315/1000 | GDG-V315/1000 | 315/1000A | 250V | 1 |
| GDG4/10 | GDG-V4/10 | 4/10A | 250V | 1 |
| GDG1/2 | GDG-V1/2 | 1/2A | 250V | 1 |
| GDG630/1000 | GDG-V630/1000 | 630/1000A | 250V | 1 |
| GDG8/10 | GDG-V8/10 | 8/10A | 250V | 1 |
| GDG1 | GDG-V1 | 1A | 250V | 1 |
| GDG1-1/4 | GDG-V1-1/4 | 1-1/4A | 250V | 1 |
| GDG1-6/10 | GDG-V1-6/10 | 1-6/10A | 250V | 1 |
| GDG2 | GDG-V2 | 2A | 250V | 1 |
| GDG2-1/2 | GDG-V2-1/2 | 2-1/2A | 250V | 1 |
| GDG3-15/100 | GDG-V3-15/100 | 3-15/100A | 250V | 1 |
| GDG4 | GDG-V4 | 4A | 250V | 2 |
| GDG5 | GDG-V5 | 5A | 250V | 3 |
| GDG6-3/10 | GDG-V6-3/10 | 6-3/10A | 250V | 4 |
| GDG8 | GDG-V8 | 8A | 250V | 5 |
| GDG10 | GDG-V10 | 10A | 250V | 6 |

1. 250VAC @ 35A I.R.
2. 250VAC @ 40A I.R.
3. 250VAC @ 50A I.R.
4. 250VAC @ 63A I.R.
5. 250VAC @ 80A I.R.
6. 250VAC @ 100A I.R.

*IEC Standards for 5x20mm fuses do not include ratings above 6.3 amperes.