

## TECHNICAL DATA

# Fluke 279 FC Thermal Multimeter



### CAMERA

Built-in thermal imager

### DISPLAY

Full-color LCD screen provides clean, crisp readings

### IFLEX®

Expand your measurement capabilities—get into tight, hard to reach spaces for current measurement (up to 2500 A ac)

### FLUKE CONNECT

Transmit results wirelessly to your smartphone with Fluke Connect



## Find. Repair. Validate. Report.

The 279 FC is a full-featured digital multimeter with integrated thermal imaging and is designed to increase your productivity and confidence. The thermal multimeter helps you find, repair, validate, and report many electrical issues quickly so that you are confident problems are solved.

## Locate the problem immediately

Thermal imaging multimeters are a first-line troubleshooting tool for electrical equipment that can check hot spots on high-voltage equipment and transformers, detect heating of fuses, wires, insulators, connectors, splices and switches. Scanning with the 279 FC's thermal imager reveals many electrical issues rapidly and from a safe distance. By combining two tools into one, the thermal multimeter lightens the load and increases productivity.

## Expanded functionality

Compatible with iFlex® (a flexible current clamp) to expand your measurement capabilities and get into tight, hard to reach spaces for current measurement (up to 2500 A ac). The large full-color LCD screen makes for easier and clearer viewing of images and readings. The 10 hour+ rechargeable battery keeps you going all day long under normal conditions.

## Communicate your results

With built-in Fluke Connect®, transmit results wirelessly to a smartphone and save time on reporting to validate work is complete. Troubleshoot better by instantly trending and monitoring measurements live on your smartphone screen. Create and email reports right from the field.

## Product highlights

- Full-featured multimeter with built-in thermal imager
- 15 measurement functions including: ac voltage with low-pass filter, dc voltage, resistance, continuity, capacitance, diode test, min/max/avg, ac current (with iFlex), frequency
- Thermal imaging reveals many electrical issues quickly and safely, eliminating the need for time-consuming testing and validation
- Two-in-one tool is designed to increase productivity—no need to go back to the truck or office to retrieve a shared camera or wait for the thermographer—do more in less time!
- iFlex expands your measurement capabilities—get into tight, hard to reach spaces for current measurement (up to 2500 A ac)
- Save measurements and images while communicating wirelessly with a smart phone up to 20 feet (6.1 m) away (no obstructions)
- Image resolution—80 x 60
- 3.5 in (8.89 cm) color LCD screen
- Rechargeable lithium ion battery allows for a full work day (10+ hours) under normal conditions
- Assembled in the USA
- Three-year standard warranty
- Auto power off to save battery power
- CAT III 1000 V, CAT IV 600 V measurement category
- Optional accessories: Fluke i2500-10 or i2500-18 iFlex® Flexible Current Probes, Fluke BC500 AC Power Charger and Fluke BP500 Lithium-ion Battery 3000 mAh

## Specifications

### AC voltage

Range <sup>1</sup> /resolution	600.0 mV / 0.1 mV 6.000 V / 0.001 V 60.00 V / 0.01 V 600.0 V / 0.1 V 1000 V / 1 V	
Accuracy <sup>2, 3, 4, 5</sup>	45 Hz to 65 Hz	1.0 % + 3
	65 Hz to 200 Hz	4.0 % + 3
	200 Hz to 500 Hz	15 % + 3

### AC mV

Range <sup>1</sup> /resolution	600.0 mV / 0.1 mV	
Accuracy <sup>2, 3, 4</sup>	45 Hz to 500 Hz	1.0 % + 3

<sup>1</sup>AC voltage ranges are specified from 1 % of range to 100 % of range.

<sup>2</sup>Crest factor of ≤ 3 at full scale up to 500 V, decreasing linearly to crest factor < 1.5 at 1000 V.

<sup>3</sup>For non-sinusoidal waveforms, add - (2 % of reading + 2 % full scale) typical, for crest factor up to 3.

<sup>4</sup>Do not exceed 10<sup>7</sup> V-Hz.

<sup>5</sup>Full-time low pass filter

### DC voltage

Range/resolution	6.000 V / 0.001 V 60.00 V / 0.01 V 600.0 V / 0.1 V 1000 V / 1 V	
Accuracy	6 V, 60 V, 600 V	0.09 % + 2
	1000 V	0.15 % + 2

### DC mV

Range/resolution	600.0 mV / 0.1 mV	
Accuracy	0.09 % + 2	

### Continuity

Range/resolution	600 Ω / 1 Ω	
Accuracy	Meter beeps at < 25 Ω, beeper detects opens or shorts of 600 μs or longer	

## Detailed specifications (continued)

### Resistance

Range/resolution	600.0 $\Omega$ / 0.1 $\Omega$ 6.000 k $\Omega$ / 0.001 k $\Omega$ 60.00 k $\Omega$ / 0.01 k $\Omega$ 600.0 k $\Omega$ / 0.1 k $\Omega$ 6.000 M $\Omega$ / 0.001 M $\Omega$ 50.00 M $\Omega$ / 0.01 M $\Omega$	
Accuracy	600 $\Omega$	0.5 % + 2
	6 k $\Omega$ to 600 k $\Omega$	0.5 % + 1
	50 M $\Omega$	1.5 % + 3

### Diode test

Range/resolution	2.000 V / 0.001 V	
Accuracy	1 % + 2	

### Capacitance

Range/resolution	1000 nF / 1 nF 10.00 $\mu$ F / 0.01 $\mu$ F 100.0 $\mu$ F / 0.1 $\mu$ F 9999 $\mu$ F <sup>1</sup> / 1 $\mu$ F	
Accuracy	1000 nF thru 100 $\mu$ F	1.2 % + 2
	9999 $\mu$ F	10 % typical

<sup>1</sup>In the 9999  $\mu$ F range for measurements to 1000  $\mu$ F, the measurement accuracy is 1.2 % + 2.

### AC current

Range/resolution	999.9 A / 0.1 A 2500 A / 1 A (with iFlex)	
Accuracy	45 Hz to 500 Hz	3.0 % + 5

### Frequency

Range/resolution	99.99 Hz / 0.01 Hz 999.9 Hz / 0.1 Hz	
Accuracy	0.1 % + 1	

### Input characteristics

AC voltage	Input impedance (nominal)	> 10 M $\Omega$ < 100 pF
	Common mode rejection ratio (1 k $\Omega$ unbalance)	> 60 dB, DC to 60 Hz
	Overload protection	1100 V rms
DC voltage	Input impedance (nominal)	> 10 M $\Omega$ < 100 pF
	Common mode rejection ratio (1 k $\Omega$ unbalance)	> 120 dB at DC, 50 Hz or 60 Hz
	Normal mode rejection	> 60 dB at 50 Hz or 60 Hz
	Overload protection	1100 V rms
AC mV/DC mV	Input impedance (nominal)	> 10 M $\Omega$ < 100 pF
	Common mode rejection ratio (1 k $\Omega$ unbalance)	> 120 dB at DC, 50 Hz or 60 Hz
	Normal mode rejection	> 60 dB at 50 Hz or 60 Hz
	Overload protection	1100 V rms
Resistance/capacitance	Open circuit test voltage	< 2.7 V dc
	Full scale voltage to 6 M $\Omega$	< 0.7 V dc
	Full scale voltage 50 M $\Omega$	< 0.9 V dc
	Typical short circuit current	< 350 mA
	Overload protection	1100 V rms
Continuity/diode test	Open circuit test voltage	< 2.7 V dc
	Full scale voltage	2.000 V dc
	Typical short circuit current	< 1.1 mA