

ORDERING INFORMATION

CAT. NO.	UPC NO.	DESCRIPTION
WK100	07745	Workhorse™ Bending and Threading Station (includes kit accessories)
WK100-B	07865	Workhorse™ Bending and Threading Cart (excludes all kit and additional accessories)

SPECIFICATIONS

HEIGHT, WITH CASTERS	38" (965.2mm)
WIDTH	32" (813mm)
LENGTH	74" (1880mm)
WEIGHT, WK100	440lb (199.6kg)
WEIGHT, WK100-B	390lb (17.9kg)

KIT ACCESSORIES - INCLUDED WITH WK100

CAT. NO.	UPC NO.	DESCRIPTION
CRSL8	07870	8" Caster Kit
MK555	07760	555® Bender Series Mounting Brackets
MKTC	07756	Threader Mounting Brackets
90BC	07761	90 Degree Bend Check Tray
MK467	07757	Chain Vise Mount

ADDITIONAL ACCESSORIES AND EQUIPMENT - SOLD SEPARATELY

CAT. NO.	UPC NO.	DESCRIPTION
MK85X	07759	854DX / 855GX Bender Mounting Brackets
MKOIL	07758	Oil Catch System
CRSL6	07868	6" Caster Kit
555CXRS	01634	Electric Bender, CX with Single Rigid Shoes
555RSC	01632	Electric Bender, Classic with Single Rigid Shoes
854DX	02670	Bender, Electric Conduit
855GX	12579	Bender, Electric Conduit (855GX)
467	27318	Vise and Chain, Packaged

*Threaders Sold Separately

COMPATIBILITY

Use these Greenlee® tools with your Workhorse



555® Series Bender

The Triple-Nickel is known as the industry standard for electric benders. It's rugged design bends ½" - 2" Rigid, EMT, IMC, & PVC Coated conduit.



854DX Bender

This versatile electric bender allows for bending vertical and horizontal configurations. The digital pendant sets desired angle and monitors process. One shoe bends ½" to 2" Rigid, EMT, & IMC conduit. PVC Coated Rigid shoe also available.



467 Chain Vise

For use with a wide range of sizes of pipe or conduit. Designed to securely hold conduit and pipe to prevent from twisting or turning during cutting or threading.



www.greenlee.com MA6682 08/17

4455 Boeing Dr • Rockford, IL 61109-2988 • USA • 815-397-7070

©2017 Greenlee Textron Inc. • An ISO 9001 Company • Printed in USA

Greenlee Textron Inc. is a subsidiary of Textron Inc.