RAB DESIGN

SpaceLite with sensor
LED Ceiling Light

Slim LED Ceiling light with occupancy sensor that
automatically detects motion and turns light On and Off.

Project	
Type	
Date	
Notes	

APPLICATIONS

Ideal for utility rooms, work rooms, storage rooms, laundry rooms, and other small spaces.

SPECIFICATIONS

Construction
Durable thermoplastic housing with built in occupancy sensor. Four mounting holes on housing to position for maximum coverage.

Optics
The fixture delivers a total output of 956 lumens at an efficacy of 80 lumens per watt. LEDs have a colour temperature of 4000K natural white. The fixture is ideal for indoor use. LED life of 50,000 hours.

Electrical
Total system wattage of the unit is 12W measured, 14W maximum. The driver operates at 120V.

Mounting
Four mounting holes on housing to position the fixture.

Finish
Standard finish is white.

Sensor
No wall switch needed, occupancy sensor automatically detects motion and turns light on. Light is turned off after one minute once room is vacated.

Input Watts	12W measured 14W maximum
Lumens	956
Efficacy	80 lumens/watt

Warranty	5 Years
Colour Temperature	4000K (natural white)
Operating Temp.	-30°C to + 40°C
LED life	50,000 hours
Voltage	120V
Power Factor	0.99
CRI	>80
THD	<20%

DIMENSIONS

Ø 139.95mm [5.51in]

35.87mm [1.41in]

20.00mm [.79in]

Ø 70.00mm [2.76in]

Ø 89.00mm [3.50in]

ENERGY STAR

SENSOR INFORMATION

8~12ft

Height of installation8~12ft

Max:20ft   Max:20ft

(Height of installation8ft)
Detection range

360

Detection angel

SENSOR SPECS

Detection angle: 360°

Detection Range: 20ft (radii.)

Time: 1 min

Light Control: 24H Lux

ORDERING GUIDE

| SPLR1 | – | LED12 | – | A | – | 4K | – | SMS |

VOLTAGE

A - 120V

COLOUR TEMP

NW - (natural white) 4000K

MOTION SENSOR

SMS - Motion Sensor

* Standard configuration