

FEATURES & SPECIFICATIONS

INTENDED USE — The OneUp™ recessed direct-wire LED downlight includes integrated junction box, trim, pre-installed non-metallic bushings and 3-port push wire quick connectors in one package. The OneUp is the most economical means to create a well lit environment with exceptional energy efficiency and pear zero maintenance.

CONSTRUCTION — Aluminum die cast, square baffle trim. Integrated galvanized steel junction box with captive door for easy access. Suitable for daisy chaining (pulling wires). Available in 3000K color temperature LEDs.

OPTICS — Square baffle recesses optical system into the ceiling to prevent glare and provide a traditional look. Diffused lens provides even light distribution for general illumination, equivalent to 65W incandescent flood lamp. Wide flood beam angle at $>90^\circ$. CRI >90. Maintains at least 70% light output for 50,000 hours.

INSTALLATION — Tool-less installation. Secure trim retention with two side-mounted spring clips for easy installation in plaster, sheet rock, or plywood ceilings. The integrated junction box - with pre-installed non-metallic bushing - allows non-metallic cable to be fed through without the hassle of knockouts. The captive junction box door provides easy access to pre-installed 3-port push wire quick connectors for straight-forward wiring. Rated for Type IC installations. Maximum of 4 No. 12AWG through branch circuit conductor suitable for 90°C permitted in box. Ground wire provided.

ELECTRICAL SYSTEM — LED module with high-efficiency on board driver. Dimming down to 10%. For compatible dimmers, refer to: Compatible dimmers chart.


Actual wattage may differ by +/-5% when operating at 120V +/-10%.

LISTINGS — ETL certified to US and Canadian safety standards. Can be used to comply with California Title 24 Part6 High Efficacy LED Light Source Requirements. WSEC ASTEM E283 for Air-Tight rated with gasket or caulking between fixture trim and ceiling. ENERGY STAR® certified. Wet location listed*. Indoor damp location only for items in Brushed Nickel finish.

WARRANTY — 5-year limited warranty. Complete warranty terms located at: www.acuitybrands.com/CustomerResources/Terms and conditions.aspx

Note: Actual performance may differ as a result of end-user environment and application. All values are design or typical values, measured under laboratory conditions at 25 °C. Specifications subject to change without notice.

	pecifica	tions			
Aperture:	2-13/1	6" (72.0)			
Overlap Trim:	5" (125	5.0)			
Height:	4-3/8"	(109.7)			
Ceiling Opening:	4-5/8"	(117)			
Min Ceiling Thickr	ness:	1/2" (12.7)			
Max Ceiling Thickness:		1-1/2" (38.1)			
All dimensions are inches (millimeters).					



Direct-Wire LED Recessed Downlight

4JBK SQ

Remodel


















Brushed nicke



ORDERING INFORMATION For shortest lead times, configure product using standard options (shown in bold).

Series	Shape	CCT/Watts/Lumens ¹	CRI	Finish		
4JBK	SQ Square	30K 3000K/9W/625L	90CRI 90 CRI	MW Matte White		
				BN Brushed Nickel ²		
				ORB Oil-Rubbed Bronze		

Notes

- 1 Total System Delivered Lumens.
- 2 Indoor damp location only for items in Brushed Nickel Finish.


Example: 4JBK SQ 30K 90CRI BN

DOWNLIGHTING 4JBK SQ

PHOTOMETRICS

Distribution Curve	Distribution Data	Output Data	Coefficient of Utilization	Illuminance Data at 30" Above Floor for
				a Single Luminaire

4JBK SQ 30K, 3000 K LEDs, input watts: 8.92, delivered lumens: 631.5, LM/W=70.79, test no. ISF 35168



						pf				20	1%				
						рс		80%			70%			50%	
	Ave	Lumens	Zone	Lumens	% Lamp	pw	50%	30%	10%	50%	30%	10%	50%	30%	10%
0	283		0°-30°	215.1	34.1	0	119	119	119	116	116	116	111	111	111
5	282	27	0°-40°	341.9	54.2	1	106	102	99	104	101	97	100	97	94
15	271	76	0°-60°	552.2	87.5	2	94	88	83	92	87	82	89	84	80
25	243	112	0°-90°	631.0	100.0	3	84	77	71	82	76	70	79	74	69
35	204	127	90° - 120°	0.0	0.0	4	75	67	61	74	66	61	71	65	60
45	155	119	90° - 130°	0.0	0.0	5	68	59	53	67	59	53	65	58	52
55	102	91	90° - 150°	0.0	0.0	6	61	53	47	60	53	47	59	52	46
65	52	52	90° - 180°	0.0	0.0	7	56	48	42	55	47	42	54	47	42
75	19	21	0°-180°	631.1	*100.0	8	51	43	38	51	43	38	49	42	37
85	5	6	*1	Efficiency		9	47	39	34	47	39	34	46	39	34
90	0					10	44	36	31	43	36	31	42	36	31

ENERGY DATA

4" ENERGY DATA - 3000K					
Lumens	625				
Color temperature	3000K				
CRI	90				
Lumens/Watt	69.44				
Min. starting temperature	-18°C (0°F)				
EMI/RFI	FCC Title 47 CFR, Part 15, Class B				
Sound rating	Class A standards				
Input voltage	120V AC				
Total Harmonic Distortion	5.56				
Min. power factor	0.9				
Input frequency	50/60 Hz				
Rated wattage	9W				
Input power	9W				
Input current	0.07A				

DIMMER COMPATIBILITY

COMPATIBLE DIMMERS								
Lutron	Leviton	Pass & Seymour	Synergy/Leviton	Sensorswitch				
DV-603P-LA	6633-PA	HCL453PTCCCV6	ISD 600 I 120 / IPI06	nSP5 PCD 2W				
CT-603PR-WH	6615-P	LS 603 PWV	ISD 1000 I 120 / IPI10	nSP5 PCD ELV 120				
DVELV-300P			ISD 400 ELV 120 / IPE04					
300P SELV								
DV-600P								
NTELV-300P								
NLV-600								
Caseta PD-6WCL dimmer (requires Lutron Smart Bridge L-BDG2-WH which is sold separately from the dimmer)								

50% beam -

61.3°

6.5 4.7

11.3 1.6 24.1 29.2

13.6 1.1

0.8 34.2

Inital FC Mounting Center _Height

Beam

9.4

5.0 3.1 2.1

8.0

10.0

12.0

14.0

16.0

10% beam -

103.5°

0.3

14.0 0.9

LIGHTING FACTS

