

PASS & SEYMOUR®

Commercial Specification Grade Receptacles
Tamper-Resistant 15 & 20A, 125V


TR26242, TR26342

Style meets safety in Pass & Seymour® Tamper-Resistant Decorator Receptacles!

Corrosion-resistant plated-steel mounting strap, durable nylon faces, and triple-wipe power contacts combine with tamper-resistant shutters to deliver safe and reliable performance. Ergonomic decorator-style offers a sleek design, while giving the same performance and ease of installation as standard Pass & Seymour devices. Tamper-resistant feature helps you comply with 2014 NEC® Article 406.12 and get the job done right. Tri-drive, backed-out terminal screws also save installation time. These UL listed receptacles are ideal for residential, multi-dwelling, commercial office, and hospitality applications.



FEATURES & BENEFITS



- Residential
 Hospitality/Lodging
- Retail
- Multiple Dwelling
- Office
- Education



PASS & SEYMOUR®

Commercial Specification Grade Receptacles Tamper-Resistant 15 & 20A, 125V

ORDERING INFORMATION

Catalog Number	Ratino	v	Color	NEMA Configuration No.	
Duplex Receptacles Side Wire					
TR26242I	15A	125V	Ivory	5-15R	
TR26242W	15A	125V	White	5-15R	
TR26242	15A	125V	Brown	5-15R	
TR26242GRY	15A	125V	Gray	5-15R	
TR26242BK	15A	125V	Black	5-15R	
TR26242RED	15A	125V	Red	5-15R	
TR26242LA	15A	125V	Light Almond	5-15R	
TR26342I	20A	125V	Ivory	5-20R	
TR26342W	20A	125V	White	5-20R	
TR26342	20A	125V	Brown	5-20R	
TR26342GRY	20A	125V	Gray	5-20R	
TR26342BK	20A	125V	Black	5-20R	
TR26342RED	20A	125V	Red	5-20R	
TR26342LA	20A	125V	Light Almond	5-20R	





5-15R

NEMA 5-20R

PASS & SEYMOUR®




Commercial Specification Grade Receptacles Tamper-Resistant 15 & 20A, 125V

TECHNICAL INFORMATION

3rd Party Compliance

UL Listed, File Number E140596, Standard UL498 CSA Certified, File Number LR16063, Standard CSA-C22.2 No. 42 Conforms to NEMA WD-1 and WD-6

Performance	
Electrical	
Dielectric Withstand Voltage	Withstands 2000V minimum
Maximum Working Voltage	250V
Current Interrupting	Certified for current interrupting at full-rated current
Temperature Rise	Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current
Mechanical	
Terminal Identification	Terminal Identification in accordance with UL 498 (Brass, White, Green)
Terminal Accommodation	#14 AWG - #10 AWG copper conductor only.
Product Identification	Ratings are permanent part of the device
Environmental	
Flammability	UL94 V2
Operating Temperature	Maximum continuous +60°C, minimum -40°C without impact



Materials	
Face	Nylon
Back Body	Nylon
Line Contacts	.032 260 Brass
Mounting Strap	.042 Zinc-Plated Steel
Ground Contacts	.040 260 Brass
Tamper-Resistant Shutters	Thermoplastic
Terminal Screws	#8 Tri-Drive Steel (Neutral = Nickel Plated-Steel)
Ground Screw	#8 Hex Tri-Drive Steel; Zinc Coating with Green Chromate
Auto-Ground Clip	Steel


Tri-Drive Steel

Warranty

Mounting Screws


1 Year

COMPLEMENTARY DEVICES & ACCESSORIES



STRAIGHT BLADE RECEPTACLES

- Extra Heavy-Duty
- Heavy-Duty
- Hard Use
- Construction Grade
- Construction Grade Leaded
- Commercial Grade




PLUGTAIL™ DEVICES

- Extra Heavy-Duty SpecGrade
- Extra Heavy Duty Hospital Grade
- Extra Heavy-Duty Tamper-Resistant
- Extra Heavy-Duty Tamper-Resistant Hospital Grade



DECORATOR DEVICES

- Construction Grade Switches
- Specification Grade Combo Switches
- Construction Grade Receptacles
- Commercial Grade Receptacles
- Specification Grade Hallway Lights



SWITCHES

- Extra Heavy-Duty
- Extra Heavy-Duty Lighted
- Extra Heavy-Duty Security
- Extra Heavy-Duty Locking
- Hard Use
- Commercial Grade



GFCIs

- Specification Grade
- Hospital Grade
- PlugTail™



WALL PLATES

- TradeMaster® Thermoplastic Nylon
- Screwless Polycarbonate
- Stainless Steel
- Brass
- Aluminum
- Dustproof Stainless Steel Covers

ALSO AVAILABLE...

- Hospital Grade Devices
- PlugTail™ Devices
- SPD & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight BladePlugs & Connectors
- Turnlok® Locking Devices
- Weatherproof Boxes & Covers
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips



Electrical Wiring Systems

P.O. Box 4822 Syracuse, NY 13221-4822 Phone: 1.800.776.4035 www.legrand.us/passandseymour

570 Applewood Crescent Vaughan, Ontario L4K 4B4 Phone:905.738.9195 www.legrand.ca