

# Technical Information Bulletin

## LED Linear Tubes



Date: \_\_\_\_\_ Name of distributor: \_\_\_\_\_  
 In hands date of project: \_\_\_\_\_ Client #: \_\_\_\_\_  
 Project name/Number: \_\_\_\_\_ Name of end user: \_\_\_\_\_

### ORDERING INFORMATION

**Order code:** 66988  
**Description:** T8/S2/15W/840/48/U6/ND/STD  
**UPC:** 69549669888  
**Case quantity:** 12  
**DLC Unique ID:** PLK2GZQEZAPC



Nominal length : 22 7/16 in. (570 mm) Dia. : 1 in. (26 mm)

### PHYSICAL DATA

**Shape:** T8 UBEND U6  
**Base:** G13  
**Material:** Glass

### PERFORMANCE DATA

**Bare Lamp Watts (W):** 15  
**Volts (VAC):** 120 -277/347  
**Colour temperature (K)<sup>1</sup>:** 4 000  
**Life L70 (hrs):** 50 000  
**CRI:** 82  
**Starting method:** Instant & Program Start  
**Operating temperature range:** -20°C to 45°F (4°C to 113°F)

Order code	Average System Watts (W)			Initial Lumens (lm) <sup>2</sup>		
	LBF	NBF	HBFS <sup>3</sup>	LBF	NBF	HBFS <sup>3</sup>
66988	15.8	17.5	24.1	1 980	2 200	2 840

<sup>1</sup> Typical colour temperature range: +/- 5 %  
<sup>2</sup> Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %  
<sup>3</sup> LBF= Low ballast factor, NBF= Normal ballast factor, HBF= High ballast factor



Please refer to the ballast compatibility list to confirm lamp compatibility with the existing luminaire.

### ADDITIONAL INFORMATION

THIS LAMP OPERATES ON INSTANT START AND MANY PROGRAM START ELECTRONIC BALLASTS.  
 Direct replacement for 32W/23T8/U6 watts lamps only.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: \_\_\_\_\_  
 Company: \_\_\_\_\_  
 Signature: \_\_\_\_\_

Date: \_\_\_\_\_

This lighting equipment complies with Canadian standard ICES-005 for use in residential applications.  
 Data is based upon tests performed in a controlled environment and representative of relative performance.  
 Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.