# **Technical Information Bulletin DESIGN LED Lamps**



Date:	Name of distributor:	
In hands date of project:	Client #:	
Project name/Number:	Name of end user:	

#### ORDERING INFORMATION

Order code: 67607 P20/7W/30K/45/DESIGN/STD Description: UPC: 69549676077 Case quantity: 10/60

### PHYSICAL DATA

PAR20 Type: E26 Base: Material: Glass Lens type: Clear



MOL: 3 11/32" (85 mm) Dia. : 2 15/32" (63 mm)

## **PERFORMANCE DATA**

Typical colour temperature range: +/- 5 %

Watts (W):	7
Lamp volts (VAC):	120
Colour temperature (K) <sup>1</sup> :	3 000
Life L70 (hrs):	25 000
Lumens (lm) <sup>2</sup> :	500
Lumens per watt (Im/W):	71
Traditional equivalent (W):	50
CRI:	80
Beam angle (°):	45
CBCP (cd):	520
THD (%):	55
Frequency (Hz)	60
Power factor:	0.88
Operating temperature range:	-20°C to 45°C (-4°F to 113°F)

## **COMPATIBLE DIMMERS**

Legrand	RH703PTUTC
Cooper	AAL06, SLC03P
Leviton	6615, IPL06, 6674, DSL06-1LZ, IPE04-1LZ, DDMX1
Lutron	RRD-6NA, DVCL-153P, DVCL-253P, AYCL-253P, DVRP-253P, SELV-300P, MACL-153P,



<sup>2</sup> Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %



Qty	Description	Price		
I accept the specifications of the luminaire configuration mentioned above.				
Name:				
Company:				
Signature:		Date:		

This lighting equipment complies with Canadian standard ICES-005 for use in residential applications.

Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.