

Device Boxes

Armoured and Nonmetallic Sheathed Cable Clamps











Presenting the LHTQ family of Iberville boxes. With their additional cubic capacity, this family of boxes is designed for any installations that require a greater number of conductors such as heating, GFCI and arc-fault applications.

What's more, because it's an LHTQ, installation is always fast and accurate. Look for these practical and time saving features on all LHTQ models.

- *positioning guides for drywall and outside wall applications*
- *retractable positioning tabs*
- *internally embossed mounting slots*
- *flat box sides for maximum stability*
- *holding prongs*
- *single and 2 gang boxes are CSA approved for one-screw mounting*

Device Boxes







Armoured and Nonmetallic Sheathed Cable Clamps

			
BC1018-LHTQ	BC1304-LHTQ	BC2004-LHTQ	BC2304-LHTQ
Internally embossed slots for screw mounting. Fixed positioning tabs for single 1/2 in. drywall along with retractable positioning tabs for double 1/2 in. drywall applications. Fixed positioning tabs for outside wall applications. Holding prongs. One screw mounting.	Internally embossed slots for screw mounting. Fixed positioning tabs for single 1/2 in. drywall along with retractable positioning tabs for double 1/2 in. drywall applications. Fixed positioning tabs for outside wall applications. Holding prongs. One screw mounting.	Internally embossed slots for screw mounting. Fixed positioning tabs for single 1/2 in. drywall along with retractable positioning tabs for double 1/2 in. drywall applications. Fixed positioning tabs for outside wall applications. Holding prongs. One screw mounting.	Internally embossed slots for screw mounting. Fixed positioning tabs for single 1/2 in. drywall along with retractable positioning tabs for double 1/2 in. drywall applications. Fixed positioning tabs for outside wall applications. Holding prongs. One screw mounting.
			
BC2304-LHTQ-2	BC2304-LHTQ-3	BC2304-LHTQ-4	BC3104-LHTQ
Internally embossed slots for screw mounting. Fixed positioning tabs for single 1/2 in. drywall along with retractable positioning tabs for double 1/2 in. drywall applications. Fixed positioning tabs for outside wall applications. Holding prongs. One screw mounting.	Internally embossed slots for screw mounting. Fixed positioning tabs for single 1/2 in. drywall along with retractable positioning tabs for double 1/2 in. drywall applications. Fixed positioning tabs for outside wall applications. Holding prongs.	Internally embossed slots for screw mounting. Fixed positioning tabs for single 1/2 in. drywall along with retractable positioning tabs for double 1/2 in. drywall applications. Fixed positioning tabs for outside wall applications. Holding prongs.	Internally embossed slots for screw mounting. Fixed positioning tabs for single 1/2 in. drywall along with retractable positioning tabs for double 1/2 in. drywall applications. Fixed positioning tabs for outside wall applications. Holding prongs. One screw mounting.

Cat. No.	Dimensions H x W x D (in.)	Volume (Cu. in.)	Gangable Yes or No	Features			Pryouts ends
				One screw mounting	Pos. tabs	Prov. for external nailing	
BC1018-LHTQ	3 x 2 x 3	18.0	yes	yes	yes	yes	4
BC1304-LHTQ	3 x 2 x 2-1/2	14.5	yes	yes	yes	yes	4
BC1304-LHATQ	3 x 2 x 2-1/2	14.5	yes	yes	yes	yes	4
BC2004-LHTQ	3-3/4 x 2-3/16 x 2-3/4	20.5	no	yes	yes	yes	4
BC2304-LHTQ	3 x 2 x 2-1/2	14.5	no	yes	yes	yes	4
BC2304-LHTQ-2	3 x 3-3/4 x 2-1/2	27.0	no	yes	yes	yes	8
BC2304-LHTQ-3	3 x 5-1/2 x 2-1/2	39.5	no	no	yes	yes	12
BC2304-LHTQ-4	3 x 7-3/8 x 2-1/2	52.0	no	no	yes	yes	16
BC3104-LHTQ	3 x 2 x 2-1/2	16.0	yes	yes	yes	yes	4

Device Boxes

Conduit Knockouts





		
CI425	BC1102	CI1102-SB
"Screwlok" brackets for rework installation. Max. wall thickness: 5/8 in.	Recessed ears	
		
CI3102-SSX	BC1104	CI1104-B
"Wraparound" bracket for 1-5/8 in. steel studs. With integral support bracket.	Recessed ears	







Cat. No	Volume (Cu. in.)	Features		Knockouts	
		Ears	Bracket	1/2 in. ends	1/2 in. bottom
2 in. Deep — Gangable — 3 in. x 2 in					
CI425	10.0	flush	rework	2	-
BC1102	10.0	recessed	-	2	-
CI1102-SB	10.0	-	“SB”	2	-
CI3102-SSX	12.0	-	“SSX”	2	-
2-1/2 in. Deep — Gangable — 3 in. x 2 in.					
BC1104	12.5	recessed	-	2	2
CI1104-B	12.5	-	“B”	2	2

Device Boxes

Conduit Knockouts

			
CI1104-K	BC1104-LE	CI1104-SB	BCR2000
Concentric knockouts. Recessed ears.	Less ears.		

			
CI3104-KSSX	BC3104-KSS1X-1	CI3104-SSX	CI1004
Concentric knockouts. "Wraparound" bracket for 2-1/2 in. and 3-5/8 in. steel studs. With integral support bracket.	Concentric knockouts. "Wraparound" bracket for 2-1/2 in. and 3-5/8 in. steel studs. With integral support bracket. Brackets positioned for 2 layers of 1/2 in. Drywall.	"Wraparound" bracket for 2-1/2 in. and 3-5/8 in. steel studs. With integral support bracket.	Recessed ears.



Cat. No.	Volume (Cu. in.)	Features		Knockouts		
		Ears	Bracket	1/2 in. ends	1/2 in. bottom	3/4 in. ends
2 in. Deep — Gangable — 3 in. x 2 in.						
CI1104-K	12.5	recessed	-	2	2	2
BC1104-LE	12.5	-	-	2	2	-
CI1104-SB	12.5	-	“SB”	2	2	-
CI3104-KSSX	16.0	-	“SSX”	2	2	2
BC3104-KSS1X-1	16.0	-	“SSX”	2	2	2
CI3104-SSX	16.0	-	“SSX”	2	2	-
3 in. Deep — Gangable — 3 in. x 2 in						
CI1004	15.0	recessed	-	2	2	-
CI3004-KSSX-1.25	18.0	-	“SSX”	-	1	2

Cat. No.	Volume (Cu. in.)	Usage	Ground Screw	Knockout
2 in. Deep — Non-Gangable — 3-3/4 in. x 4 in. x 2 in.				
BCR2000*	18.0	K0	2	2

*Supplied c/w one CI4004 connector



Device Boxes

Armoured and Nonmetallic Sheathed Cable Clamps


BC1100-L


Flush ears.


BC1100-LLE


Less ears.


CI1100-LRE

Recessed ears.


CI425-L

"Screwlok" brackets for rework installation.
Max. wall thickness: 5/8 in.


BC1102-L

Flush ears.


BC1102-LH

Provision for external nailing.



Cat. No.	Volume (Cu. in.)	Features		Pryouts
		Ears	Bracket	ends
1-1/2 in. Deep — Gangable — 3 in. x 2 in.				
BC1100-L	8.0	flush	-	4
BC1100-LLE	8.0	-	-	4
CI1100-LRE	8.0	recessed	-	4
2 in. Deep — Gangable — 3 in. x 2 in.				
CI425-L	10.0	flush	rework	4
BC1102-L	10.0	flush	-	4
BC1102-LH	10.0	-	-	4

Device Boxes

Armoured and Nonmetallic Sheathed Cable Clamps






			
CI775-L	BC775-LD	BC777-LRB	CI525-L
Flush ears.	"Swing-arm" rework brackets. Max. wall thickness: 3/4 in.	Pivoting ends for rework installation. Max. wall thickness: 1-1/8 in. * Non-Gangable	"Screwlok" brackets for rework installation. Max. wall thickness: 5/8 in.
			
BC1104-LB	BC1104-LHT	CI1104-LMS	BC1104-L
	Positioning tabs. Provision for external nailing. Two embossed mounting slots for internal screw installation.	Mounting strap with prongs. Recessed 1/2 in.	Flush ears.
			
BC1104-LRB	BC1104-LRW	BC1104-LSSX	BC1304-LHTQ
Flat sides for rework applications.	Rework bracket for closed wall applications. Max. wall thickness: 1 in.		One screw mounting. Provision for external nailing. Positioning tabs for 1/2 in. and 3/4 in. drywall.










Cat. No.	Volume (Cu. in.)	Features		Pryouts	Knockouts
		Ears	Bracket	ends	1/2 in. bottom
2-1/4 in. Deep — Gangable — 3 in. x 2 in. - For use with nonmetallic sheathed cable only					
CI775-L	10.0	flush	-	4	1
BC775-LD	10.0	flush	rework	4	1
BC777-LRB*	11.0	-	rework	4	1
2-1/2 in. Deep — Gangable — 3 in. x 2 in.					
CI525-L	12.5	flush	rework	4	-
BC1104-L	12.5	flush	-	4	-
BC1104-LB	12.5	-	“B”	4	-
BC1104-LHT	12.5	-	P. Tabs	4	-
CI1104-LMS	12.5	-	“MS”	4	-
BC1104-LRB	12.5	flush	-	4	-
BC1104-LRW	12.5	flush	rework	4	-
BC1104-LSSX	12.5	-	“SSX”	4	-
BC1304-LHTQ	14.5	-	P. Tabs	4	-

Device Boxes

Armoured and Nonmetallic Sheathed Cable Clamps

				
BC2104-LLE	BC2304-LHTQ	BC2104-LX	BC2104-LN	BC2104-LRB
Holding prongs and prepositioned depth tabs.	One screw mounting. Provision for external nailing. Positioning tabs for 1/2 in. and 3/4 in. drywall.	Self-locking spring clamps. Holding prongs and prepositioned depth tabs. Raised ground screws. Approved for nonmetallic sheathed cable only.	Staked nails. Holding prongs and prepositioned depth tabs.	Flat sides for rework applications. 1 gang.

			
BC2104-LLE-2	BC2104-LRB-2	BC2104-LLE-3	BC2104-LLE-4
2 gang. Holding prongs and prepositioned depth tabs.	Flat sides for rework applications. 2 gang.	3 gang. Holding prongs and prepositioned depth tabs.	4 gang. Holding prongs and prepositioned depth tabs.










		
BC2304-LHTQ-2	BC2304-LHTQ-3	BC2304-LHTQ-4
2 gang. Holding prongs and prepositioned depth tabs.	3 gang. Holding prongs and prepositioned depth tabs.	4 gang. Holding prongs and prepositioned depth tabs.



Cat. No.	Width (in.)	Volume (Cu. in.)	Features		Pryouts
			Ears	Bracket	ends
2-1/2 in. Deep — Non-Gangable — 3 in. High					
BC2104-LLE	2	12.5	-	P. Tabs	4
BC2104-LLE-2	3-3/4	25.0	-	P. Tabs	8
BC2104-LLE-3	5-1/2	37.5	-	P. Tabs	12
BC2104-LLE-4	7-3/8	50.0	-	P. Tabs	16
BC2104-LN	2	12.5	-	P. Tabs/Nails	4
BC2104-LX	2	12.5	-	P. Tabs	4
BC2304-LHTQ	2	14.5	-	P. Tabs	4
BC2304-LHTQ-2	3-3/4	27.0	-	P. Tabs	8
BC2304-LHTQ-3	5-1/2	39.5	-	P. Tabs	12
BC2304-LHTQ-4	7-3/8	52.0	-	P. Tabs	16
BC2104-LRB	2	12.5	-	-	4
BC2104-LRB-2	3-3/4	25.0	-	-	8

Device Boxes

Armoured and Nonmetallic Sheathed Cable Clamps









		
CI2104-LSSA1X-1	CI2104-LSSA2X-1	CI2104-LSSX
"Wraparound" bracket for 2-1/2 in. and 3-5/8 in. steel studs. With integral support bracket. Brackets positioned for 2 layers of 1/2 in. drywall.	"Wraparound" bracket for 2-1/2 in. and 3-5/8 in. steel studs. With integral support bracket. Brackets positioned for 2 layers of 1/2 in. drywall.	"Wraparound" bracket for 2-1/2 in. and 3-5/8 in. steel studs. With integral support bracket.
		
CI2104-LSS1X-1	CI2104-LSS2X-1	CI2104-LSS2X
"Wraparound" bracket for 2-1/2 in. and 3-5/8 in. steel studs. With integral support bracket. Brackets positioned for 2 layers of 1/2 in. drywall.	"Wraparound" bracket for 2-1/2 in. and 3-5/8 in. steel studs. With integral support bracket. Brackets positioned for 2 layers of 1/2 in. drywall.	"Wraparound" bracket for 2-1/2 in. and 3-5/8 in. steel studs. With integral support bracket.
		
CI2104-LSS3X-1	CI2104-LSS3X	BC1504-LLE
"Wraparound" brackets for 2-1/2 in. and 3-5/8 in. steel studs. With integral support bracket. Brackets positioned for 2 layers of 1/2 in. drywall.	"Wraparound" brackets for 2-1/2 in. and 3-5/8 in. steel studs. With integral support bracket.	Holding prongs and prepositioned depth tabs on one side.



Cat. No.	Width (in.)	Volume (Cu. in.)	Features		Pryouts ends
			Ears	Bracket	
2-1/2 in. Deep — Non-Gangable — 3 in. High					
CI2104-LSSA1X-1	2	12.5	-	“SSX”	4
CI2104-LSSA2X-1	3-3/4	25.0	-	“SSX”	8
CI2104-LSSX	2	12.5	-	“SSX”	4
CI2104-LSS1X-1	2	12.5	-	“SSX”	4
CI2104-LSS2X-1	3-3/4	25.0	-	“SSX”	8
CI2104-LSS2X	3-3/4	25.0	-	“SSX”	8
CI2104-LSS3X-1	5-1/2	37.5	-	“SSX”	12
CI2104-LSS3X	5-1/2	37.5	-	“SSX”	12
2-1/2 in. Deep — Non-Gangable — 3 in. High					
BC1504-LLE	2-1/4	15.0	-	P. Tabs	4


Device Boxes

Armoured and Nonmetallic Sheathed Cable Clamps

			
BC3104-LH	BC3104-LHTQ	BC3104-LSSX	CI3104-LSS1X-1
Positioning tabs. Provision for external nailing.	One screw mounting. Provision for external nailing. Positioning tabs for 1/2 in. and 3/4 in. drywall.	"Wraparound" bracket for 2-1/2 in. and 3-5/8 in. steel studs. With integral support bracket.	"Wraparound" bracket for 2-1/2 in. and 3-5/8 in. steel studs. With integral support bracket. Brackets positioned for 2 layers of 1/2 in. drywall.
			
CI1804-LH	BC2004-LH	BC2004-LHTQ	CI2016-LX
Positioning tabs. External nailing. Mounting slots for internal screw installation. X-Cube adds 5.5 cu. in.	Provision for external nailing. Holding prongs and prepositioned depth tabs on one side.	Internally embossed slots for screw mounting. Fixed positioning tabs for single 1/2 in. drywall along with retractable positioning tabs for double 1/2 in. drywall applications. Fixed positioning tabs for outside wall applications. Holding prongs. One screw mounting.	Self-locking spring clamps. Holding prongs and prepositioned depth tabs on one side. Approved for nonmetallic sheathed cable only.










Cat. No.	Volume (Cu. in.)	Features		Pryouts ends
		Ears	Bracket	
2-1/2 in. Deep — Gangable — 3 in. x 2 in.				
BC3104-LH	16.0	-	P. Tabs	4
BC3104-LHTQ	16.0	-	P. Tabs	4
BC3104-LSSX	16.0	-	“SSX”	4
CI3104-LSS1X-1	16.0	-	“SSX”	4
CI1804-LH	18.0	-	P. Tabs	4
2-3/4 in. Deep — Non-Gangable — 3-3/4 in. x 2-3/16 in.				
BC2004-LH	18.5	-	P. Tabs	4
BC2004-LHTQ	20.5	-	P. Tabs	4
2-1/2 in. Deep — Non-Gangable — 3-3/4 in. x 2 in.				
CI2016-LX	18.5	-	P. Tabs	4



Device Boxes

Armoured and Nonmetallic Sheathed Cable Clamps


			
BC1004-L	BC1004-LH	CI1004-LB	BC1018-LHTQ
Flush ears.	Positioning tabs. Provision for external nailing. Two embossed mounting slots for internal screw installation.	Side bracket wood stud.	One screw mounting provisions for external nailing.

		
BC1304-LHT	BC3004-LH	CI3004-LSSX-1
Provision for external nailing.	Provision for external nailing.	1 in. recessed brackets for 2-1/2 in. and 3-5/8 in. steel studs. Brackets positioned for 2 layers of 1/2 in. drywall.




Cat. No.	Volume (Cu. in.)	Features		Pryouts
		Ears	Bracket	ends
3 in. Deep — Gangable — 3 in. x 2 in.				
BC1004-L	15.0	flush	-	4
BC1004-LH	15.0	-	P. Tabs	4
CI1004-LB	16.0	-	“B”	4
BC1018-LHTQ	18.0	-	P. Tabs	4
BC1304-LHT	14.5	-	P. Tabs	4
BC3004-LH	18.0	-	-	4
CI3004-LSSX	18.0	-	“SSX”	4
CI3004-LSSX-1	18.0	-	“SSX”	4
CI3004-LSSAX-1.25*	18.0	-	“SSX”	4

* Brackets positioned for 2 layers of 5/8 in. drywall



Device Boxes

Armoured and Nonmetallic Sheathed Cable Clamps



CI3102-LSSAX

"Wraparound" bracket for 1-5/8 in. steel studs. With integral support bracket.




BC1104-LA

Flush ears.




BC1104-LHA

Positioning tabs. Provision for external nailing. Two embossed mounting slots for internal screw installation.




CI1104-LMSA

Mounting strap recessed 1/2 in.



BC1104-LSSAX



CI3004-LSSAX-1

1 in. recessed brackets for 2-1/2 in. and 3-5/8 in. steel studs. Brackets positioned for 2 layers of 1/2 in. drywall.




Cat. No.	Volume (Cu. in.)	Features		Pryouts
		Ears	Bracket	ends
2 in. Deep — Gangable — 3 in. x 2 in.				
CI3102-LSSAX	12.0	-	“SSX”	4
2-1/2 in. Deep — Gangable — 3 in. x 2 in.				
BC1104-LA	12.5	flush	-	4
BC1104-LHA	12.5	-	P. Tabs	4
CI1104-LMSA	12.5	-	“MS”	4
BC1104-LSSAX	12.5	-	“SSX”	4
3 in. Deep — Gangable — 3 in. x 2 in.				
CI3004-LSSAX-1*	18.0	-	“SSX”	4

* Brackets positioned for 2 layers of 1/2 in. drywall





CI3004-LSSAX-1

Top View



Device Boxes

Armoured and Nonmetallic Sheathed Cable Clamps


	
CI2104-LLEA	CI2104-LSSAX
Holding prongs and prepositioned depth tabs.	"Wraparound" bracket for 2-1/2 in. and 3-5/8 in. steel studs. With integral support bracket.
	
CI2104-LSSA-2X	CI2104-LSSA-3X
2 gang. "Wraparound" bracket for 2-1/2 in. and 3-5/8 in. steel studs. With integral support bracket.	3 gang. "Wraparound" bracket for 2-1/2 in. and 3-5/8 in. steel studs. With integral support bracket.




Cat. No.	Width (in.)	Volume (Cu. in.)	Features		Pryouts
			Ears	Bracket	ends
2-1/2 in. Deep — Non-Gangable — 3 in. High					
CI2104-LLEA	2	12.5	-	P. Tabs	4
CI2104-LSSAX	2	12.5	-	P. Tabs	4
CI2104-LSSA-2X	4	25	-	“SSX”	8
CI2104-LSSA-3X	6	37.5	-	“SSX”	12

Device Boxes


Armoured and Nonmetallic Sheathed Cable Clamps


CI1504-LSSAX


"Wraparound" bracket for 2-1/2 in. and 3-5/8 in. steel studs. With integral support bracket.


CI3104-LHA


Positioning tabs. Provision for external nailing.


BC3104-LSSAX


"Wraparound" bracket for 2-1/2 in. and 3-5/8 in. steel studs. With integral support bracket.


CI3104-LSSA1X-1


1 in. recessed brackets for 2-1/2 in. and 3-5/8 in. steel studs. **Brackets positioned for 2 layers of 1/2 in. drywall.**


BC3104-LSSX

"Wraparound" bracket for 2-1/2 in. and 3-5/8 in. steel studs. With integral support bracket.


CI2004-LHA

Provision for external nailing. Holding prongs and prepositioned depth tabs.


CI1004-LHA
















Positioning tabs. Provision for external nailing. Two embossed mounting slots for internal screw installation.



Cat. No.	Volume (Cu. in.)	Features		Pryouts
		Ears	Bracket	ends
2-1/2 in. Deep — Non-Gangable — 3 in. x 2-1/4 in.				
CI1504-LSSAX	15.0	-	“SSX”	4
2-1/2 in. Deep — Gangable — 3 in. x 2 in.				
CI3104-LHA	16.0	-	P. Tabs	4
BC3104-LSSAX	16.0	-	“SSX”	4
CI3104-LSSA1X-1	16.0	-	“SSX”	4
BC3104-LSSX	16.0		P. Tabs	4
2-3/4 in. Deep — Non-Gangable — 3-3/4 in. x 2-3/16 in.				
CI2004-LHA	18.5	-	P. Tabs	4
3 in. Deep — Gangable — 3 in. x 2 in.				
CI1004-LHA	15.0		P. Tabs	4

Device Boxes

Boxes for ICF Construction

			
BC2104-LMS	BC2104-LMS-2	BC2104-LMS-3	BC2104-LMS-4
			
BC2104-LMSA	BC2104-LMSA-2	BC2104-LMSA-3	BC2104-LMSA-4
			
CI3102-LMS	CI3102-LMSA	CI3102-MS	BC52151-KMS
			
BC52171-KMS	CI72151-KMS	BC72171-KMS	



Cat. No.	Volume (Cu. in.)	Dimensions H x W x D (in.)	Features	Gangable Yes or No
Device Boxes				
BC2104-LMS	12.5	3 x 2 x 2-1/2	BX/Loomex	Yes
BC2104-LMS-2	25.0	3 x 3-3/4 x 2-1/2	Loomex/BX	No
BC2104-LMS-3	37.5	3 x 5-1/2 x 2-1/2	Loomex/BX	No
BC2104-LMS-4	50.0	3 x 7-3/8 x 2-1/2	Loomex/BX	No
BC2104-LMSA	12.5	3 x 2 x 2-1/2	BX/Loomex	No
BC2104-LMSA-2	25.0	3 x 3-3/4 x 2-1/2	BX/Loomex	No
BC2104-LMSA-3	37.5	3 x 5-1/2 x 2-1/2	BX/Loomex	No
BC2104-LMSA-4	50.0	3 x 7-3/8 x 2-1/2	BX/Loomex	No
CI3102-LMS	12.0	3 x 2 x 2	Loomex/BX	Yes
CI3102-LMSA	12.0	3 x 2 x 2	BX/Loomex	Yes
CI3102-MS	12.0	3 x 2 x 2	Conduit	Yes
BC54151-LMS	15.0	4 x 4 x 1-1/2	Loomex/BX	No
BC54151-LMSA	15.0	4 x 4 x 1-1/2	BX/Loomex	No

Cat. No.	Volume (Cu. in.)	Dimensions H x W x D (in.)	Knockouts			
			1/2 in. sides	1/2 in. bottom	3/4 in. sides	3/4 in. bottom
Conduit Knockouts						
BC52151-KMS	15.0	4 x 4 x 1-1/2	4	2	2	2
BC52171-KMS	30.0	4 x 4 x 2-1/8	4	2	2	2
CI72151-KMS	30.0	4-11/16 x 4-11/16 x 1-1/2	-	2	4	2
BC72171-KMS	42.0	4-11/16 x 4-11/16 x 2-1/8	-	2	4	2

Device Boxes


Stainless Steel Wall Plates

General Usage

Toggle Switch



CI97071




CI97080 (1 gang to 10 gangs)

Duplex Receptacle



CI97101



CI97102

Blank Box Mounting (3.281 in.)




CI97011

GFCI / Decora



CI97401




CI97406 (1 gang to 6 gangs)

Blank Device Mounting (2.375 in.)



CI97121



CI97124 (1 gang to 4 gangs)

Combination Switch / Receptacle



CI97532








CI97573 (2 gang to 7 gangs)

Device Boxes

Stainless Steel Wall Plates





Specialty Usage

Telephone		Emergency	Single Receptacle	GFCI Conversion Kit
				
* CI97181		CI6851-RF	CI97091	BC97002
3/8 in. opening.		ON / OFF	1-13/32 in. diameter.	For 4 in. square boxes.

347 V Toggle Specialty Usage

For 1204 Series			For MBD / MBS Series
			
CI6851-HV	CI6854-HV	CI6851-HV	CI97074-HVR
	1 gang to 4 gangs		1 gang to 4 gangs

347 V Blank



For 1204 Series		For MBD/MBS Series	
			
CI97151-HV	CI97154-HV	CI97151-HV	CI97154-HVR
1 gang, 2 gangs and 4 gangs		1 gang, 2 gangs and 4 gangs	

Device Boxes


Stainless Steel Wall Plates

Dimensions


Standard all Plate



Mounting Hole Spacings



347 V Wall Plate




Dimensions are in inches.

Device Boxes

Stainless Steel Wall Plates

Selection Guide

DESCRIPTION	1 GANG	2 GANGS	3 GANGS	4 GANGS	5 GANGS	6 GANGS	7 GANGS	8 GANGS	9 GANGS	10 GANGS
Toggle Switch	CI97071	CI97072	CI97073	CI97074	CI97075	CI97076		CI97078	CI97079	CI97080
Duplex Receptacle	CI97101	CI97102								
Blank Boxes										
Mounting 3.281 in.	CI97011	CI97012	CI97013	CI97014						
Blank Device										
Mounting 2.375 in.	CI97121	CI97122	CI97123	CI97124						
GFCI / Decora	CI97401	CI97402	CI97403	CI97404	CI97405	CI97406				
GFCI Conversion Kit		BC97002								
Combination										
Switch / Receptacle		CI97532			CI97563	CI97573				
15 A Receptacle	CI97091									
Telephone 3/8 in. Opening	* CI97181									
Telephone 5/8 in. Opening	* CI97191									
Emergency On / Off	CI6851-RF									
347 V Toggle										
for 1204 Series	CI6851-HV	CI6852-HV	CI6853-HV	CI6854-HV						
347 V Blank										
for 1204 Series	CI97151-HV	CI97152-HV		CI97154-HV						
347 V Toggle	USE									
for MBD and MBS Series	CI6851-HV	CI97072-HVR	CI97073-HVR	CI97074-HVR						
347 V Blank	USE									
for MBD and MBS Series	CI97151-HV	CI97152-HVR		CI97154-HVR						

 * Not applicable.

Technical Specifications

Type 430 Stainless Steel

- 16% chrome
- Corrosion resistant
- Recommended for industrial, commercial and institutional applications
- Supplied with nickel plated brass screws
- 1 to 3 gangs — Vertically Brushed
- 4 gangs and up — Horizontally Brushed