

# Technical Information Bulletin


## DESIGN LED Lamps



Date: \_\_\_\_\_ Name of distributor: \_\_\_\_\_  
 In hands date of project: \_\_\_\_\_ Client #: \_\_\_\_\_  
 Project name/Number: \_\_\_\_\_ Name of end user: \_\_\_\_\_

### ORDERING INFORMATION

**Order code:** 67615  
**Description:** GU10/7W/30K/45/DESIGN/STD  
**UPC:** 69549676152  
**Case quantity:** 10/100



MOL: 2 5/32" (55 mm) Dia.: 1 31/32" (50 mm)

### PHYSICAL DATA

**Type:** GU10  
**Base:** GU10  
**Material:** Glass  
**Lens type:** Clear

### PERFORMANCE DATA

**Watts (W):** 7  
**Lamp volts (VAC):** 120  
**Colour temperature (K)<sup>1</sup>:** 3 000  
**Life L70 (hrs):** 25 000  
**Lumens (lm)<sup>2</sup>:** 530  
**Lumens per watt (lm/W):** 76  
**Traditional equivalent (W):** 50  
**CRI:** 80  
**Beam angle (°):** 45  
**CBCP (cd):** 600  
**THD (%):** 50  
**Frequency (Hz):** 60  
**Power factor:** 0.8  
**Operating temperature range:** -20°C to 45°C (-4°F to 113°F)

<sup>1</sup> Typical colour temperature range: +/- 5 %  
<sup>2</sup> Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %

### COMPATIBLE DIMMERS

<b>Leviton</b>	IPL06*, 6674*, DSL06-1LZ*, IPE04-1LZ,
<b>Lutron</b>	PD-5NE, RRD-6NA, CTCL-153P*, DVVRP-253P, SELV-300P
<b>Legrand</b>	RH703PTUTC

\* Low noise might occur within the dimming range



Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: \_\_\_\_\_  
 Company: \_\_\_\_\_  
 Signature: \_\_\_\_\_ Date: \_\_\_\_\_

This lighting equipment complies with Canadian standard ICES-005 for use in residential applications. Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.