

# Technical Information Bulletin


## CHOICE LED Lamps



Date: \_\_\_\_\_ Name of distributor: \_\_\_\_\_  
 In hands date of project: \_\_\_\_\_ Client #: \_\_\_\_\_  
 Project name/Number: \_\_\_\_\_ Name of end user: \_\_\_\_\_

### ORDERING INFORMATION

Order code: 66310  
 Description: MR16/12V/6.5W/30K/35/CHOICE/STD  
 UPC: 69549663107  
 Case quantity: 24



### PERFORMANCE DATA

Shape: MR16  
 Base: GU5.3  
 Watts(W): 6.5  
 Volts (VAC): 12  
 Colour temperature (K)\*\*: 3 000  
 Life L70 (hrs): 25 000  
 Initial lumens (lm)\*: 557  
 Initial lumens per watt (lm/W): 86  
 CRI: 83  
 Beam angle (°): 35  
 CBCP: 778  
 Power factor: 0.92  
 Operating temperature range: -20 °C to 40 °C (-4 °F to 104 °F)  
 Traditional equivalent (W): 50

\*Initial lumens range: +/- 10 %      \*\*Typical colour temperature range: +/- 10 %



### CAUTIONS

- Turn power off before inspection, installation, or removal.
- Not for use in totally enclosed luminaires.
- Suitable for use in damp locations.
- Do not open – no user serviceable parts inside.
- Use only on 120 VAC, 60Hz circuits.
- This device is not intended for use with emergency exit fixtures or emergency exit lights.
- Compatible with most dimmers.
- For complete dimmer and warranty information visit [www.standardpro.com](http://www.standardpro.com).

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: \_\_\_\_\_  
 Company: \_\_\_\_\_  
 Signature: \_\_\_\_\_ Date: \_\_\_\_\_

This lighting equipment complies with Canadian standard ICES-005 for use in residential applications.  
 Data is based upon tests performed in a controlled environment and representative of relative performance.  
 Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.