

Low voltage brackets

Steel

Features and benefits

- Eliminates the need for an electrical box when installing low voltage Class 2 wiring
- For old work or new work
- Installs easily with a drywall saw and screwdriver



CIMB-0



CIMB-1



CICSB-1



WBF-1

| Cat. No. | Description |
|--------------------------------------|--|
| Low voltage mounting brackets | |
| CIMB-0 | Flat mounting brackets that provides quick installation of low voltage class 2 communication outlets. Positioning tabs ensure straight installation |
| CIMB-1 | Mounting bracket that provides quick installation of low voltage class 2 communication outlets. Raised 1/2 in. Positioning tabs ensure straight installation |
| CICSB-1 | Mounting brackets that provides quick installation of low voltage communication outlets. May be used with all 2 1/2 in. deep gangable boxes |
| WBF-1 | Low voltage wall bracket |




CI1544



CI1544P



CIS-1X2



CIS-2 / CIS-4

| Cat. No. | Dimensions (in.) | | Hole Size (in.) | Suggested Application NMD90 (loomex) |
|--|------------------|----------|-----------------|--|
| | H | W | | |
| Nailing straps (Zinc plated steel) | | | | |
| CI1544 | 0.25 | 0.51 | - | 14/2-12/2 |
| Nailing straps (Polyethylene) | | | | |
| CI1544-P | 0.25 | 0.49 | - | 14/2-12/2 |
| CI1546-P | 0.25 | 0.75 | - | 14/2-8/2 |
| Cable staples (Galvanized steel) | | | | |
| CIS-1 | 0.25 | 0.48 | - | 14/2-12/2 |
| CIS-2 | 0.44 | 0.54 | - | 14/2-10/2; 14/3-10/3; 2 cables 14/2; 2 cables 12/2 |
| CIS-3 | 0.49 | 0.70 | - | 10/2-8/2; 14/3-10/3 |
| CIS-4 | 0.76 | 0.86 | - | 8/3-6/3 |
| Double cable staples (Galvanized steel) | | | | |
| CIS-1X2 | 0.25 | 0.48 X 2 | - | 14/2-12/2 |
| CIS-1X2-FP3 | 0.25 | 0.48 X 2 | - | |
| CIS-1X2-FP5 | 0.25 | 0.48 X 2 | - | |

Low voltage brackets

Nonmetallic

—
01 SC100A, SC200A, SC300A
 Open-backed to easily accommodate the bend radiuses required for low voltage cabling and deep devices such as volume controls, and is designed to fit a standard two-gang three-gang faceplate. It also features an easy nail-on mounting or screw-in bracket, while more hard shell provides increased durability and no racking.




—
01

—
02 SC100RR
 Swing arm rework bracket. 1 gang.

—
03 SC200RR
 Swing arm rework bracket. 2 gang.

—
04 SC100SC
 This low voltage bracket provides a low voltage outlet next to a previously installed high voltage outlet. For new construction and rework. Attaches easily to most electrical boxes, and is designed to fit a standard two-gang faceplate.



—
02

—
03

—
04

—
05

—
05 SC100ADJC
 New work adjustable low voltage bracket. 1 gang.



| Cat. No. | Description |
|--|--|
| Low voltage brackets | |
| SC100A | One-gang backless bracket 2.32 in. W x 3.73 in. L |
| SC200A | Two-gang backless bracket 5.35 in. W x 3.81 in. L |
| SC300A | Three-gang backless bracket 8.69 in. W x 7.20 in. L |
| Old work backless brackets | |
| SC100RR | One-gang backless old work bracket w/ swing clamps 2 ¹ / ₄ in. x 3 ¹ / ₄ in. |
| SC200RR | Two-gang backless old work bracket w/ swing clamps 3.92 in. x 4.00 in. |
| Low voltage add-on bracket | |
| SC100SC | One-gang add-on bracket 1.80 in. W x 3.68 in. L |
| One-gang and two gang – low voltage | |
| SC100ADJC | One-gang adjustable brackless bracket 3 ⁷ / ₈ in. W x 3 ³ / ₄ in. H |
| SC200ADJC | Two-gang adjustable brackless bracket 5 ⁵ / ₈ in. W x 3 ⁵ / ₈ in. H |
| CSA not applicable | |